

FLOOR OIL

Page: 1

Compilation date: 11/09/2012

Revision No: 3

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name: FLOOR OIL

Product code: FOIL

Synonyms: FLOOR OIL

## 1.2. Relevant identified uses of the substance or mixture and uses advised against

### 1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd

Waterloo Road Cricklewood London NW2 7TX

United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

### 1.4. Emergency telephone number

# Section 2: Hazards identification

## 2.1. Classification of the substance or mixture

Classification under CHIP: -: R10; -: R66; -: R67

Most important adverse effects: Flammable. Repeated exposure may cause skin dryness or cracking. Vapours may

cause drowsiness and dizziness.

#### 2.2. Label elements

Label elements under CHIP:

**Hazard symbols:** Symbol not required.

Risk phrases: R10: Flammable.

R66: Repeated exposure may cause skin dryness or cracking.

R67: Vapours may cause drowsiness and dizziness.

Safety phrases: S2: Keep out of the reach of children.

S46: If swallowed, seek medical advice immediately and show this container or label.

Precautionary phrases: Contains gum turpentine, cobalt octoate, methyl ethyl ketoxime. May produce an allergic

reaction.

FLOOR OIL

Page: 2

#### 2.3. Other hazards

**PBT:** This substance is not identified as a PBT substance.

#### Section 3: Composition/information on ingredients

#### 3.2. Mixtures

### **Hazardous ingredients:**

#### NAPTHA (PETROLEUM) HYDROTREATED HEAVY

EINECS	CAS	CHIP Classification	CLP Classification	Percent
265-150-3	64742-48-9	Xn: R65; -: R66; -: R67	-	50-70%
GUM TURPEN	NTINE			
-	-	-: R10; Xn: R20/21/22; Xi: R36/38; Sens.: R43; N: R51/53; Xn: R65	-	<1%
CALCIUM DRI	IER 4%			
-	-	-: R10; N: R51/53; Xn: R65; -: R66	-	<1%
1,2,4-TRIMET	HYLBENZENE			
202-436-9	95-63-6	-: R10; Xn: R20; Xi: R36/37/38; N: R51/53	Flam. Liq. 3: H226; Acute Tox. 4: H332; Eye Irrit. 2: H319; STOT SE 3: H335; Skin Irrit. 2: H315; Aquatic Chronic 2: H411	<1%
LOW BOILING	POINT NAPHTH	IA - UNSPECIFIED - SOLVENT NAPHT	HA (PETROLEUM), LIGHT AROM.	•
265-199-0	64742-95-6	Xn: R65; -: R10; Xi: R37; N:	Asp. Tox. 1: H304; Flam. Liq. 3: H226;	<1%

### Section 4: First aid measures

# 4.1. Description of first aid measures

**Skin contact:** Remove contaminated clothing. Wash skin thoroughly with soap and water or use a proprietry skin cleaner. Do NOT use solvents or thinners. If irritation persists seek

medical attention.

R51/53

Eye contact: Contact lenses should be removed. Irrigate copiously with clean, fresh water for at least

H411

STOT SE 3: H335; Aquatic Chronic 2:

10 minutes, holding the eyelids apart, and seek medical advice.

Ingestion: If accidentally swallowed, wash mouth out with water. Do not induce vomiting, keep at

rest and obtain medical attention.

Inhalation: Remove to fresh air, keep the patient warm and at rest. If breathing has stopped,

administer artificial respiration. Give nothing by mouth if unconscious, place in the

recovery position and seek medical advice.

## 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** May cause irritation on prolonged or repeated contact.

FLOOR OIL

Page: 3

**Eye contact:** Irritation with short term redness and stinging.

Ingestion: May cause nausea and diarrhoea.

**Inhalation:** May cause irritation of the respiratory tract.

### 4.3. Indication of any immediate medical attention and special treatment needed

### Section 5: Fire-fighting measures

### 5.1. Extinguishing media

Extinguishing media: Carbon dioxide (CO2). Dry chemical powder. Alcohol resistant foam. Sand or earth. Do

NOT use water jet.

#### 5.2. Special hazards arising from the substance or mixture

Exposure hazards: In a fire, hazardous decomposition products such as smoke and Carbon Monoxide may

be produced.

#### 5.3. Advice for fire-fighters

Advice for fire-fighters: Exposure to decomposition products may be a hazard to health. Appropriate self-

contained breathing apparatus may be required. Cool closed containers exposed to fire with water spray. Do NOT allow run-off from fire fighting to enter drains or water courses.

#### Section 6: Accidental release measures

# 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Ventilate the area. Eliminate all sources of ignition. No Smoking. Avoid inhaling vapour.

Mark out the contaminated area with signs and prevent access to unauthorised

personnel. Do not attempt to take action without suitable protective clothing (see section

8).

#### 6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. If the product enters drains or sewers, the local

water company should be contacted immediately. In the case of contamination of

streams, rivers or lakes contact the relevant environment agency.

### 6.3. Methods and material for containment and cleaning up

Clean-up procedures: Contain and collect spillages with non-combustible absorbent materials, e.g. sand,

earth, vermiculite. Transfer into a suitable container for disposal in accordance with the waste regulations (see section 13) Do not use equipment in clean-up procedure which

may produce sparks. Clean preferably with a detergent, avoid the use of solvents.

## 6.4. Reference to other sections

#### Section 7: Handling and storage

### 7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Avoid inhalation of vapour. Avoid skin

FLOOR OIL

Page: 4

and eye contact. Smoking, eating and drinking should be prohibited in areas of storage and use. Exclude sources of heat, sparks and open flame. Earth any equipment used in handling. Use non-sparking tools. The Manual Handling Operations Regulations may apply to the handling of containers of this product.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. Keep away from direct

sunlight. Exclude sources of heat, sparks and open flame. Take precautionary measures to prevent product spills into drains, the ground or waters. Although the storage of this product is not subject to specific statutory requirements, the principles contained in the HSE guidance note Storage of Flammable Liquids in containers,

should be observed.

Suitable packaging: Ideally, keep in original container. If transfer is necessary use glass or coated steel

containers.

### 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

#### 8.1. Control parameters

#### **Hazardous ingredients:**

## 1,2,4-TRIMETHYLBENZENE

#### Workplace exposure limits:

# Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	125 mg/m3	-	-	-

## 8.2. Exposure controls

Engineering measures: Provide adequate ventilation. Where reasonably practicable, this should be achieved by

the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and/or solvent vapours below the relevant occupational exposure limits, suitable respiratory protective equipment should be worn

(see Respiratory protection below).

**Respiratory protection:** All personal protective equipment, including respiratory protective equipment, used to

control exposure to hazardous substances must be selected to meet the requirements

of the COSHH Regulations.

Hand protection: Where repeated skin exposure may occur, wear PVC or Nitrile gloves.

**Eye protection:** Safety goggles. Ensure eye bath is to hand.

**Skin protection:** Overalls are normally suitable, PVC apron if risk of splashing.

#### Section 9: Physical and chemical properties

FLOOR OIL

Page: 5

## 9.1. Information on basic physical and chemical properties

State: Liquid

**Colour:** Pale amber. **Odour:** Paraffinic.

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Oily

Kinematic viscosity: 33

Viscosity test method: Flow time in seconds in a 3 mm ISO cup (ISO 2431)

Flash point °C: 38 Relative density: 0.87 @ 20C

#### 9.2. Other information

Other information: Not applicable.

## Section 10: Stability and reactivity

#### 10.1. Reactivity

### 10.2. Chemical stability

Chemical stability: Stable under normal storage and handling conditions (see Section 7).

## 10.3. Possibility of hazardous reactions

#### 10.4. Conditions to avoid

Conditions to avoid: Avoid heat, flames and sparks. Direct sunlight.

### 10.5. Incompatible materials

Materials to avoid: Oxidising agents. Strong acids.

## 10.6. Hazardous decomposition products

Haz. decomp. products: In a fire, hazardous decomposition products such as smoke and carbon monoxide may

be produced.

## **Section 11: Toxicological information**

### 11.1. Information on toxicological effects

Toxicity values: Not applicable.

### Symptoms / routes of exposure

**Skin contact:** May cause irritation on prolonged or repeated contact.

Eye contact: Irritation with short term redness and stinging.

Ingestion: May cause nausea and diarrhoea.

**Inhalation:** May cause irritation of the respiratory tract.

#### Section 12: Ecological information

FLOOR OIL

Page: 6

12.1. Toxicity

Ecotoxicity values: Not applicable.

12.2. Persistence and degradability

12.3. Bioaccumulative potential

12.4. Mobility in soil

**Mobility:** Insoluble in water. Partially volatile. Partially absorbed into soil. The product should not be allowed to enter drains or water courses or be deposited where it can affect ground

12.5. Results of PBT and vPvB assessment

PBT identification: This substance is not identified as a PBT substance.

12.6. Other adverse effects

Other adverse effects: There is no data available on the product itself.

or surface waters.

Section 13: Disposal considerations

13.1. Waste treatment methods

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information** 

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No Marine pollutant: No

14.6. Special precautions for user

**Section 15: Regulatory information** 

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

FLOOR OIL

Page: 7

#### Section 16: Other information

#### Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No

453/2010.

\* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and 3: H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H340: May cause genetic defects <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

H350: May cause cancer <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

H411: Toxic to aquatic life with long lasting effects.

R10: Flammable.

R20/21/22: Harmful by inhalation, in contact with skin and if swallowed.

R20: Harmful by inhalation.

R36/37/38: Irritating to eyes, respiratory system and skin.

R36/38: Irritating to eyes and skin.

R37: Irritating to respiratory system.

R43: May cause sensitisation by skin contact.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65: Harmful: may cause lung damage if swallowed.

R66: Repeated exposure may cause skin dryness or cracking.

R67: Vapours may cause drowsiness and dizziness.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

and shall be used only as a guide. This company shall not be held liable for any

damage resulting from handling or from contact with the above product. As the specific

conditions of use of the product are outside the supplier's control, the user is

responsible for ensuring that the requirements of relevant legislation are complied with.