



SAFETY DATA SHEET
BRUSH RESTORER

Page: 1

Compilation date: 03/05/2008

Revision date: 09/01/2020

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: BRUSH RESTORER

Product code: BRUR

Synonyms: BRUSH RESTORER

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd

Waterloo Road

Cricklewood

London

NW2 7TX

United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

1.4. Emergency telephone number

Emergency tel: .+44(0)2084504666 (Office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Irrit. 2: H319; Acute Tox. 4: H302; Aquatic Chronic 2: H411; Carc. 2: H351; Flam. Liq. 2: H225; Skin Irrit. 2: H315; STOT SE 2: H371

Most important adverse effects: Highly flammable liquid and vapour. Harmful if swallowed. Causes skin irritation. Causes serious eye irritation. Suspected of causing cancer. May cause damage to organs. Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H225: Highly flammable liquid and vapour.

H302: Harmful if swallowed.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H351: Suspected of causing cancer.

H371: May cause damage to organs.

H411: Toxic to aquatic life with long lasting effects.

[cont...]

SAFETY DATA SHEET

BRUSH RESTORER

Page: 2

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark

GHS08: Health hazard

GHS09: Environmental



Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P241: Use explosion-proof electrical/ventilating/lighting/... equipment.

P260: Do not breathe dust/fumes/gas/mist/vapours/spray.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P301+P312: IF SWALLOWED: Call a POISON CENTRE or doctor if you feel unwell.

P302+P352: IF ON SKIN: Wash with plenty of water.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

1,2,4-TRIMETHYLBENZENE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
202-436-9	95-63-6	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Eye Irrit. 2: H319; STOT SE 3: H335; Skin Irrit. 2: H315; Aquatic Chronic 2: H411	28.800%

DICHLOROMETHANE

200-838-9	75-09-2	-	Carc. 2: H351	26.450%
-----------	---------	---	---------------	---------

LOW BOILING POINT NAPHTHA - UNSPECIFIED - SOLVENT NAPHTHA (PETROLEUM), LIGHT AROM.

265-199-0	64742-95-6	-	Carc. 1B: H350; Muta. 1B: H340; Asp. Tox. 1: H304; Flam. Liq. 3: H226; STOT SE 3: H335; Aquatic Chronic 2: H411	19.200%
-----------	------------	---	---	---------

[cont...]

SAFETY DATA SHEET

BRUSH RESTORER

Page: 3

METHANOL

200-659-6	67-56-1	-	Flam. Liq. 2: H225; Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT SE 1: H370	5.300%
-----------	---------	---	---	--------

XYLENE

215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	4.800%
-----------	-----------	---	--	--------

MESITYLENE

203-604-4	108-67-8	-	Flam. Liq. 3: H226; STOT SE 3: H335; Aquatic Chronic 2: H411	4.800%
-----------	----------	---	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Transfer to hospital as soon as possible.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be soreness and redness of the mouth and throat. There may be difficulty swallowing. Nausea and stomach pain may occur. There may be vomiting.

Inhalation: Absorption through the lungs can occur causing symptoms similar to those of ingestion.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

[cont...]

SAFETY DATA SHEET

BRUSH RESTORER

Page: 4

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid the formation or spread of mists in the air. Avoid direct contact with the substance.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Ideally, keep in original container. If transfer is necessary use glass or coated steel containers. Do not use plastic containers.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

1,2,4-TRIMETHYLBENZENE

Workplace exposure limits:

Respirable dust

State	Workplace exposure limits		Respirable dust	
	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	125 mg/m ³	-	-	-

DICHLOROMETHANE

UK	350 mg/m ³	1060 mg/m ³	-	-
----	-----------------------	------------------------	---	---

[cont...]

SAFETY DATA SHEET

BRUSH RESTORER

Page: 5

METHANOL

UK	266 mg/m ³	333 mg/m ³	-	-
----	-----------------------	-----------------------	---	---

XYLENE

UK	220 mg/m ³	441 mg/m ³	-	-
----	-----------------------	-----------------------	---	---

MESITYLENE

UK	25 ppm	-	-	-
----	--------	---	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and/or solvent vapours below the relevant occupational exposure limits, suitable respiratory protective equipment should be worn (see Respiratory protection below).

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Red

Odour: Pungent

Solubility in water: Partially soluble.

Flash point°C: 22

Relative density: 0.967 @ 20 C

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions. Decomposition may occur on exposure to conditions or materials listed below.

[cont...]

SAFETY DATA SHEET

BRUSH RESTORER

Page: 6

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

1,2,4-TRIMETHYLBENZENE

IPR	RAT	LDLO	1752	mg/kg
ORL	RAT	LD50	5	gm/kg

DICHLOROMETHANE

ORL	MUS	LD50	4770	mg/kg
ORL	RAT	LD50	5350	mg/kg
SCU	MUS	LD50	6460	mg/kg

LOW BOILING POINT NAPHTHA - UNSPECIFIED - SOLVENT NAPHTHA (PETROLEUM), LIGHT AROM.

ORL	RAT	LD50	8400	mg/kg
-----	-----	------	------	-------

METHANOL

IVN	RAT	LD50	2131	mg/kg
ORL	MUS	LD50	7300	mg/kg
ORL	RAT	LD50	5628	mg/kg

XYLENE

ORL	MUS	LD50	2119	mg/kg
ORL	RAT	LD50	4300	mg/kg
SCU	RAT	LD50	1700	mg/kg

MESITYLENE

IPR	GPG	LDLO	1303	mg/kg
-----	-----	------	------	-------

[cont...]

SAFETY DATA SHEET

BRUSH RESTORER

Page: 7

Relevant hazards for product:

Hazard	Route	Basis
Acute toxicity (ac. tox. 4)	ING	Hazardous: calculated
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Carcinogenicity	--	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be soreness and redness of the mouth and throat. There may be difficulty swallowing. Nausea and stomach pain may occur. There may be vomiting.

Inhalation: Absorption through the lungs can occur causing symptoms similar to those of ingestion.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

SAFETY DATA SHEET

BRUSH RESTORER

Page: 8

Section 14: Transport information

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

Shipping name: PAINT

including paint, lacquer, enamel, stain, shellac, varnish, polish, liquid filler and liquid lacquer base

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: I

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D/E

Transport category: 1

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H301: Toxic if swallowed.

H302: Harmful if swallowed.

H304: May be fatal if swallowed and enters airways.

H311: Toxic in contact with skin.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

[cont...]

SAFETY DATA SHEET
BRUSH RESTORER

Page: 9

H319: Causes serious eye irritation.

H331: Toxic if inhaled.

H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H340: May cause genetic defects.

H350: May cause cancer.

H351: Suspected of causing cancer.

H370: Causes damage to organs.

H371: May cause damage to organs.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.