



## SAFETY DATA SHEET

OXYLUBE SPRAY

Page: 1

Compilation date: 23/04/15

Revision No: 1

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

**Product name:** OXYLUBE SPRAY

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Use of substance / mixture:** Dry film lubricant.

#### 1.3. Details of the supplier of the safety data sheet

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

#### 1.4. Emergency telephone number

**Emergency tel:** +44 (0) 113 232 2600

### Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

**Classification under CLP:** Skin Irrit. 2: H315; STOT SE 3: H336; Aquatic Chronic 2: H411; Flam. Aerosol 1: H222; -: H229

**Classification under CHIP:** F: R11; Xi: R38; N: R51/53; -: R67

**Most important adverse effects:** Extremely flammable aerosol. Pressurised container: May burst if heated. Causes skin irritation. May cause drowsiness or dizziness. Toxic to aquatic life with long lasting effects.

#### 2.2. Label elements

**Label elements under CLP:**

**Hazard statements:** H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

H315: Causes skin irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

**Signal words:** Danger

[cont...]

# SAFETY DATA SHEET

## OXYLUBE SPRAY

Page: 2

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark

GHS09: Environmental



**Precautionary statements:** P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P251: Pressurized container: Do not pierce or burn, even after use.

P210: Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P211: Do not spray on an open flame or other ignition source.

P271: Use only outdoors or in a well-ventilated area.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P273: Avoid release to the environment.

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) - REACH registered number(s): EXEMPT

EINECS	CAS	CHIP Classification	CLP Classification	Percent
270-704-2	68476-85-7	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	50-70%

HYDROCARBONS C7-C9, ISOALKANES - REACH registered number(s): 01-2119471305-42-0000

921-728-3	-	-	Flam. Liq. 2: H225; Skin Irrit. 2: H315; Aquatic Chronic 2: H411; STOT SE 3: H336; Asp. Tox. 1: H304	10-30%
-----------	---	---	--	--------

MOLYBDENUM DISULPHIDE

215-263-9	1317-33-5	Substance with a Community workplace exposure limit.	-	2-10%
-----------	-----------	--	---	-------

1-BUTANOL, TITANIUM(4+) SALT (4:1), HOMOPOLYMER

-	9022-96-2	-	Eye Irrit. 2: H319	2-10%
---	-----------	---	--------------------	-------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

[cont...]

# SAFETY DATA SHEET

OXYLUBE SPRAY

Page: 3

## 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. May cause dizziness.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

## 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Do not use water. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Mix with sand or vermiculite. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in cool, well ventilated area. Keep away from direct sunlight.

**Suitable packaging:** Must only be kept in original packaging.

[cont...]

# SAFETY DATA SHEET

OXYLUBE SPRAY

Page: 4

## 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1000ppm 1750mg/m <sup>3</sup>	1250ppm 2180mg/m <sup>3</sup>	-	-

**HYDROCARBONS C7-C9, ISOALKANES**

UK	1400 mg/m <sup>3</sup> RCP TWA	-	-	-
----	--------------------------------	---	---	---

**MOLYBDENUM DISULPHIDE**

UK	-	-	15mg/m <sup>3</sup>	10mg/m <sup>3</sup>
----	---	---	---------------------	---------------------

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Respiratory protection not normally required.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses with side-shields.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Aerosol

**Colour:** Black

**Odour:** Characteristic odour

**Evaporation rate:** Fast

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Not miscible

**Viscosity:** Non-viscous

**Boiling point/range°C:** -26

**Melting point/range°C:** -100

**Flash point°C:** <21

**Autoflammability°C:** >200

**Vapour pressure:** 4270

**Relative density:** <1

### 9.2. Other information

**Other information:** No data available.

[cont...]

# SAFETY DATA SHEET

OXYLUBE SPRAY

Page: 5

## Section 10: Stability and reactivity

### 10.1. Reactivity

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

### 10.4. Conditions to avoid

**Conditions to avoid:** Direct sunlight. Heat.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong reducing agents.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

#### Relevant effects for mixture:

Effect	Route	Basis
Irritation	DRM	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. May cause dizziness.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

## Section 12: Ecological information

### 12.1. Toxicity

#### Hazardous ingredients:

#### HYDROCARBONS C7-C9, ISOALKANES

Daphnia magna	48H EC50	2.4	mg/l
Pseudokirchneriella	72H ErC50	6.3	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H ErC50	18.4	mg/l

### 12.2. Persistence and degradability

**Persistence and degradability:** Only slightly biodegradable.

[cont...]

# SAFETY DATA SHEET

OXYLUBE SPRAY

Page: 6

## 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

## 12.4. Mobility in soil

**Mobility:** Highly volatile. Readily absorbed into soil.

## 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

## 12.6. Other adverse effects

**Other adverse effects:** Toxic to aquatic organisms.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN1950

### 14.2. UN proper shipping name

**Shipping name:** AEROSOLS, ENVIRONMENTALLY HAZARDOUS

### 14.3. Transport hazard class(es)

**Transport class:** 2

### 14.4. Packing group

### 14.5. Environmental hazards

**Environmentally hazardous:** Yes

**Marine pollutant:** No

### 14.6. Special precautions for user

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

[cont...]

# SAFETY DATA SHEET

## OXYLUBE SPRAY

Page: 7

EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

.....  
Compiled in accordance with REACH.

Product label must specify:

CONTAINS SUBSTANCE(S):

HYDROCARBONS C7-C9, ISOALKANES (EINECS 921-728-3)  
.....

**Phrases used in s.2 and s.3:** H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H229: Pressurised container: May burst if heated

H280: Contains gas under pressure; may explode if heated.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

R11: Highly flammable.

R38: Irritating to skin.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R67: Vapours may cause drowsiness and dizziness.

**Legend to abbreviations:** PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

[cont...]

## SAFETY DATA SHEET

OXYLUBE SPRAY

Page: 8

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = physico-chemical properties

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.