

PLASTIC COATING THINNERS

Page: 1

Compilation date: 02/12/2016

**Revision date:** 08/01/2020

**Revision No: 7** 

# Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name: PLASTIC COATING THINNERS

Product code: PCTHT

Synonyms: PLASTIC COATING THINNERS

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

### 1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd

Waterloo Road Cricklewood London NW2 7TX

United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

### 1.4. Emergency telephone number

Emergency tel: .+44(0)2084504666 (Office hours only)

# Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Flam. Liq. 2: H225; Skin Irrit. 2: H315; STOT

SE 3: H335

Most important adverse effects: Highly flammable liquid and vapour. Causes skin irritation. Causes serious eye

irritation. May cause respiratory irritation. Toxic to aquatic life with long lasting effects.

### 2.2. Label elements

### Label elements:

Hazard statements: H225: Highly flammable liquid and vapour.

H315: Causes skin irritation.

H319: Causes serious eye irritation.H335: May cause respiratory irritation.

H411: Toxic to aquatic life with long lasting effects.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark

GHS09: Environmental

[cont...]

### PLASTIC COATING THINNERS

Page: 2







Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition

sources. No smoking.

P241: Use explosion-proof equipment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352: IF ON SKIN: Wash with plenty of water.

P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing.

Flam. Liq. 3: H226; STOT SE 3: H335;

Aquatic Chronic 2: H411

Rinse skin with water.

P362+P364: Take off contaminated clothing and wash it before reuse.

### 2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

# Section 3: Composition/information on ingredients

#### 3.2. Mixtures

### **Hazardous ingredients:**

#### **ETHANOL**

MESITYLENE 203-604-4

108-67-8

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-578-6	64-17-5	Substance with a Community workplace exposure limit.	Flam. Liq. 2: H225	45.130%
1,2,4-TRIMETH	IYLBENZENE			
202-436-9	95-63-6	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Eye Irrit. 2: H319; STOT SE 3: H335; Skin Irrit. 2: H315; Aquatic Chronic 2: H411	23.630%
LOW BOILING	POINT NAPHTH	IA - UNSPECIFIED - SOLVENT NAP	HTHA (PETROLEUM), LIGHT AROM.	
265-199-0	64742-95-6	-	Asp. Tox. 1: H304; Flam. Liq. 3: H226; STOT SE 3: H335; Aquatic Chronic 2: H411	15.753%
XYLENE				
215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	3.938%

3.938%

#### PLASTIC COATING THINNERS

Page: 3

#### **METHANOL**

200-659-6	67-56-1	-	Flam. Liq. 2: H225; Acute Tox. 3: H331;	1.880%
			Acute Tox. 3: H311; Acute Tox. 3: H301;	
			STOT SE 1: H370	

#### Section 4: First aid measures

#### 4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash

immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a

doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may

cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

### Section 5: Fire-fighting measures

#### 5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray

to cool containers.

# 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

#### 5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact

with skin and eyes.

### Section 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from

downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn

leaking containers leak-side up to prevent the escape of liquid.

[cont...]

### PLASTIC COATING THINNERS

Page: 4

### 6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

#### 6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for

disposal by an appropriate method.

#### 6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

### Section 7: Handling and storage

#### 7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

Do not handle in a confined space. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. The floor of the

storage room must be impermeable to prevent the escape of liquids.

Suitable packaging: Do not use plastic containers. Coated steel. Glass.

# 7.3. Specific end use(s)

Specific end use(s): No data available.

### Section 8: Exposure controls/personal protection

# 8.1. Control parameters

### **Hazardous ingredients:**

### **ETHANOL**

### Workplace exposure limits:

### Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1920 mg/m3	-	-	-

#### 1,2,4-TRIMETHYLBENZENE

UK	125 mg/m3	-	-	-
----	-----------	---	---	---

#### **XYLENE**

UK	220 mg/m3	441 mg/m3	-	-
----	-----------	-----------	---	---

# **MESITYLENE**

•	=			
UK	25 ppm	-	-	-

### PLASTIC COATING THINNERS

Page: 5

#### **METHANOL**

UK 266	/m3 333 mg/m3	-	-
--------	---------------	---	---

#### **DNEL/PNEC Values**

**DNEL / PNEC** No data available.

#### 8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. The floor of the storage room must be

impermeable to prevent the escape of liquids.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

# Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

State: Liquid Colour: Clear.

Odour: Alcoholic

**Evaporation rate:** No data available.

Oxidising: No data available.

Solubility in water: Partially miscible.

Also soluble in: Ethanol. Acetone. Methanol.

Viscosity: Non-viscous

**Boiling point/range°C:** 75 **Melting point/range°C:** No data available.

Flammability limits %: lower: No data available. upper: No data available.

Flash point°C: 14 Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available. Vapour pressure: No data available.

Relative density: 0.838 @ 20 C pH: No data available.

VOC g/l: 838

#### 9.2. Other information

Other information: No data available.

#### Section 10: Stability and reactivity

### 10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

Chemical stability: Stable under normal conditions.

### PLASTIC COATING THINNERS

Page: 6

### 10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

Conditions to avoid: Heat.

### 10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

### 10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

# Section 11: Toxicological information

# 11.1. Information on toxicological effects

### **Hazardous ingredients:**

#### **ETHANOL**

IVN	RAT	LD50	1440	mg/kg
ORL	MUS	LD50	3450	mg/kg
ORL	RAT	LD50	7060	mg/kg

# 1,2,4-TRIMETHYLBENZENE

IPR	RAT	LDLO	1752	mg/kg
ORL	RAT	LD50	5	gm/kg

# LOW BOILING POINT NAPHTHA - UNSPECIFIED - SOLVENT NAPHTHA (PETROLEUM), LIGHT AROM.

ORL	RAT	LD50	8400	ma/ka
OIL	100	LDSG	0-100	111g/1kg

### **XYLENE**

ORL	MUS	LD50	2119	mg/kg
ORL	RAT	LD50	4300	mg/kg
SCU	RAT	LD50	1700	mg/kg

#### **MESITYLENE**

IPR	GPG	LDLO	1303	ma/ka
11 13	01 0	LDLO	1000	111g/ Ng

### **METHANOL**

IVN RAT	LD50	2131	mg/kg
---------	------	------	-------

### PLASTIC COATING THINNERS

Page: 7

ORL	MUS	LD50	7300	mg/kg
ORL	RAT	LD50	5628	mg/kg

#### Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may

cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

### Section 12: Ecological information

### 12.1. Toxicity

Ecotoxicity values: No data available.

### 12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

# 12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

# 12.4. Mobility in soil

Mobility: Readily absorbed into soil.

### 12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

### Section 13: Disposal considerations

# 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal

company.

**NB:** The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

### PLASTIC COATING THINNERS

Page: 8

### **Section 14: Transport information**

#### 14.1. UN number

UN number: UN1263

#### 14.2. UN proper shipping name

Shipping name: PAINT

including paint, lacquer, enamel, stain, shellac, varnish, polish, liquid filler and liquid

lacquer base

### 14.3. Transport hazard class(es)

Transport class: 3

### 14.4. Packing group

Packing group: |

#### 14.5. Environmental hazards

Environmentally hazardous: Yes Marine pollutant: Yes

### 14.6. Special precautions for user

Special precautions: No special precautions.

**Tunnel code:** D/E **Transport category:** 1

#### **Section 15: Regulatory information**

# 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

### 15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture

by the supplier.

### **Section 16: Other information**

# Other information

Other information: according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation

(EU) 2015/830

\* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H301: Toxic if swallowed.

H304: May be fatal if swallowed and enters airways.

H311: Toxic in contact with skin. H312: Harmful in contact with skin.

# PLASTIC COATING THINNERS

Page: 9

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H331: Toxic if inhaled.
H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H370: Causes damage to organs.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

and shall be used only as a guide. This company shall not be held liable for any

damage resulting from handling or from contact with the above product.