



**SAFETY DATA SHEET**  
METAL REPAIR COMPOUND

Page: 1

Compilation date: 15/05/2015

Revision date: 03/02/2016

Revision No: 7

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** METAL REPAIR COMPOUND

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Repair compound, filler, putty

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** Aquatic Chronic 3: H412; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317

**Most important adverse effects:** Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation.  
Harmful to aquatic life with long lasting effects.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H412: Harmful to aquatic life with long lasting effects.

**Hazard pictograms:** GHS07: Exclamation mark



[cont...]

# SAFETY DATA SHEET

## METAL REPAIR COMPOUND

Page: 2

**Signal words:** Warning

**Precautionary statements:** P273: Avoid release to the environment.  
P264: Wash hands thoroughly after handling.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P302+352: IF ON SKIN: Wash with plenty of water/.  
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P332+313: If skin irritation occurs: Get medical advice/attention.  
P337+313: If eye irritation persists: Get medical advice/attention.  
P501: Dispose of contents/container to local/national regulations.

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

**Hazardous ingredients:**

EPOXY RESIN (NUMBER AVERAGE MW <=700)

EINECS	CAS	PBT / WEL	CLP Classification	Percent
500-033-5	25068-38-6	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319; Skin Sens. 1: H317; Aquatic Chronic 2: H411	20-50%

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** No data available.

### 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

[cont...]

**SAFETY DATA SHEET**  
METAL REPAIR COMPOUND

Page: 3

**5.1. Extinguishing media**

**Extinguishing media:** Alcohol resistant foam. Dry chemical powder. Carbon dioxide. Do not use water.

**5.2. Special hazards arising from the substance or mixture**

**Exposure hazards:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

**5.3. Advice for fire-fighters**

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

**Section 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

**Personal precautions:** Refer to section 8 of SDS for personal protection details.

**6.2. Environmental precautions**

**Environmental precautions:** Do not discharge into drains or rivers.

**6.3. Methods and material for containment and cleaning up**

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

**6.4. Reference to other sections**

**Reference to other sections:** Refer to section 8 of SDS. Refer to section 13 of SDS.

**Section 7: Handling and storage**

**7.1. Precautions for safe handling**

**Handling requirements:** Avoid direct contact with the substance.

**7.2. Conditions for safe storage, including any incompatibilities**

**Storage conditions:** Store in a cool, well ventilated area. Keep away from direct sunlight.

**Suitable packaging:** Must only be kept in original packaging.

**7.3. Specific end use(s)**

**Specific end use(s):** No data available.

**Section 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Workplace exposure limits:** No data available.

**DNEL/PNEC Values**

**DNEL / PNEC** No data available.

**8.2. Exposure controls**

**Engineering measures:** Not applicable.

[cont...]

**SAFETY DATA SHEET**  
METAL REPAIR COMPOUND

Page: 4

**Respiratory protection:** Respiratory protection not required.  
**Hand protection:** Protective gloves. Nitrile gloves.  
**Eye protection:** Safety glasses with side-shields. Ensure eye bath is to hand.  
**Skin protection:** Protective clothing.  
**Environmental:** No special requirement.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Paste  
**Colour:** Grey  
**Odour:** Barely perceptible odour  
**Evaporation rate:** Negligible  
**Oxidising:** Non-oxidising (by EC criteria)  
**Solubility in water:** Insoluble  
**Viscosity:** Non-viscous  
**Boiling point/range°C:** > 35  
**Flammability limits %:** lower: No data available.  
**Flash point°C:** > 100  
**Autoflammability°C:** No data available.  
**Relative density:** 2.25  
**VOC g/l:** No data available.  
**Melting point/range°C:** No data available.  
**upper:** No data available.  
**Part.coeff. n-octanol/water:** No data available.  
**Vapour pressure:** <500 Pa 50°C  
**pH:** No data available.

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** No data available.

### 10.4. Conditions to avoid

**Conditions to avoid:** Direct sunlight. Heat.

### 10.5. Incompatible materials

**Materials to avoid:** Strong acids. Bases. Amines.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

[cont...]

**SAFETY DATA SHEET**  
METAL REPAIR COMPOUND

Page: 5

**Section 11: Toxicological information**

**11.1. Information on toxicological effects**

**Toxicity values:**

Route	Species	Test	Value	Units
ORAL	RAT	LD50	11400	mg/kg

**Relevant hazards for product:**

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated

**Symptoms / routes of exposure**

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** No data available.

**Section 12: Ecological information**

**12.1. Toxicity**

**Ecotoxicity values:**

Species	Test	Value	Units
RAINBOW TROUT ( <i>Oncorhynchus mykiss</i> )	96H LC50	2	mg/l
Daphnia magna	48H EC50	1.8	mg/l
ALGAE	72H ErC50	11	mg/l

**12.2. Persistence and degradability**

**Persistence and degradability:** Not biodegradable.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** No data available.

**12.4. Mobility in soil**

**Mobility:** Non-volatile. Insoluble in water. Absorbed only slowly into soil.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

[cont...]

**SAFETY DATA SHEET**  
METAL REPAIR COMPOUND

Page: 6

**12.6. Other adverse effects**

**Other adverse effects:** No data available.

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information**

**Transport class:** This product does not require a classification for transport.

**Section 15: Regulatory information**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**Specific regulations:** No data available

**15.2. Chemical Safety Assessment**

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

**Section 16: Other information**

**Other information**

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

**Phrases used in s.2 and s.3:** H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.