

SAFETY DATA SHEET

according to Regulation (EU) 2015/830

Page 1/5

QSW-NC600-SN100 Solder Wire

Revision 7
Revision date 2021-02-02

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	QSW-NC600-SN100 Solder Wire
Other means of identification	UFI NO.G8YK-8QR7-V10G-HTCV.

1.2. Relevant identified uses of the substance or mixture and uses advised against

Description	Soldering.
-------------	------------

1.3. Details of the supplier of the safety data sheet

Company	Qualitek Europe Ltd
Address	Unit 9 Apex Court Bassendale Road Bromborough Wirral CH62 3RE
Web	www.qualitek.com
Telephone	+ 44(0)151 334 0888
Fax	+ 44(0)151 334 1408
Email address of the competent person	sales@qualitek-europe.com

1.4. Emergency telephone number


Emergency telephone number	+ 44(0)151 334 0888 9.00 am - 5.00 pm Mon -Fri
----------------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

2.1.2. Classification - EC 1272/2008	Skin Sens. 1: H317;
--------------------------------------	---------------------

2.2. Label elements

Hazard pictograms	
Signal Word	Warning
Hazard Statement	Skin Sens. 1: H317 - May cause an allergic skin reaction.
Precautionary Statement: Prevention	P261 - Avoid breathing dust/fume/gas/mist/vapours/spray. P280 - Wear protective gloves/protective clothing/eye protection/face protection.
Precautionary Statement: Response	P302+P352 - IF ON SKIN: Wash with plenty of water/ . P333+P313 - If skin irritation or rash occurs: Get medical advice/attention.
Precautionary Statement: Disposal	Dispose of in compliance with all local and national regulations

QSW-NC600-SN100 Solder Wire

Revision 7

Revision date 2021-02-02

Further information

CAUTION CONTAINS ROSIN: Exposure to this material may cause certain sensitive individuals to develop eczema and/or asthma. Sensitised persons may subsequently show asthmatic symptoms when exposed to atmospheric concentrations well below the OEL. Persons with a history of asthma allergies or chronic or recurrent respiratory disease should not be employed in any process in which this product is used.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Tin		7440-31-5	231-141-8	01-2119486474-28	95 - 100%	
Natural Rosin (Mod Rosin)		65997-05-9	500-163-2	01-2119960933-37	1 - 5%	Skin Sens. 1: H317;
Copper (Copper dusts and mists (as Cu))					0-1%	Acute Tox. 4: H302; Skin Irrit. 2: H315; STOT SE 3: H335;

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Irritating to respiratory system. Inhalation may cause coughing, tightness of the chest and irritation of the respiratory system. Move the exposed person to fresh air. Seek medical attention.
Eye contact	Irritating to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	Irritating to skin. Wash off immediately with plenty of soap and water. Seek medical attention if irritation or symptoms persist.
Ingestion	DO NOT INDUCE VOMITING. Seek medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	Inhalation may cause coughing, tightness of the chest and irritation of the respiratory system. Prolonged or repeated exposure may cause: Sensitization.
Eye contact	Prolonged or repeated exposure may cause: Irritating to eyes.
Skin contact	Prolonged or repeated exposure may cause: Skin irritation and dermatitis.

SECTION 5: Firefighting measures

5.1. Extinguishing media

	Carbon oxides.
--	----------------

5.2. Special hazards arising from the substance or mixture

	Burning produces irritating, toxic and obnoxious fumes.
--	---

5.3. Advice for firefighters

	Wear suitable respiratory equipment when necessary.
--	---

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

	Ensure adequate ventilation of the working area. Wear suitable protective equipment.
--	--

6.2. Environmental precautions

	No precautions required to be mentioned.
--	--

6.3. Methods and material for containment and cleaning up

	Sweep up. Transfer to suitable, labelled containers for disposal.
--	---

SECTION 7: Handling and storage

QSW-NC600-SN100 Solder Wire

Revision 7

Revision date 2021-02-02

7.1. Precautions for safe handling

Avoid contact with eyes and skin. Ensure adequate ventilation of the working area. Adopt best Manual Handling considerations when handling, carrying and dispensing.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated area. Keep containers tightly closed. Store in correctly labelled containers.

7.3. Specific end use(s)

Soldering.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1. Exposure Limit Values

Copper (Copper dusts and mists (as Cu))	WEL 8-hr limit ppm: -	WEL 8-hr limit mg/m3: 1
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: 2
	WEL 8-hr limit mg/m3 total inhalable dust: -	WEL 15 min limit mg/m3 total inhalable dust: -
	WEL 8-hr limit mg/m3 total respirable dust: -	WEL 15 min limit mg/m3 total respirable dust: -
Natural Rosin (Mod Rosin)	WEL 8-hr limit ppm:	WEL 8-hr limit mg/m3: 0.05
	WEL 15 min limit ppm:	WEL 15 min limit mg/m3:
	WEL 8-hr limit mg/m3 total inhalable dust: 0.15	WEL 15 min limit mg/m3 total inhalable dust:
	WEL 8-hr limit mg/m3 total respirable dust:	WEL 15 min limit mg/m3 total respirable dust:

8.2. Exposure controls

8.2.1. Appropriate engineering controls	Ensure adequate ventilation of the working area.
8.2.2. Individual protection measures	Wear chemical protective clothing.
Eye / face protection	Approved safety goggles.
Skin protection - Handprotection	Chemical resistant gloves (PVC).
Respiratory protection	In case of insufficient ventilation, wear suitable respiratory equipment.
8.2.3. Environmental exposure controls	Not normally required.
Occupational exposure controls	Appropriate local exhaust ventilation is required.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Solid
Colour	Dark grey
Odour	Characteristic
Melting point	227 °C
Flash point	> 115 °C
Autoignition temperature	> 226 °C
Solubility	Slightly soluble in water

SECTION 10: Stability and reactivity

QSW-NC600-SN100 Solder Wire

Revision 7
Revision date 2021-02-02

10.1. Reactivity

No data available.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

None.

10.4. Conditions to avoid

None.

10.5. Incompatible materials

Avoid contact with: Acids. Oxidising agents.

10.6. Hazardous decomposition products

aliphatic hydrocarbons. Acids. may be formed in fire conditions.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	No Significant Hazard.
Skin corrosion/irritation	Irritating to eyes.
Respiratory or skin sensitisation	May cause sensitisation by inhalation and skin contact.
Germ cell mutagenicity	No mutagenic effects reported.
Carcinogenicity	No carcinogenic effects reported.
Reproductive toxicity	No Significant Hazard.

SECTION 12: Ecological information

12.2. Persistence and degradability

Not readily biodegradable.

12.3. Bioaccumulative potential

Does not bioaccumulate.

12.4. Mobility in soil

No data is available on this product.

SECTION 13: Disposal considerations

General information

Dispose of in compliance with all local and national regulations.

SECTION 14: Transport information

14.1. UN number

The product is not classified as dangerous for carriage.

14.2. UN proper shipping name

The product is not classified as dangerous for carriage.

14.3. Transport hazard class(es)

The product is not classified as dangerous for carriage.

14.4. Packing group

The product is not classified as dangerous for carriage.

14.5. Environmental hazards

QSW-NC600-SN100 Solder Wire

Revision 7

Revision date 2021-02-02

14.5. Environmental hazards

	The product is not classified as dangerous for carriage.
--	--

14.6. Special precautions for user

	The product is not classified as dangerous for carriage.
--	--

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

	The product is not classified as dangerous for carriage.
--	--

Further information

	The product is not classified as dangerous for carriage.
--	--

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****Regulations**

	REGULATION (EC) No 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC.
--	---

SECTION 16: Other information**Other information****Revision**

	This document differs from the previous version in the following areas: 1 - Other means of identification.
--	---

Text of Hazard Statements in Section 3

	Skin Sens. 1: H317 - May cause an allergic skin reaction. Acute Tox. 4: H302 - Harmful if swallowed. Skin Irrit. 2: H315 - Causes skin irritation. STOT SE 3: H335 - May cause respiratory irritation.
--	---

Further information

	The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.
--	--