



**QQGQ2.E201955
Power Supplies, Information Technology Equipment Including Electrical Business
Equipment - Component**

Page Bottom

**Power Supplies, Information Technology Equipment Including Electrical Business
Equipment - Component**

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

UNIFIVE TECHNOLOGY CO LTD

E201955

4TH FL
269 SIANGYANG RD
FENG YUAN DISTRICT
TAICHUNG, 420 TAIWAN

Model No.	Rated Input		SC	Max Output			OC	SP	EP	FC	GC
	Volts	Hz		V	A	VA					
SOC112-0320[*r]											
	100-120ac	50/60	0	3	2	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-0520[*r]											
	100-120ac	50/60	0	5	2	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-0523[*r]											
	100-120ac	50/60	0	5	2.3	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-0620[*r]											
	100-120ac	50/60	0	6	2	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-0714[*r]											
	100-120ac	50/60	0	7	1.4	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-0716[*r]											
	100-120ac	50/60	0	7	1.6	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-0810[*r]											
	100-120ac	50/60	0	8	1	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-0913[*r]											
	100-120ac	50/60	0	9	1.3	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-1011[*r]											
	100-120ac	50/60	0	10	1.1	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-1208[*r]											
	100-120ac	50/60	0	12	0.8	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-1210[*r]											
	100-120ac	50/60	0	12	1	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-1508[*r]											
	100-120ac	50/60	0	15	0.8	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-2405[*r]											
	100-120ac	50/60	0	24	0.5	-	3	60950-1, 2nd	20B	2, 6	1
SOC112-3320[*r]											
	100-120ac	50/60	0	3.3	2	-	3	60950-1, 2nd	20B	2, 6	1

				12	1.5	-	3					
UOB125D-0512-D[*r]												
	100-120ac	50/60	0	5	2	-	3	60950-1	20B	8	2	
				12	1	-	3					
UOB305-3320												
	100-240ac	-	0	3.406	4.8	10.9972	3	60950-1	20B	2,6	2	
UOB310-0320												
	100-240ac	50/60	0	3.10	3.5	10.15	3	60950-1, 2nd	20B	0	0	
UOB310-0520												
	100-240ac	50/60	0	5.11	3.7	18.20	3	60950-1, 2nd	20B	0	0	
UOB310-0911[*r]												
	100-240ac	50/60	0	9.0	1.1	-	3	60950-1, 2nd	20B	0	0	
UOB310-1210												
	100-240ac	50/60	0	12.33	1.9	23.31	3	60950-1, 2nd	20B	0	0	
UOB310-1507[*r]												
	100-240ac	50/60	0	15	0.7	-	3	60950-1, 2nd	20B	0	0	
UOB310-1806[*r]												
	100-240ac	50/60	0	18	0.6	-	3	60950-1, 2nd	20B	0	0	
UOB310-2405												
	100-240ac	50/60	0	24.03	0.9	21.6	3	60950-1, 2nd	20B	0	0	
UOB310-3320[*r]												
	100-240ac	50/60	0	3.3	2	-	3	60950-1, 2nd	20B	0	0	
UOB310-7513[*r]												
	100-240ac	50/60	0	7.5	1.3	-	3	60950-1, 2nd	20B	0	0	
UOB315-1212[*r]												
	100-240ac	50/60	0	12	1.25	15	3	60950-1	20B	8	2	
UOB318-0530[*r]												
	100-240ac	50/60	0	5	3	15	3	60950-1	20B	8	2	
UOB318-1215												
	100-240ac	50/60	0	12.08	2.3	27.48	3	60950-1	20B	8	2	
UOB318-3330[*r]												
	100-240ac	50/60	0	3.3	3	9.9	3	60950-1	20B	8	2	
UOB325D-0512-A[*r]												
	100-240ac	50/60	0	5	1.5	-	3	60950-1	20B	0	2	
				12	1.5	-	3					
UOB325D-0512-B[*r]												
	100-240ac	50/60	0	5	1.5	-	3	60950-1	20B	0	2	
				12	1	-	3					
UOB325D-0512-C												
	100-240ac	50/60	0	5.09	4.5	20.65	3	60950-1	20B	0	2	
				11.74	4.8	54.48	3					
UOB325D-0512-D[*r]												
	100-240ac	50/60	0	5	2	-	3	60950-1	20B	0	2	
				12	1	-	3					

100-240ac	50/60	0	15	1	-	3	60950-1, 2nd	20B	2, 6	1
VOC315A-2465[*r]										
100-240ac	50/60	0	24	0.65	-	3	60950-1, 2nd	20B	2, 6	1
VOC315A-3325[*r]										
100-240ac	50/60	0	3.3	2.5	-	3	60950-1, 2nd	20B	2, 6	1
VOC315A-4803[*r]										
100-240ac	50/60	0	48	0.3	-	3	60950-1, 2nd	20B	2, 6	1
VOC315A-7520[*r]										
100-240ac	50/60	0	7.5	2	-	3	60950-1, 2nd	20B	2, 6	1
VOC318A-0330										
100-240ac	50/60	0	3	3	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-0526										
100-240ac	50/60	0	5	2.6	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-0530										
100-240ac	50/60	0	5	3	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-0628										
100-240ac	50/60	0	6	2.8	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-0725										
100-240ac	50/60	0	7	2.5	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-0920										
100-240ac	50/60	0	9	2	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-1018										
100-240ac	50/60	0	10	1.8	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-1215										
100-240ac	50/60	0	12	1.25	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-1512										
100-240ac	50/60	0	15	1.2	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-2475										
100-240ac	50/60	0	24	0.75	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-3330										
100-240ac	50/60	0	3.3	3	-	-	60950-1, 2nd	20B	2, 6	1
VOC318A-4804										
100-240ac	50/60	0	48	0.4	-	-	60950-1, 2nd	20B	2, 6	1

[*r] - Output values are rated.

% - Where x may be B or C; y may be 0 thru 9, A thru Z or blank; z may be A, B, C or D

y - 0 thru 9, A thru Z or blank

z - A, B, C or D

Marking: Company name and model designation.

Last Updated on 2011-01-07



QQGQ8.E201955
Power Supplies, Information Technology Equipment Including Electrical Business
Equipment Certified for Canada - Component

Page Bottom

Power Supplies, Information Technology Equipment Including Electrical Business
Equipment Certified for Canada - Component

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment Certified for Canada - Component

UNIFIVE TECHNOLOGY CO LTD

E201955

4TH FL
 269 SIANGYANG RD
 FENG YUAN DISTRICT
 TAICHUNG, 420 TAIWAN

Model No.	Rated Input			Max Output				OC	SP	EP	FC	GC
	Volts	Hz	SC	V	A	VA						
SOC112-0320[*r]												
	100-120ac	50/60	0	3	2	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-0520[*r]												
	100-120ac	50/60	0	5	2	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-0523[*r]												
	100-120ac	50/60	0	5	2.3	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-0620[*r]												
	100-120ac	50/60	0	6	2	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-0714[*r]												
	100-120ac	50/60	0	7	1.4	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-0716[*r]												
	100-120ac	50/60	0	7	1.6	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-0810[*r]												
	100-120ac	50/60	0	8	1	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-0913[*r]												
	100-120ac	50/60	0	9	1.3	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-1011[*r]												
	100-120ac	50/60	0	10	1.1	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-1208[*r]												
	100-120ac	50/60	0	12	0.8	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-1210[*r]												
	100-120ac	50/60	0	12	1	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-1508[*r]												
	100-120ac	50/60	0	15	0.8	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-2405[*r]												
	100-120ac	50/60	0	24	0.5	-	3	60950-1, 2nd	20B	2, 6	1	
SOC112-3320[*r]												

100-120ac	50/60	0	5	2	-	3	60950-1	20B	8	2
			12	1.5	-	3				

UOB125D-0512-D[*r]

100-120ac	50/60	0	5	2	-	3	60950-1	20B	8	2
			12	1	-	3				

UOB305-3320

100-240ac	-	0	3.406	4.8	10.9972	3	60950-1	20B	2,6	2
-----------	---	---	-------	-----	---------	---	---------	-----	-----	---

UOB310-0320

100-240ac	50/60	0	3.10	3.5	10.15	3	60950-1, 2nd	20B	0	0
-----------	-------	---	------	-----	-------	---	--------------	-----	---	---

UOB310-0520

100-240ac	50/60	0	5.11	3.7	18.20	3	60950-1, 2nd	20B	0	0
-----------	-------	---	------	-----	-------	---	--------------	-----	---	---

UOB310-0911[*r]

100-240ac	50/60	0	9.0	1.1	-	3	60950-1, 2nd	20B	0	0
-----------	-------	---	-----	-----	---	---	--------------	-----	---	---

UOB310-1210

100-240ac	50/60	0	12.33	1.9	23.31	3	60950-1, 2nd	20B	0	0
-----------	-------	---	-------	-----	-------	---	--------------	-----	---	---

UOB310-1507[*r]

100-240ac	50/60	0	15	0.7	-	3	60950-1, 2nd	20B	0	0
-----------	-------	---	----	-----	---	---	--------------	-----	---	---

UOB310-1806[*r]

100-240ac	50/60	0	18	0.6	-	3	60950-1, 2nd	20B	0	0
-----------	-------	---	----	-----	---	---	--------------	-----	---	---

UOB310-2405

100-240ac	50/60	0	24.03	0.9	21.6	3	60950-1, 2nd	20B	0	0
-----------	-------	---	-------	-----	------	---	--------------	-----	---	---

UOB310-3320[*r]

100-240ac	50/60	0	3.3	2	-	3	60950-1, 2nd	20B	0	0
-----------	-------	---	-----	---	---	---	--------------	-----	---	---

UOB310-7513[*r]

100-240ac	50/60	0	7.5	1.3	-	3	60950-1, 2nd	20B	0	0
-----------	-------	---	-----	-----	---	---	--------------	-----	---	---

UOB315-1212[*r]

100-240ac	50/60	0	12	1.25	15	3	60950-1	20B	8	2
-----------	-------	---	----	------	----	---	---------	-----	---	---

UOB318-0530[*r]

100-240ac	50/60	0	5	3	15	3	60950-1	20B	8	2
-----------	-------	---	---	---	----	---	---------	-----	---	---

UOB318-1215

100-240ac	50/60	0	12.08	2.3	27.48	3	60950-1	20B	8	2
-----------	-------	---	-------	-----	-------	---	---------	-----	---	---

UOB318-3330[*r]

100-240ac	50/60	0	3.3	3	9.9	3	60950-1	20B	8	2
-----------	-------	---	-----	---	-----	---	---------	-----	---	---

UOB325D-0512-A[*r]

100-240ac	50/60	0	5	1.5	-	3	60950-1	20B	0	2
			12	1.5	-	3				

UOB325D-0512-B[*r]

100-240ac	50/60	0	5	1.5	-	3	60950-1	20B	0	2
			12	1	-	3				

UOB325D-0512-C

100-240ac	50/60	0	5.09	4.5	20.65	3	60950-1	20B	0	2
			11.74	4.8	54.48	3				

UOB325D-0512-D[*r]

100-240ac	50/60	0	5	2	-	3	60950-1	20B	0	2
-----------	-------	---	---	---	---	---	---------	-----	---	---

VOC315A-1510[*r]											
100-240ac	50/60	0	15	1	-	3	60950-1, 2nd	20B	2, 6	1	
VOC315A-2465[*r]											
100-240ac	50/60	0	24	0.65	-	3	60950-1, 2nd	20B	2, 6	1	
VOC315A-3325[*r]											
100-240ac	50/60	0	3.3	2.5	-	3	60950-1, 2nd	20B	2, 6	1	
VOC315A-4803[*r]											
100-240ac	50/60	0	48	0.3	-	3	60950-1, 2nd	20B	2, 6	1	
VOC315A-7520[*r]											
100-240ac	50/60	0	7.5	2	-	3	60950-1, 2nd	20B	2, 6	1	
VOC318A-0330											
100-240ac	50/60	0	3	3	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-0526											
100-240ac	50/60	0	5	2.6	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-0530											
100-240ac	50/60	0	5	3	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-0628											
100-240ac	50/60	0	6	2.8	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-0725											
100-240ac	50/60	0	7	2.5	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-0920											
100-240ac	50/60	0	9	2	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-1018											
100-240ac	50/60	0	10	1.8	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-1215											
100-240ac	50/60	0	12	1.25	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-1512											
100-240ac	50/60	0	15	1.2	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-2475											
100-240ac	50/60	0	24	0.75	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-3330											
100-240ac	50/60	0	3.3	3	-	-	60950-1, 2nd	20B	2, 6	1	
VOC318A-4804											
100-240ac	50/60	0	48	0.4	-	-	60950-1, 2nd	20B	2, 6	1	

[*r] - Output values are rated.

% - Where x may be B or C; y may be 0 thru 9, A thru Z or blank; z may be A, B, C or D

y - 0 thru 9, A thru Z or blank

z - A, B, C or D



Marking: Company name, model designation and Recognized Component Mark for Canada, Last Updated on 2011-01-07