



SAFETY DATA SHEET Janitol Altrans

According to Regulation (EU) No 453/2010

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name Janitol Altrans
Product No. ALT60W, ALT764

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Acidic Cleaner

1.3. Details of the supplier of the safety data sheet

Supplier Deb Ltd
Denby Hall Way
Denby
Derbyshire
DE5 8JZ
Main Tel. 01773 855100
Technical Tel 01773 855105
reach@deb.co.uk

1.4. Emergency telephone number

National Poisons Information Service (UK) 0844 8920111

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) C;R34.

Environment

The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

2.2. Label elements

Contains PHOSPHORIC ACID 29.5800%

Detergent Labelling < 5% non-ionic surfactants

Labelling



Corrosive

Risk Phrases

R34 Causes burns.

Safety Phrases

S24/25 Avoid contact with skin and eyes.
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S27/28 After contact with skin, take off immediately all contaminated clothing, and wash immediately with plenty of water.
S36/37/39 Wear suitable protective clothing, gloves and eye/face protection.
S45 In case of accident or if you feel unwell, seek medical advice immediately (show label where possible).
S56 Dispose of this material and its container to hazardous or special waste collection point.

Janitol Altrans

S64

If swallowed, rinse mouth with water (only if the person is conscious).

S1/2

Keep locked up and out of the reach of children.

2.3. Other hazards

None.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS**3.2. Mixtures**

PHOSPHORIC ACID ...%	20-30%
CAS-No.: 7664-38-2	EC No.: 231-633-2
Classification (EC 1272/2008) Skin Corr. 1B - H314	Classification (67/548/EEC) C;R34
CITRIC ACID	1-5%
CAS-No.: 77-92-9	EC No.:
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 STOT SE 3 - H335	Classification (67/548/EEC) Xi;R36/37/38.
ISOTRIDECANOL ETHOXYLATED(>5-20 EO)	1-5%
CAS-No.: 69011-36-5	EC No.:
Classification (EC 1272/2008) Acute Tox. 4 - H302 Eye Dam. 1 - H318	Classification (67/548/EEC) Xn;R22. Xi;R41.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: FIRST AID MEASURES**4.1. Description of first aid measures****Inhalation**

In case of inhalation of spray mist: Move person into fresh air and keep at rest. Get medical attention if any discomfort continues.

Ingestion

NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Rinse mouth thoroughly. Get medical attention immediately!

Skin contact

Remove affected person from source of contamination. Remove contaminated clothing. Wash the skin immediately with soap and water. Get medical attention promptly if symptoms occur after washing.

Eye contact

Remove victim immediately from source of exposure. Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Get medical attention immediately. Continue to rinse.

4.2. Most important symptoms and effects, both acute and delayed**Inhalation**

This is unlikely to occur but symptoms similar to those of ingestion may develop.

Ingestion

May cause chemical burns in mouth and throat. May cause stomach pain or vomiting.

Skin contact

May cause serious chemical burns to the skin.

Janitol Altrans

Eye contact

May cause blurred vision and serious eye damage.

4.3. Indication of any immediate medical attention and special treatment needed

No specific first aid measures noted.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

None known.

5.3. Advice for firefighters

Special Fire Fighting Procedures

No specific fire fighting procedure given.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Do not allow ANY environmental contamination.

6.3. Methods and material for containment and cleaning up

DO NOT TOUCH SPILLED MATERIAL! Stop leak if possible without risk. Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area.

6.4. Reference to other sections

For personal protection, see section 8.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid spilling, skin and eye contact.

7.2. Conditions for safe storage, including any incompatibilities

Store in closed original container at temperatures between 0°C and 40°C.

Storage Class

Corrosive storage.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
PHOSPHORIC ACID ...%	WEL		1 mg/m ³		2 mg/m ³	

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

8.2. Exposure controls

Janitol Altrans

Protective equipment



Process conditions

Provide eyewash, quick drench.

Engineering measures

Observe occupational exposure limits and minimize the risk of inhalation of vapours.

Respiratory equipment

No specific recommendation made, but respiratory protection may still be required under exceptional circumstances when excessive air contamination exists.

Hand protection

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

Eye protection

If risk of splashing, wear safety goggles or face shield.

Other Protection

Wear appropriate clothing to prevent any possibility of skin contact.

Hygiene measures

Wash promptly if skin becomes wet or contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Pink. Purple.
Odour	Characteristic.
Solubility	Soluble in water.
Initial boiling point and boiling range (°C)	
Not determined.	
Melting point (°C)	
Not determined.	
Relative density	1.151-1.171 25
Vapour density (air=1)	
Not determined.	
Evaporation rate	
Not determined.	
pH-Value, Conc. Solution	
Not determined.	
Viscosity	
Not determined.	
Decomposition temperature (°C)	
Not determined.	
Odour Threshold, Lower	
Not determined.	
Odour Threshold, Upper	
Not determined.	
Flash point (°C)	
Not applicable.	
Auto Ignition Temperature (°C)	
Not applicable.	
Flammability Limit - Lower(%)	
Not applicable.	
Flammability Limit - Upper(%)	
Not applicable.	

Janitol Altrans

Partition Coefficient**(N-Octanol/Water)**

Not determined.

Explosive properties

Not applicable.

Oxidising properties

Does not meet the criteria for oxidising.

9.2. Other information

None.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

Will react violently with: Alkalis.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not known.

10.4. Conditions to avoid

Avoid excessive heat for prolonged periods of time. Avoid contact with: Strong alkalis. Oxidising materials.

10.5. Incompatible materials**Materials To Avoid**

Bases, alkalis (inorganic). Bases, alkalis (organic).

10.6. Hazardous decomposition productsFire creates: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects**Acute toxicity:**

Based on available data the classification criteria are not met.

Skin Corrosion/Irritation:

Corrosive to skin.

Serious eye damage/irritation:

Skin corrosive; corrosivity to eyes is assumed. No testing is needed.

Respiratory or skin sensitisation:

Based on available data the classification criteria are not met.

Germ cell mutagenicity:

Does not contain any substances known to be mutagenic.

Carcinogenicity:

Does not contain any substances known to be carcinogenic.

Reproductive Toxicity:

Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure:**STOT - Single exposure**

No information available.

Specific target organ toxicity - repeated exposure:

Janitol Altrans

STOT - Repeated exposure

No information available.

Aspiration hazard:

Based on available data the classification criteria are not met.

Inhalation

May cause damage to mucous membranes in nose, throat, lungs and bronchial system.

Ingestion

May cause burns in mucous membranes, throat, oesophagus and stomach.

Skin contact

May cause serious chemical burns to the skin.

Eye contact

Causes burns.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

The product may affect the acidity (pH-factor) in water with risk of harmful effects to aquatic organisms.

12.1. Toxicity

Acute Fish Toxicity

The product may affect the acidity (pH-factor) in water with risk of harmful effects to aquatic organisms.

12.2. Persistence and degradability

Degradability

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

Partition coefficient

Not determined.

12.4. Mobility in soil

Mobility:

Mobile.

12.5. Results of PBT and vPvB assessment

Not Classified as PBT/vPvB by current EU criteria.

12.6. Other adverse effects

None known.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

When handling waste, consideration should be made to the safety precautions applying to handling of the product. Waste to be treated as controlled waste. Disposal to licensed waste disposal site in accordance with local Waste Disposal Authority.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements. Residues and empty containers should be taken care of as hazardous waste according to local and national provisions. Recover and reclaim or recycle, if practical.

SECTION 14: TRANSPORT INFORMATION

14.1. UN number

UN No. (ADR/RID/ADN)

1760

Janitol Altrans

UN No. (IMDG) 1760

UN No. (ICAO) 1760

14.2. UN proper shipping name

Proper Shipping Name CORROSIVE LIQUID, N.O.S. (CONTAINS PHOSPHORIC ACID, CITRIC ACID)

14.3. Transport hazard class(es)

ADR/RID/ADN Class 8
 ADR/RID/ADN Class Class 8: Corrosive substances.
 ADR Label No. 8
 IMDG Class 8
 ICAO Class/Division 8
 Transport Labels



14.4. Packing group

ADR/RID/ADN Packing group III
 IMDG Packing group III
 ICAO Packing group III

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant
 No.

14.6. Special precautions for user

EMS F-A, S-B
 Emergency Action Code 2X
 Hazard No. (ADR) 80
 Tunnel Restriction Code (E)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not relevant

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU Legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work. Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments. Commission Directive 91/322/EEC of 29 May 1991 on establishing indicative limit values by implementing Council Directive 80/1107/EEC on the protection of workers from the risks related to exposure to chemical, physical and biological agents at work.

Janitol Altrans

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

General information

Only trained personnel should use this material.

Revision Comments

Revision of information

Revision Date 13/09/2011

Revision 1

Risk Phrases In Full

R34	Causes burns.
R22	Harmful if swallowed.
R36/37/38	Irritating to eyes, respiratory system and skin.
R41	Risk of serious damage to eyes.

Hazard Statements In Full

H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.

Notes for Risk Phrases and Hazard Statements in Full

The full text for Risk Phrases and Hazard Statements in section 16 relates to the reference numbers in sections 2 and 3 and not necessarily the finished product classification.