

# SAFETY DATA SHEET

#### **Janitol Plus**

According to Regulation (EC) No 1907/2006, Annex II, as amended.

#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name Janitol Plus

**Product number** JNP604, JNP76B, JNP84A, SHD5SFX, 5605, 5625, 5699

# 1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Detergent. For full details regarding recommended uses please refer to the product label.

#### 1.3. Details of the supplier of the safety data sheet

Supplier SC Johnson Professional Ltd

Denby Hall Way

Denby Derbyshire DE5 8JZ

+44 (0) 1773 855100 info.prouk@scj.com

# 1.4. Emergency telephone number

Emergency telephone National Poisons Information Service (UK) 0344 8920111 (Health Professionals only)

National Poisons Information Centre (Eire) 01-8092566/8379964

# SECTION 2: Hazards identification

# 2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

**Health hazards** Skin Irrit. 2 - H315 Eye Dam. 1 - H318

Environmental hazards Not Classified

#### 2.2. Label elements

# Hazard pictograms



Signal word Danger

Hazard statements H315 Causes skin irritation.

H318 Causes serious eye damage.

**Precautionary statements** P264 Wash contaminated skin thoroughly after handling.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

P302+P352 IF ON SKIN: Wash with plenty of water.

P332+P313 If skin irritation occurs: Get medical advice/ attention.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing. P337+P313 If eye irritation persists: Get medical advice/ attention.

Contains TETRAPOTASSIUM PYROPHOSPHATE, 2-AMINOETHANOL, BENZENE SULPHONIC

ACID, C10-13-ALKYL DERIVS., SODIUM SALTS, SODIUM XYLENE SULPHONATE,

ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO

**Detergent labelling** 5 - < 15% anionic surfactants, 5 - < 15% phosphates, < 5% non-ionic surfactants

Supplementary precautionary

P362+P364 Take off contaminated clothing and wash it before reuse.

statements P401 Store in accordance with national regulations.

P501 Dispose of contents/ container in accordance with national regulations.

### 2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

# SECTION 3: Composition/information on ingredients

# 3.2. Mixtures

TETRAPOTASSIUM PYROPHOSPHATE	1-10%

CAS number: 7320-34-5 EC number: 230-785-7 REACH registration number: 01-

2119489369-18-xxxx

Classification

Eve Irrit. 2 - H319

2-AMINOFTHANOI	4 0%

CAS number: 141-43-5 EC number: 205-483-3 REACH registration number: 01-

2119486455-28

Classification

Acute Tox. 4 - H302

Acute Tox. 4 - H312

Acute Tox. 4 - H332

Skin Corr. 1B - H314

Eye Dam. 1 - H318

STOT SE 3 - H335

Aquatic Chronic 3 - H412

#### **Janitol Plus**

BENZENE SULPHONIC ACID , C10-13-ALKYL DERIVS.,

1-10%

**SODIUM SALTS** 

CAS number: 68411-30-3 EC number: 270-115-0

REACH registration number: 01-

2119489428-22-XXXX

Classification

Acute Tox. 4 - H302 Skin Irrit. 2 - H315 Eye Dam. 1 - H318 Aquatic Chronic 3 - H412

SODIUM XYLENE SULPHONATE

1-10%

CAS number: 1300-72-7 EC number: 215-090-9 REACH registration number: 01-

2119513350-56-XXXX

Classification

Eye Irrit. 2 - H319

ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO

1-10%

CAS number: 69011-36-5 EC number: 931-138-8 REACH registration number: 01-

2119976362-32-XXXX

Classification

Skin Irrit. 2 - H315 Eye Dam. 1 - H318 Aquatic Chronic 3 - H412

The full text for all hazard statements is displayed in Section 16.

# SECTION 4: First aid measures

# 4.1. Description of first aid measures

**Inhalation** Move affected person to fresh air at once. Get medical attention if any discomfort continues.

**Ingestion** Never give anything by mouth to an unconscious person. Do not induce vomiting. Rinse

mouth thoroughly with water. Get medical attention.

Skin contact Remove contaminated clothing. Wash skin thoroughly with soap and water. Get medical

attention if irritation persists after washing.

**Eye contact** Remove affected person from source of contamination. Remove any contact lenses and open

eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention.

# 4.2. Most important symptoms and effects, both acute and delayed

**Inhalation** Irritation of nose, throat and airway.

Ingestion May cause discomfort if swallowed. May cause stomach pain or vomiting.

**Skin contact** Skin irritation.

Eye contact The product is strongly irritating to eyes and skin. May cause serious eye damage.

#### 4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor 
No specific recommendations. If in doubt, get medical attention promptly.

#### SECTION 5: Firefighting measures

# 5.1. Extinguishing media

Suitable extinguishing media The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire.

#### 5.2. Special hazards arising from the substance or mixture

Hazardous combustion

Does not decompose when used and stored as recommended.

products

5.3. Advice for firefighters

**Protective actions during** No specific firefighting precautions known.

firefighting

#### SECTION 6: Accidental release measures

# 6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet.

#### 6.2. Environmental precautions

**Environmental precautions**Collect and dispose of spillage as indicated in Section 13. Avoid discharge to the aquatic

environment.

#### 6.3. Methods and material for containment and cleaning up

**Methods for cleaning up**Stop leak if safe to do so. Absorb in vermiculite, dry sand or earth and place into containers.

Flush contaminated area with plenty of water. Avoid contamination of ponds or watercourses

with washing down water.

#### 6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see Section 13.

# SECTION 7: Handling and storage

# 7.1. Precautions for safe handling

**Usage precautions**Wear appropriate clothing to prevent skin contamination. Avoid contact with skin and eyes.

Avoid spilling.

#### 7.2. Conditions for safe storage, including any incompatibilities

**Storage precautions** Store at temperatures between 0°C and 30°C.

Storage class Chemical storage.

7.3. Specific end use(s)

**Specific end use(s)** The identified uses for this product are detailed in Section 1.2.

# SECTION 8: Exposure controls/Personal protection

# 8.1. Control parameters

# Occupational exposure limits

#### 2-AMINOETHANOL

Long-term exposure limit (8-hour TWA): WEL 1 ppm 2.5 mg/m<sup>3</sup> Short-term exposure limit (15-minute): WEL 3 ppm 7.6 mg/m<sup>3</sup>

Sk

WEL = Workplace Exposure Limit. Sk = Can be absorbed through the skin.

Ingredient comments None.

# TETRAPOTASSIUM PYROPHOSPHATE (CAS: 7320-34-5)

**DNEL** Professional - Inhalation; Long term systemic effects: 44.08 mg/m³

Consumer - Inhalation; Long term systemic effects: 10.87 mg/m<sup>3</sup>

PNEC - Fresh water; 0.5 mg/l

- marine water; 0.005 mg/l

- STP; 50 mg/l

- Fresh water; 0.05 mg/l

# 2-AMINOETHANOL (CAS: 141-43-5)

**DNEL** Industry - Dermal; Long term systemic effects: 1 mg/kg/day

Industry - Inhalation; Long term systemic effects: 3.3 mg/m³ Industry - Inhalation; Long term local effects: 3.3 mg/m³

Consumer - Dermal; Long term systemic effects: 0.24 mg/kg/day Consumer - Inhalation; Long term systemic effects: 2 mg/m³

Consumer - Inhalation; Long term: 2 mg/m3

Consumer - Oral; Long term systemic effects: 3.75 mg/kg/day

PNEC - Fresh water; 0.085 mg/l

- STP; 100 mg/l

- marine water; 0.0085 mg/l

- Sediment (Marinewater); 0.0425 mg/kg

- Soil; 0.035 mg/kg

Sediment (Freshwater); 0.425 mg/kgIntermittent release; 0.025 mg/l

# BENZENE SULPHONIC ACID, C10-13-ALKYL DERIVS., SODIUM SALTS (CAS: 68411-30-3)

**DNEL** Workers - Inhalation; Long term systemic effects: 12 mg/m³

Workers - Inhalation; Long term local effects: 12 mg/m³
Workers - Dermal; Long term systemic effects: 170 mg/kg/day
General population - Inhalation; Long term systemic effects: 3 mg/m³
General population - Inhalation; Long term local effects: 3 mg/m³
General population - Oral; Long term systemic effects: 0.85 mg/kg/day

PNEC - Fresh water; 0.268 mg/l

- marine water; 0.0268 mg/l - Intermittent release; 0.0167 mg/l

- STP; 3.43 mg/l

- Sediment (Freshwater); 8.1 mg/kg

- marine water; 8.1 mg/kg

- Soil; 35 mg/kg

# SODIUM XYLENE SULPHONATE (CAS: 1300-72-7)

**DNEL** Workers - Inhalation; Long term systemic effects: 26.9 mg/m³

Workers - Dermal; Long term systemic effects: 136.25 mg/kg/day

Workers - Dermal; Long term local effects: 0.096 mg/cm<sup>2</sup>

General population - Inhalation; Long term systemic effects: 6.6 mg/m³ General population - Dermal; Long term systemic effects: 68.1 mg/kg/day General population - Dermal; Long term local effects: 0.048 mg/cm² General population - Oral; Long term systemic effects: 3.8 mg/kg/day

**PNEC** - Fresh water; 0.23 mg/l

- Intermittent release; 2.3 mg/l

- STP; 100 mg/l

# ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO (CAS: 69011-36-5)

**DNEL** Workers - Inhalation; Long term systemic effects: 294 mg/m³

Workers - Dermal; Long term systemic effects: 2080 mg/kg

General population - Inhalation; Long term systemic effects: 87 mg/m<sup>3</sup> General population - Dermal; Long term systemic effects: 1250 mg/kg/day General population - Oral; Long term systemic effects: 25 mg/kg/day

**PNEC** - Fresh water; 0.074 mg/l

> - marine water; 0.0074 mg/l - Intermittent release; 0.015 mg/l

- STP; 1.4 mg/l

- Sediment (Freshwater); 0.604 mg/kg - Sediment (Marinewater); 0.0604 mg/kg

- Soil; 0.1 mg/kg

#### 8.2. Exposure controls

#### Protective equipment





Appropriate engineering controls

Provide adequate ventilation. Avoid inhalation of vapours. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. The following protection should be worn: Wear tight-fitting, chemical splash goggles or face shield. Personal protective equipment for eye and face protection should comply with European Standard EN166.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. Wear protective gloves made of the following material: Neoprene. Nitrile rubber. Polyethylene. Polyvinyl chloride (PVC). To protect hands from chemicals, gloves should comply with European Standard EN374. The selected gloves should have a breakthrough time of at least 8 hours.

Other skin and body

protection

Wear appropriate clothing to prevent any possibility of skin contact.

Hygiene measures

Good personal hygiene procedures should be implemented. Wash hands thoroughly after handling. Wash promptly if skin becomes contaminated. When using do not eat, drink or smoke.

Respiratory protection

No specific recommendations.

# SECTION 9: Physical and chemical properties

# 9.1. Information on basic physical and chemical properties

**Appearance** Liquid. Colour Pink.

Odour Characteristic.

#### **Janitol Plus**

Odour threshold Not determined.

pH (concentrated solution): 12.0-13.0

Melting pointNot determined.Initial boiling point and rangeNot determined.Flash pointNot determined.

Evaporation rate Not determined.

Upper/lower flammability or

explosive limits

Not applicable.

Vapour pressure Not determined.

Vapour density Not determined.

**Relative density** 1.075-1.095 @ 25 C°C

Partition coefficient Scientifically unjustified.

Auto-ignition temperature Scientifically unjustified.

Decomposition Temperature Not determined.

Viscosity Not determined.

**Explosive properties** Scientifically unjustified.

Oxidising properties Does not meet the criteria for classification as oxidising.

9.2. Other information

Other information Not relevant.

#### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

**Reactivity** There are no known reactivity hazards associated with this product.

10.2. Chemical stability

**Stability** Stable at normal ambient temperatures.

# 10.3. Possibility of hazardous reactions

Possibility of hazardous

Not applicable.

reactions

10.4. Conditions to avoid

Conditions to avoid Avoid excessive heat for prolonged periods of time. Avoid freezing.

10.5. Incompatible materials

Materials to avoid Avoid contact with acids and alkalis.

# 10.6. Hazardous decomposition products

Hazardous decomposition

Does not decompose when used and stored as recommended.

products

# SECTION 11: Toxicological information

# 11.1. Information on toxicological effects

# Acute toxicity - oral

#### **Janitol Plus**

Notes (oral LD<sub>50</sub>) Based on available data the classification criteria are not met.

**ATE oral (mg/kg)** 9,136.21

Acute toxicity - dermal

Notes (dermal LD<sub>50</sub>) Based on available data the classification criteria are not met.

**ATE dermal (mg/kg)** 27,500.0

Acute toxicity - inhalation

Notes (inhalation LC50) Based on available data the classification criteria are not met.

ATE inhalation (vapours mg/l) 32.5

Skin corrosion/irritation

Animal data Irritating.

Serious eye damage/irritation

Serious eye damage/irritation Risk of serious damage to eyes.

Respiratory sensitisation

**Respiratory sensitisation** Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

**Genotoxicity - in vivo**Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Does not contain any substances known to be carcinogenic.

Reproductive toxicity

**Reproductive toxicity - fertility** Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

**Aspiration hazard** Not anticipated to present an aspiration hazard, based on chemical structure.

**Inhalation** May cause respiratory system irritation.

**Ingestion** May cause discomfort if swallowed.

Skin contact Irritating to skin.

Eye contact Irritating to eyes.

Toxicological information on ingredients.

# TETRAPOTASSIUM PYROPHOSPHATE

Acute toxicity - dermal

Acute toxicity dermal (LD<sub>50</sub> 2.0

mg/kg)

# **Janitol Plus**

Rabbit **Species** 

Skin corrosion/irritation

Animal data Primary dermal irritation index: 0

Skin sensitisation

Skin sensitisation - Mouse: Not sensitising.

2-AMINOETHANOL

Acute toxicity - oral

Acute toxicity oral (LD50

mg/kg)

1,515.0

Rat Rat **Species** 

ATE oral (mg/kg) 1,515.0

Acute toxicity - dermal

Acute toxicity dermal (LD<sub>50</sub> 2,504.0

mg/kg)

**Species** Rabbit

ATE dermal (mg/kg) 1,100.0

Acute toxicity - inhalation

Acute toxicity inhalation

(LC50 vapours mg/l)

1.3

**Species** Rat

ATE inhalation (vapours

11.0

mg/l)

# BENZENE SULPHONIC ACID, C10-13-ALKYL DERIVS., SODIUM SALTS

Acute toxicity - oral

Acute toxicity oral (LD₅o

1,080.0

mg/kg)

**Species** Rat

1,080.0 ATE oral (mg/kg)

Acute toxicity - dermal

Notes (dermal LD50) LD50 >2000 mg/Kg bw RAT

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Endpoint waived according to REACH Annex VII, IX or XI.

Skin corrosion/irritation

Animal data Dose: 2.17, 72 hours, Rabbit

Serious eye damage/irritation

Serious eye H318 REACH dossier information.

damage/irritation

Skin sensitisation

#### **Janitol Plus**

Skin sensitisation Guinea pig maximization test (GPMT) - Guinea pig: Not sensitising.

Germ cell mutagenicity

**Genotoxicity - in vitro**Gene mutation: Negative.

**Genotoxicity - in vivo** Chromosome aberration: Negative.

Carcinogenicity

Carcinogenicity Endpoint waived according to REACH Annex VII, IX or XI.

Reproductive toxicity

Reproductive toxicity -

fertility

- NOAEL 350 mg/kg/day, Oral, Rat F2a

Reproductive toxicity -

development

Maternal toxicity:, Teratogenicity: - NOAEL: 300 mg/kg, Oral,

Specific target organ toxicity - single exposure

STOT - single exposure Based on available data the classification criteria are not met.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Conclusive data but not sufficient for classification.

#### ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO

Acute toxicity - oral

Notes (oral LD<sub>50</sub>) LD50 >2000 mg/Kg Rat

Acute toxicity - dermal

Acute toxicity dermal (LD<sub>50</sub> 2,000.0

mg/kg)

**Species** Rat

# SECTION 12: Ecological information

**Ecotoxicity** The product is not expected to be hazardous to the environment.

12.1. Toxicity

**Toxicity** The product is not expected to be toxic to aquatic organisms.

#### 12.2. Persistence and degradability

Persistence and degradability The surfactant(s) contained in this product complies(comply) with the biodegradability criteria

as laid down in Regulation (EC) No. 648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them at their direct request, or at the request of a detergent manufacturer.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Scientifically unjustified.

12.4. Mobility in soil

**Mobility** The product is soluble in water. The product is non-volatile.

# 12.5. Results of PBT and vPvB assessment

#### **Janitol Plus**

Results of PBT and vPvB

assessment

None known.

12.6. Other adverse effects

Other adverse effects None known.

#### **SECTION 13: Disposal considerations**

# 13.1. Waste treatment methods

**General information** When handling waste, the safety precautions applying to handling of the product should be

considered.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the

local Waste Disposal Authority. No specific disposal method required. Reuse or recycle

products wherever possible.

# SECTION 14: Transport information

Road transport notes Not classified.

Rail transport notes Not classified.

Sea transport notes Not classified.

# 14.1. UN number

Not applicable.

#### 14.2. UN proper shipping name

Not applicable.

#### 14.3. Transport hazard class(es)

Not applicable.

# 14.4. Packing group

Not applicable.

#### 14.5. Environmental hazards

# Environmentally hazardous substance/marine pollutant

No.

# 14.6. Special precautions for user

Not applicable.

# 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78

and the IBC Code

#### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**EU legislation** Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18

December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of

Chemicals (REACH) (as amended).

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as

amended).

#### **Janitol Plus**

#### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

#### SECTION 16: Other information

General information Only trained personnel should use this material.

Key literature references and

sources for data

Where Exposure Scenarios for the substances listed in Section 3 are available they have been assessed for the uses identified in this data sheet or on the product label and the

appropriate relevant information is incorporated into this Safety Data Sheet.

Revision comments Revision of information NOTE: Lines within the margin indicate significant changes from the

previous revision.

Revision date 11/07/2019

Revision 9

Supersedes date 05/09/2018

Hazard statements in full H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage. H319 Causes serious eye irritation.

H332 Harmful if inhaled.

H335 May cause respiratory irritation.

H412 Harmful to aquatic life with long lasting effects.

Notes for Hazard Statements

in Full

The full text for Hazard Statements in section 16 relates to the reference numbers in sections

 $\boldsymbol{2}$  and  $\boldsymbol{3}$  and not necessarily the finished product classification.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.