

**BOSCH**

Invented for life

Power tools for trade & industry

Product data sheet



Angle Grinder

GWS 22-230 H Professional

Compact powerful tool for the toughest jobs

The most important data

Rated power input	2.200 W
No-load speed	6.500 rpm
Disc diameter	230 mm

**Part number:** 0 601 882 L03[> More product information](#)

* Price including VAT

Technical Data

Battery and power	
Rated power input	2.200 W
Performance data	
No-load speed	6.500 rpm
Grinding spindle thread	M 14
Main handle	Straight
Disc diameter	230 mm
Switch	PROtection / Tri-Control (see scope of delivery)
Size and weight	
Weight	5,2 kg

Noise/vibration information

Surface grinding (roughing)	
Vibration emission value ah	7,5 m/s ²
Uncertainty K	1,5 m/s ²
Sanding with sanding sheet	
Vibration emission value ah	3,5 m/s ²
Uncertainty K	1,5 m/s ²
Noise	
Sound pressure level	93 dB(A)
Sound power level	104 dB(A)
Uncertainty K	3 dB

**Power tools for trade & industry****Advantages**

- Powerful 2200 W Champion motor – for fast work progress
- Low weight for optimum handling
- Anti-rotation protective guard – reliably protects the user if the grinding disc breaks
- Armoured coils that protect the motor against sharp grinding dust ensure long lifetime
- Double-sealed ball bearings and the especially sturdy gearing guarantee a long lifetime

**HEAVY
DUTY****Prices / Scope of delivery**

Part number:	with accessory set, (Voltage 110 V)	with accessory set, (Voltage 240 V)
Protective guard 2 605 510 298	✓	✓
Locking nut 1 603 340 040	✓	✓
Backing flange 1 605 703 099	✓	✓
Auxiliary handle 1 602 025 022	✓	✓
Voltage 240 V	-	✓
Voltage 110 V	✓	-
Two-hole spanner 1 607 950 048	✓	✓