

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Rotary Hammer with SDS-plus

GBH 2-20 D Professional



* Price including VAT

Top performance in the compact class

The most important data

Rated power input	650 W
Impact energy	1,7 J
Drilling dia. concrete, hammer drill bits	4 – 20 mm

Part number: 0 611 25A 400[> More product information](#)

Technical Data

Battery and power

Rated power input	650 W
-------------------	-------

Performance data

Impact energy	1,7 J
Impact rate at rated speed	0 – 4.200 bpm
Rated speed	0 – 1.300 rpm
Bit holder	SDS-plus

Size and weight

Weight	2,3 kg
Tool dimensions (length)	323 mm
Tool dimensions (width)	82 mm
Tool dimensions (height)	210 mm

Drilling range

Drilling dia. concrete, hammer drill bits	4 – 20 mm
Opt. appl. range concrete, hammer drill bits	4 – 10 mm
Drilling diameter in concrete with core cutters	68 mm
Max. drilling diameter masonry, core cutters	68 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in wood	30 mm

Noise/vibration information

Hammer drilling in concrete

Vibration emission value ah	13,5 m/s ²
Uncertainty K	1,5 m/s ²

Chiselling

Vibration emission value ah	9,5 m/s ²
Uncertainty K	1,5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages

- High drilling rate and 30% higher chiselling performance than other rotary hammers in the entry-level class
- Lightweight and compact, ideal for working overhead
- Robust stacked construction for a long lifetime
- Versatile range of applications due to chisel function
- Overload clutch to protect the user and the machine
- Forward/reverse rotation for dislodging jammed drill bits

