



## SAFETY DATA SHEET

RL4200F/NC

Page: 1  
Compilation date: 08/02/2012  
Revision No: 1

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name: RL4200F/NC

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.3. Details of the supplier of the safety data sheet

Company name: Robnor Resins Ltd  
Hunts Rise  
South Marston Park  
Swindon  
Wiltshire  
SN3 4TE  
United Kingdom

Tel: +44(0)1793 823741

Fax: +44(0)1793 827033

Email: [support@robnor.co.uk](mailto:support@robnor.co.uk)

#### 1.4. Emergency telephone number

Emergency tel: +44(0)1793 823741  
(office hours only)

### Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

Classification under CHIP: This product has no classification under CHIP.

#### 2.2. Label elements

Label elements under CHIP:

Hazard symbols: No significant hazard.

#### 2.3. Other hazards

PBT: This substance is not identified as a PBT substance.

### Section 3: Composition/information on ingredients

#### 3.2. Mixtures

### Section 4: First aid measures

#### 4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

# SAFETY DATA SHEET

RL4200F/NC

Page: 2

## 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

## 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in cool, well ventilated area. Keep container tightly closed.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Workplace exposure limits:** Not applicable.

[cont...]

# SAFETY DATA SHEET

RL4200F/NC

Page: 3

## 8.2. Exposure controls

- Respiratory protection: Respiratory protection not required.  
Hand protection: Protective gloves.  
Eye protection: Safety glasses. Ensure eye bath is to hand.  
Skin protection: Protective clothing.  
Environmental: No special requirement.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

State: Liquid

### 9.2. Other information

Other information: Not applicable.

## Section 10: Stability and reactivity

### 10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

Chemical stability: Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

Conditions to avoid: Heat.

### 10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

### 10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

Toxicity values: Not applicable.

### Symptoms / routes of exposure

- Skin contact: There may be mild irritation at the site of contact.  
Eye contact: There may be irritation and redness.  
Ingestion: There may be irritation of the throat.  
Inhalation: No symptoms.

## Section 12: Ecological information

### 12.1. Toxicity

Ecotoxicity values: Not applicable.

### 12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

[cont...]

# SAFETY DATA SHEET

RL4200F/NC

Page: 4

## 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

## 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

## 12.5. Results of PBT and vPvB assessment

**PBT identification:** This substance is not identified as a PBT substance.

## 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

\* indicates text in the SDS which has changed since the last revision.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.



## SAFETY DATA SHEET

HL4200F/NC

Page: 1  
Compilation date: 08/02/2012  
Revision No: 1

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name: HL4200F/NC

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.3. Details of the supplier of the safety data sheet

Company name: Robnor Resins Ltd  
Hunts Rise  
South Marston Park  
Swindon  
Wiltshire  
SN3 4TE  
United Kingdom

Tel: +44(0)1793 823741

Fax: +44(0)1793 827033

Email: [support@robnor.co.uk](mailto:support@robnor.co.uk)

#### 1.4. Emergency telephone number

Emergency tel: +44(0)1793 823741  
(office hours only)

### Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

Classification under CHIP: Xn: R20; Xi: R37; Sens.: R43

Most important adverse effects: Harmful by inhalation. Irritating to respiratory system. May cause sensitisation by skin contact.

#### 2.2. Label elements

Label elements under CHIP:

Hazard symbols: Harmful.



Risk phrases: R20: Harmful by inhalation.  
R37: Irritating to respiratory system.  
R43: May cause sensitisation by skin contact.

Safety phrases: S23: Do not breathe fumes.  
S24: Avoid contact with skin.  
S37: Wear suitable gloves.

Precautionary phrases: Contains hexamethylene-di-isocyanate. May produce an allergic reaction.

#### 2.3. Other hazards

PBT: This substance is not identified as a PBT substance.

# SAFETY DATA SHEET

HL4200F/NC

Page: 2

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

Hazardous ingredients:

HEXAMETHYLENE DIISOCYANATE OLIGOMERS

EINECS	CAS	CHIP Classification	CLP Classification	Percent
500-060-2	28182-81-2	Xn: R20; Xi: R37; Sens.: R43	-	>90%

HEXAMETHYLENE-DI-ISOCYANATE

212-485-8	822-06-0	T: R23; Xi: R36/37/38; Sens.: R42/43	-	<1%
-----------	----------	--------------------------------------	---	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin.

Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Not applicable.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach

[cont...]

# SAFETY DATA SHEET

HL4200F/NC

Page: 3

from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

## 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

## 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

## 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in cool, well ventilated area. Keep container tightly closed.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

HEXAMETHYLENE-DI-ISOCYANATE

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	0.02 mg/m <sup>3</sup>	0.07 mg/m <sup>3</sup>	-	-

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Impermeable gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Impermeable protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Pale yellow

**Odour:** Odourless

**Solubility in water:** Reacts with water.

**Boiling point/range°C:** >220

**Flash point°C:** 168

[cont...]

# SAFETY DATA SHEET

HL4200F/NC

Page: 4

## 9.2. Other information

Other information: Not applicable.

## Section 10: Stability and reactivity

### 10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

Chemical stability: Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

Conditions to avoid: Heat.

### 10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

### 10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

Relevant effects for mixture:

Effect	Route	Basis
Acute toxicity (harmful)	INH	Hazardous: calculated
Irritation	INH	Hazardous: calculated
Sensitisation	DRM	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

## Section 12: Ecological information

### 12.1. Toxicity

Ecotoxicity values: Not applicable.

### 12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

### 12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

[cont...]



# SAFETY DATA SHEET

HL4200F/NC

Page: 5

## 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

## 12.5. Results of PBT and vPvB assessment

**PBT identification:** This substance is not identified as a PBT substance.

## 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and 3:** R20: Harmful by inhalation.

R23: Toxic by inhalation.

R36/37/38: Irritating to eyes, respiratory system and skin.

R37: Irritating to respiratory system.

R42/43: May cause sensitisation by inhalation and skin contact.

R43: May cause sensitisation by skin contact.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.