

SAFETY DATA SHEET

according to Regulation (EU) 2015/830

Page 1/5

QSW-NC600-3% Silver(SAC305)

Revision 6
Revision date 2022-05-18

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	QSW-NC600-3% Silver(SAC305)
Other means of identification	UFI NO.CVHM-1Q7M-N10X-4SU3.

1.2. Relevant identified uses of the substance or mixture and uses advised against

Description	Soldering.
-------------	------------

1.3. Details of the supplier of the safety data sheet

Company	Qualitek Europe Ltd
Address	Unit 9 Apex Court Bassendale Road Bromborough Wirral CH62 3RE
Web	www.qualitek.com
Telephone	+ 44(0)151 334 0888
Fax	+ 44(0)151 334 1408
Email address of the competent person	sales@qualitek-europe.com

1.4. Emergency telephone number


Emergency telephone number	+ 44(0)151 334 0888 9.00 am - 5.00 pm Mon -Fri
----------------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

2.1.2. Classification - EC 1272/2008	Skin Sens. 1: H317;
--------------------------------------	---------------------

2.2. Label elements

Hazard pictograms	
Signal Word	Warning
Hazard Statement	Skin Sens. 1: H317 - May cause an allergic skin reaction.
Precautionary Statement: Prevention	P261 - Avoid breathing dust/fume/gas/mist/vapours/spray. P280 - Wear protective gloves/protective clothing/eye protection/face protection.
Precautionary Statement: Response	P302+P352 - IF ON SKIN: Wash with plenty of water/ . P333+P313 - If skin irritation or rash occurs: Get medical advice/attention.
Precautionary Statement: Disposal	Dispose of in compliance with all local and national regulations

QSW-NC600-3% Silver(SAC305)

Revision 6

Revision date 2022-05-18

Further information

CAUTION CONTAINS ROSIN: Exposure to this material may cause certain sensitive individuals to develop eczema and/or asthma. Sensitised persons may subsequently show asthmatic symptoms when exposed to atmospheric concentrations well below the OEL. Persons with a history of asthma allergies or chronic or recurrent respiratory disease should not be employed in any process in which this product is used.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Tin		7440-31-5	231-141-8	01-2119486474-28	95-100 - 90%	
Natural Rosin (Mod Rosin)		65997-05-9	500-163-2	01-2119960933-37	1 - 10%	Skin Sens. 1: H317;
Silver			231-131-3	01-2119555669-21	1 - 10%	
copper-metal (Copper fume)		7440-50-8	231-159-6		0.5 - 1%	STOT SE 3: H335;

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Irritating to respiratory system. Inhalation may cause coughing, tightness of the chest and irritation of the respiratory system. Move the exposed person to fresh air. Seek medical attention.
Eye contact	Irritating to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	Irritating to skin. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention if irritation or symptoms persist.
Ingestion	Ingestion may cause nausea and vomiting. Seek medical attention if irritation or symptoms persist. DO NOT INDUCE VOMITING.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	May cause irritation to respiratory system. May cause sensitisation by inhalation.
Eye contact	May cause irritation to eyes.
Skin contact	May cause irritation to skin. May cause sensitisation by skin contact.
Ingestion	Seek medical attention.

4.3. Indication of any immediate medical attention and special treatment needed

Inhalation	Coughing, difficulty in breathing. Move the exposed person to fresh air.
Eye contact	Rinse immediately with plenty of water. Seek medical attention.
Skin contact	Wash with soap and water.
Ingestion	If you feel unwell, seek medical advice (show the label where possible).

SECTION 5: Firefighting measures

5.1. Extinguishing media

Use extinguishing media appropriate to the surrounding fire conditions.

5.2. Special hazards arising from the substance or mixture

. Burning produces irritating, toxic and obnoxious fumes.

5.3. Advice for firefighters

Self-contained breathing apparatus. Wear protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

QSW-NC600-3% Silver(SAC305)

Revision 6
Revision date 2022-05-18

6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation of the working area. Wear suitable protective equipment.

6.2. Environmental precautions

Do not allow product to enter drains.

6.3. Methods and material for containment and cleaning up

Sweep up. Transfer to suitable, labelled containers for disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid contact with eyes and skin. Ensure adequate ventilation of the working area.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated area.

7.3. Specific end use(s)

Soldering.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1. Exposure Limit Values

copper-metal (Copper dusts and mists (as Cu))	WEL 8-hr limit ppm: -	WEL 8-hr limit mg/m3: 1
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: 2
	WEL 8-hr limit mg/m3 total - inhalable dust:	WEL 15 min limit mg/m3 total - inhalable dust:
	WEL 8-hr limit mg/m3 total - respirable dust:	WEL 15 min limit mg/m3 total - respirable dust:
copper-metal (Copper fume)	WEL 8-hr limit ppm: -	WEL 8-hr limit mg/m3: 0.2
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: -
	WEL 8-hr limit mg/m3 total - inhalable dust:	WEL 15 min limit mg/m3 total - inhalable dust:
	WEL 8-hr limit mg/m3 total - respirable dust:	WEL 15 min limit mg/m3 total - respirable dust:
Natural Rosin (Mod Rosin)	WEL 8-hr limit ppm:	WEL 8-hr limit mg/m3: 0.05
	WEL 15 min limit ppm:	WEL 15 min limit mg/m3:
	WEL 8-hr limit mg/m3 total 0.15 inhalable dust:	WEL 15 min limit mg/m3 total inhalable dust:
	WEL 8-hr limit mg/m3 total respirable dust:	WEL 15 min limit mg/m3 total respirable dust:

8.2. Exposure controls

8.2.1. Appropriate engineering controls	Ensure adequate ventilation of the working area.
8.2.2. Individual protection measures	Wear chemical protective clothing.
Eye / face protection	Approved safety goggles.
Skin protection - Handprotection	Chemical resistant gloves (PVC).
Respiratory protection	Wear suitable respiratory equipment when necessary.
8.2.3. Environmental exposure controls	Not normally required.
Occupational exposure controls	Appropriate local exhaust ventilation is required.

QSW-NC600-3% Silver(SAC305)

Revision 6

Revision date 2022-05-18

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	Solid
Colour	Grey
Odour	Characteristic
Melting point	217 - 219 °C
Flash point	> 115 °C
Autoignition temperature	> 226 °C
Solubility	Slightly miscible in water

SECTION 10: Stability and reactivity**10.1. Reactivity**

	No data available.
--	--------------------

10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

10.3. Possibility of hazardous reactions

	None.
--	-------

10.4. Conditions to avoid

	None.
--	-------

10.5. Incompatible materials

	Avoid contact with: Oxidising agents.
--	---------------------------------------

10.6. Hazardous decomposition products

	aliphatic hydrocarbons.
--	-------------------------

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Acute toxicity	No Significant Hazard.
Serious eye damage/irritation	Irritating to eyes.
Respiratory or skin sensitisation	May cause sensitisation by inhalation and skin contact.
Germ cell mutagenicity	No Significant Hazard.
Carcinogenicity	No carcinogenic effects reported.
Reproductive toxicity	No Significant Hazard.

11.1.2. Mixtures

	No data available.
--	--------------------

11.1.3. Hazard Information

	No data available.
--	--------------------

11.1.4. Toxicological Information

	No data available.
--	--------------------

SECTION 12: Ecological information**12.2. Persistence and degradability**

	Not readily biodegradable.
--	----------------------------

12.3. Bioaccumulative potential

	Does not bioaccumulate.
--	-------------------------

QSW-NC600-3% Silver(SAC305)

Revision 6

Revision date 2022-05-18

12.4. Mobility in soil

No data is available on this product.

SECTION 13: Disposal considerations**General information**

Dispose of in compliance with all local and national regulations.

SECTION 14: Transport information**Further information**

The product is not classified as dangerous for carriage.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

REGULATION (EC) No 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC.

SECTION 16: Other information**Other information****Text of Hazard Statements in Section 3**

Skin Sens. 1: H317 - May cause an allergic skin reaction.
STOT SE 3: H335 - May cause respiratory irritation.

Further information

The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.