

# Contact VA 250 Black



Cyanoacrylate Adhesive for special requirements  
rubber-filled and high viscosity  
high temperature resistant

VA 250 Black is highly viscous (2000-3000 mPa\*s) and temperature resistant between -50°C (-58°F) and +140°C (+284°F). It hardens slowly and with residual elasticity, is rubber-filled and black, and has high peel and impact strength.

Thanks to its curing with residual elasticity, WEICON Contact VA 250 Black is particularly suitable under changing climatic conditions. It is insensitive even under a longer influence of humidity. It is best suited for the bonding of diverse rubber materi

WEICON Contact VA 250 Black can be used in various fields of industry.

## Technical data

Ester type	Etyhl
Condition / nature	black
Viscosity at +20°C Brookfield	2000-3000 mPa*s
Max. gap covering	0,2 mm
Initial adhesion on Aluminium	90-120 sec.
Initial adhesion on Nora test rubber	20-40 sec.
Initial adhesion on Rigid PVC	40-80 sec.
Final strength after	24 h
Temperature resistance	-55 bis +140 Erweichungstemp. +160 °C

## Pretreatment of the surface

- To ensure a perfect bonding, the surfaces to be joined must be clean and dry (to clean and degrease use WEICON Surface Cleaner).
- Smooth surfaces should be mechanically roughened.

## Processing

- Apply WEICON Contact Cyanoacrylate Adhesive only on one of the surfaces to be bonded.
- The bond line should be between 0.05 mm and max. 0.2 mm (acc. to type) in thickness. Otherwise complete hardening cannot be guaranteed.
- For bonding large surfaces WEICON Contact Cyanoacrylate Adhesive should be applied drop by drop to avoid inner tensions.
- WEICON Contact Cyanoacrylate Adhesives are very economical. One drop is sufficient to cover approx. 3 - 5 cm<sup>2</sup> of bonded surface.

- The parts to be joined should be bonded in an atmosphere of 40 - 80 % relative humidity. In conditions of below 40%, the cure will be considerably slowed or even inhibited. With a relative air humidity of more than 80% or with basic substrates (e.g. glass), shock-curing can occur. In such cases, some materials show a drop in bond strength of 10 - 15 %, due to inner tensions in the bond line.

- Basic-reacting surfaces (pH-value >7) will speed up the cure whereas acidic-reacting surfaces will retard and, under extreme conditions, completely inhibit the polymerization.

## Storage

WEICON Contact Cyanoacrylate Adhesives should always be stored in a cool, dry and dark place. The shelf life is at least 9 months if stored at room temperature (18 - 25°C). If stored at +5°C (e.g. in a refrigerator), the shelf life can be extended to 12 months.

## Note

The specifications and recommendations given in this technical data sheet must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do guarantee the continuously high quality of our products. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

## Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets ([www.weicon.com](http://www.weicon.com)) must be observed.

### WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster  
P.O. Box 84 60 · DE-48045 Münster  
Germany

Tel. +49 (0) 251 / 93 22-0  
Fax +49 (0) 251 / 93 22-244  
Fax +49 (0) 251 / 93 22-233 Export  
[www.weicon.de](http://www.weicon.de) · [info@weicon.de](mailto:info@weicon.de)

### WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216  
Dubai · U.A.E

Phone +971 4 880 25 05  
Fax +971 4 880 25 09  
Mobile +971 50 545 99 83  
[www.weicon.ae](http://www.weicon.ae) · [info@weicon.ae](mailto:info@weicon.ae)

### WEICON Inc.

20 Steckle Place · Unit 20  
Kitchener · Ontario · N2E 2C3  
Canada

Phone +1 519 896 5252  
Fax +1 519 896 5254  
Cell +1 519 590 5168  
[www.weicon.ca](http://www.weicon.ca) · [info@weicon.ca](mailto:info@weicon.ca)

### WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi  
Arifağa Sokak No: 29 Kat: 3  
34530 Yenibosna – İstanbul Turkey  
[www.weicon.biz.tr](http://www.weicon.biz.tr) · [info@weicon.biz.tr](mailto:info@weicon.biz.tr)

### WEICON Romania SRL

Str. Podului Nr.1  
547176 Budui Mic (Targu Mures)  
[www.weicon.com](http://www.weicon.com) · [office@weicon.com](mailto:office@weicon.com)