



Label Remover Spray

! SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Name of product Label Remover Spray
Code-Nr. 112060

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended intended purpose(s)

Technical Aerosols

1.3. Details of the supplier of the safety data sheet

Distributor

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster
Postbox 48045, DE-8460 Münster
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322 - 244
E-Mail : msds@weicon.de
Internet : www.weicon.de

Advice

Produktsicherheit / Product-Safety-Department
Phone ++49(0)251 / 9322 - 0
E-mail (competent person):
msds@weicon.de

1.4. Emergency telephone number

GIZ Bonn (German, English) Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

Manufacturer

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster

1.4. Emergency telephone number

Emergency advice

-
Phone -
GIZ Bonn (Medizinische Auskunft in Deutsch und Englisch)
Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
--------------------------------------	-------------------	--------------------------

Aerosol 1	H222, H229	
Skin Irrit. 2	H315	
STOT SE 3	H336	
Aquatic Chronic 2	H411	

Hazard Statements

H222 Extremely flammable aerosol.

Label Remover Spray

H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

2.2. Label elements**Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]**

GHS02



GHS07



GHS09

Signal word

Danger

Hazard Statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Precautionary Statements

P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P264	Wash hands thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P273	Avoid release to the environment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P301 + P310	IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.
P302 + P352	IF ON SKIN: Wash with plenty of soap and water.
P304 + P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P312	Call a POISON CENTER or doctor/physician if you feel unwell.
P332 + P313	If skin irritation occurs: Get medical advice/attention.
P362	Take off contaminated clothing.
P403 + P235	Store in a well-ventilated place. Keep cool.
P405	Store locked up.
P410 + P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501	Dispose of contents/container to hazardous or special waste collection point.

Special rules for supplemental label elements for certain mixtures

Contains (R)-(+)-Limonene . May produce an allergic reaction.

2.3. Other hazards

Product has an anesthetic effect.

Information pertaining to special dangers for human and environment

In extensive use, formation of flammable / explosive vapour-air mixture is possible.

**Label Remover Spray****Results of PBT and vPvB assessment**

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

SECTION 3: Composition/ information on ingredients**3.1. Substances**

not applicable

3.2. Mixtures**Description**

Mixture of active ingredients with propellant

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
64-17-5	200-578-6	ethanol	3 - 9,99	Flam. Liq. 2, H225
106-97-8	203-448-7	butane	3 - 9,99	Flam. Gas 1, H220 / Press. Gas
109-66-0	203-692-4	pentane	10 - 24,99	Flam. Liq. 2, H225 / Asp. Tox. 1, H304 / STOT SE 3, H336 / Aquatic Chronic 2, H411
64742-49-0	265-151-9	Naphtha (petroleum) hydrotreated , free of aromatics (note P: < 0,1% benzene)	50 - 74,99	Flam. Liq. 2, H225 / Asp. Tox. 1, H304 / Skin Irrit. 2, H315 / STOT SE 3, H336 / Aquatic Chronic 2, H411
74-98-6	200-827-9	propane	3 - 9,99	Flam. Gas 1, H220 / Press. Gas

REACH

CAS No	Name	REACH registration number
64742-49-0	Naphtha (petroleum) hydrotreated , free of aromatics (note P: < 0,1% benzene)	01-2119475514-35-xxxx

Additional advice

< 0,1% Benzene

Labelling for contents according to regulation (EC) No 648/2004, annex VII

less than 5 % scents (D-LIMONENE)

30 % and more aliphatic hydrocarbons

SECTION 4: First aid measures**4.1. Description of first aid measures****General information**

Remove contaminated soaked clothing immediately.

In case of inhalation

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

In case of skin contact

In case of contact with skin wash off with soap and water.

Consult a doctor if skin irritation persists.

In case of eye contact

In case of contact with eyes rinse thoroughly with plenty of water and seek medical advice.

In case of ingestion

Do not induce vomiting.

If swallowed seek medical advice immediately and show the doctor packing or label.

4.2. Most important symptoms and effects, both acute and delayed

No information available.



4.3. Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam

Dry powder

Carbon dioxide

water mist

Unsuitable extinguishing media

Full water jet

5.2. Special hazards arising from the substance or mixture

No information available.

5.3. Advice for firefighters

Special protective equipment for fire-fighters

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

Additional information

Cool endangered containers with water spray jet.

Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Ensure adequate ventilation.

Use personal protective clothing.

6.2. Environmental precautions

Inform pollution control authorities if product gets into the sewerage systems or open waters.

Do not discharge into the drains or bodies of water..

Do not discharge into the drains/surface waters/groundwater.

6.3. Methods and material for containment and cleaning up

Allow to vaporise.

Disposal according to regulations.

Take up residues with suitable absorbent materials.

6.4. Reference to other sections

Safe handling: see section 7

Disposal: see section 13

Personal protection equipment: see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

Open and handle container with care!

**Label Remover Spray****General protective measures**

Avoid contact with eyes and skin

Do not inhale gases/vapours/aerosols.

Hygiene measures

At work do not eat, drink, smoke or take drugs.

Keep away from food and drink.

Keep separated from food and feed.

Wash hands before breaks and after work.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking

Do not spray on a naked flame or any incandescent material.

Do not pierce or burn even after use.

Vapours can form an explosive mixture with air.

Take precautionary measures against static discharges.

Avoid effect of heat.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep in closed original container.

Adhere to administrative regulations relating to storage of compressed gas cylinders / containers.

Advice on storage compatibility

Keep at distance to combustible materials.

Further information on storage conditions

Storage: cool and dry

Protect from heat and direct solar radiation.

Keep container in a well-ventilated place

Storage temperature may not exceed 50°C (=122°F).

Recommended storage temperature: room temperature.

7.3. Specific end use(s)**Recommendation(s) for intended use**

See section 1.2

! SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Ingredients with occupational exposure limits to be monitored**

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
106-97-8	Butane	8 hours	1450	600	EH40/2005
		Short-term	1810	750	
64-17-5	ethanol	8 hours	1920	1000	EH40/2005

Indicative occupational exposure limit values (91/322/EEC, 2000/39/EC, 2006/15/EC or 2009/161/EU)

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
109-66-0	pentane	8 hours	3000	1000	

Additional advice

The statutory local and national regulations have to be observed.

8.2. Exposure controls**Respiratory protection**

If ventilation insufficient, wear respiratory protection.

Short term: filter apparatus, Filter A/P2

**Label Remover Spray****! Hand protection**

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Gloves (solvent-resistant)

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: Nitrile rubber; 0,4mm; 480min;60min.

Eye protection

tightly fitting goggles

Other protection measures

protective clothing

Appropriate engineering controls

Sufficient ventilation and exhaustion.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties****Appearance**

aerosol

Colour

colourless, clear

Odour

characteristic

Odour threshold

not determined

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
pH value	not determined				
boiling point	not applicable				
Melting point / Freezing point	not determined				
Flash point	not applicable				Aerosol
Vapourisation rate	not determined				
Flammable (solid)	not determined				
Flammability (gas)	not determined				
Ignition temperature	200 °C				
Self ignition temperature					The product is not self-igniting.
Lower explosion limit	0,8 Vol-%				
Upper explosion limit	15 Vol-%				
Vapour pressure	573 hPa	20 °C			
Relative density	0,669 g/cm ³	20 °C			



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 08.01.2016

revision 17.07.2015 (GB) Version 8.4

Label Remover Spray

	Value	Temperature	at	Method	Remark
Vapour density	not determined				
Solubility in water	5 g/l	20 °C			
Solubility/other	not determined				
Partition coefficient n-octanol/water (log P O/W)	not determined				
Decomposition temperature	not determined				
Viscosity	not determined				
Solvent content	100 %				

Oxidising properties

No information available.

Explosive properties

The product is considered non-explosive ; nevertheless explosive vapour/air mixtures can be generated .

9.2. Other information

No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

No information available.

10.3. Possibility of hazardous reactions

No information available.

10.4. Conditions to avoid

Keep away from heat.

Uncleaned empty vessels may contain product gases which can form explosive mixtures with air.

10.5. Incompatible materials

No information available.

10.6. Hazardous decomposition products

No hazardous decomposition products known.

Thermal decomposition

Remark No decomposition if used as directed.

**Label Remover Spray****SECTION 11: Toxicological information****11.1. Information on toxicological effects****Acute toxicity/Irritation/Sensitization**

	Value/Validation	Species	Method	Remark
LD50 acute oral	> 5840 mg/kg	rat		Information concerns to main component.
LD50 acute dermal	> 2920 mg/kg	rabbit		Informations concern to main component.
LC50 acute inhalation	> 25 mg/l (4 h)	rat		Informations concern to main component.
Skin irritation	irritant			
Eye irritation	low irritant - no labeling duty			
Skin sensitization	non-sensitizing			

Experiences made from practice

Irritates respiratory tract.

Frequent persistent contact with the skin may cause skin irritation.

Irritates mucous membranes.

Inhalation causes narcotic effect/intoxication.

Additional information

The product is to be handled with the caution usual with chemicals.

Other hazardous properties may not be excluded.

SECTION 12: Ecological information**12.1. Toxicity****Ecotoxicological effects**

	Value	Species	Method	Validation
Fish	LL/EL/IL50 11,4 mg/l (96 h)	Oncorhynchus mykiss		CAS: 64742-49-0
Daphnia	NOEC 0,17 mg/l (21 d)	Daphnia magna		CAS: 64742-49-0
Algae	EC50 10,7 mg/l (72 h)	Pseudokirchneriella subcapitata		Pentane

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Other adverse effects

**Label Remover Spray****General regulation**

Even in the event of low quantities penetration into the underground drinking water is contaminated.

Toxic to fishes.

Do not allow uncontrolled leakage of product into the environment.

Product is not allowed to be discharged into the ground water or aquatic environment.

Product is not allowed to be discharged into aquatic environment, drains or sewage treatment plants.

Harmful to fishes and bacteria.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Waste code No.**

15 01 10*

Name of waste

packaging containing residues of or contaminated by hazardous substances

Wastes marked with an asterisk are considered to be hazardous waste pursuant to Directive 2008/98/EC on hazardous waste.

Recommendations for the product

Remove in accordance with local official regulations.

Recommendations for packaging

Dispose of according to the local waste regulations.

General information

For proper waste disposal a complete emptying of the tin is necessary.

Assignment to a waste code number / waste identification according to the EWC is to be carried out on a sector or process-specific basis.

SECTION 14: Transport information

	ADR/RID	IMDG	IATA-DGR
14.1. UN number	1950	1950	1950
14.2. UN proper shipping name	AEROSOLS	AEROSOLS (Naphta (Petroleum), Pentane)	Aerosols, flammable
14.3. Transport hazard class(es)	2.1	2.1	2.1
14.4. Packing group	-	-	-
14.5. Environmental hazards	Yes	Yes	Yes

14.6. Special precautions for user

Caution: Gases

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

Land and inland navigation transport ADR/RID

Hazard label(s) 2.1

tunnel restriction code D

Classification code 5F

transport in "limited quantities" according to 3.4 ADR is possible

Marine transport IMDG

MARINE POLLUTANT



! SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC standard

VOC content 99,98 %

VOC value 668,9 g/L

15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

! SECTION 16: Other information

! Recommended uses and restrictions

National and local regulations concerning chemicals shall be observed.

For industrial use only.

Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU-directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Danish MAL-code: 5-3

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 8.3

H220	Extremely flammable gas.
H225	Highly flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.