

PRODUCT DESCRIPTION

MAGMA 42 is designed for the sealing and locking of threaded fasteners which may require disassembly with standard handtools. The product is a single component anaerobic, medium strength thixotropic, acrylic based threadlocker. The product cures when confined in the absence of air between close fitting metal surfaces and prevents leakage and loosening from vibration and shock.



MAGMA 42 offers the following characteristics

Technology	Acrylic
Appearance (uncured)	Blue liquid
Chemical form	Dimethacrylate ester
Fluorescence	Positive under UV
Cure	Anaerobic
Secondary cure	Activator
Components	Single – requires no mixing
Viscosity	Thixotropic, medium
Strength	Medium
Application	Threadlocking


MAGMA 42 is particularly suitable for uses on less active substrates such as plated surfaces, where disassembly is required with handtools.

PROPERTIES OF UNCURED MATERIAL

	Typical Value
Specific gravity @ 25°C	1.0
Viscosity @ 25°C	1200-1500 cPs
Flash Point	See MSDS
Fixing time	10-15 mins


CURE SPEED VS. SUBSTRATE

The rate of cure is dependant on substrate used. The graph below shows the breakaway strength developed with time on M10 steel bolts and nuts compared to different materials and tested according to ISO 10964.



CURE SPEED VS. TEMPERATURE

The rate of cure is dependent on the ambient temperature. The graph below shows the breakaway strength developed with time at different temperatures on M10 steel bolts and nuts and tested according to ISO 10964.



CURE SPEED VS. ACTIVATOR

Where the cure speed is unacceptably long or large gaps are present. An activator can be applied to the surface which will improve cure speed.

TYPICAL PERFORMANCE OF CURED MATERIAL


	Typical Value
Operating temp °C	-54°C -150°C
(After 24 hour at 20-25°C) on M10 steel nuts & bolts)	

	Typical Value
Breakaway torque M10 steel bolts & nuts ISO 10964	17Nm
Prevail torque M10 steel bolts & nuts ISO 10964	5Nm

TYPICAL HEAT RESISTANCE


Hot Strength

Tested at temperature



HEAT AGING

Aged at temperature indicated and tested at 22°C



GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be used with chlorine or other strong oxidising materials.

For information on the safe handling of this product, consult the Material Safety Data Sheet, (MSDS).

Where washing systems are used to clean the surfaces before bonding, it is important to check the compatibility of the washing solution with the adhesive. In some cases these solutions can affect the cure and performance of the adhesive. This product is not recommended for use on certain plastics.

DIRECTIONS FOR USE

1. For optimum performance surfaces should be clean and free of grease.
2. If the material is an inactive metal consider using activator.
3. Apply several drops to the bolt & nut.
4. Assemble and tighten as required.
5. Shake the product thoroughly before use.
6. To prevent the clogging of the nozzle, do not let the tip touch metal surface during application.

For disassembly

1. Remove with standard hand tools.
2. In circumstances where hand tools do not work, use localized heat to bolt or nut, disassemble while hot.

For cleanup

1. To remove cured product use a combination of solvent and abrasion such as a wire brush.

PRECAUTION

1. Use with proper ventilation. Avoid contact with skin and eyes.
2. If contact with skin occurs, rinse with warm water or dissolve gradually with appropriate debonder.
3. Do not try to remove forcibly.
4. If adhesive gets into eye, keep eye open and rinse thoroughly. Seek medical attention immediately.
5. Keep well out of reach of children.

STORAGE

Keep adhesive in a cool, dry place optimal storage 8°C-21°C, is recommended unless otherwise labelled. To prevent contamination of unused material, do not return any product to its original container. For specific shelf life information, contact Cyanotec Ltd.

DISCLAIMER:

The data contained herein are furnished for informational purposes only and are believed to be reliable. However, Cyanotec Ltd does not assume responsibility for any results obtained by persons over whose methods Cyanotec Ltd has no control. It is the user's responsibility to determine the suitability of Cyanotec Ltd products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Cyanotec Ltd's products. Cyanotec Ltd specifically disclaims all warranties express or implied, including warranties of salability and suitability for a particular purpose arising from sale or use of Cyanotec Ltd's products. Cyanotec Ltd further disclaims any liability for consequential or incremental damages of any kind including lost profits.