

Leak Detection Spray



non flammable
anticorrosive
DIN-DVGW-tested

Leak Detection Spray is non-flammable, anti-corrosive, kind to the skin and DIN-DVGW-tested (certificate 5170AO0666). The spray is used for the fast, convenient and reliable location of leaks (cracks or porous spots) in pressurized pipes.

WEICON Leak Detection Spray does not form any hazardous compounds with carbon dioxide (CO₂), propane, butane, acetylene, oxygen, city or natural gases.

Leak Detection Spray can be used wherever compressed air, natural or liquid gas is processed, and wherever leaky points can occur on fittings, threaded joints, and connections. It greatly contributes to the safety of pneumatic brakes and gas lines.

Technical data

Colour	milky
Odour	almost odourless
Temperature resistance	0 bis +50 °C
Shelf life (minimum)	24 months
Special features	DVGW-tested for oxygen and CO ₂

Processing

Spray on area to be tested. Bubbles will be formed if there is a leakage. Thanks to its high sensitivity even smallest leakages can be detected.

Storage

Pressurized container: protect from sunlight and do not expose to temperatures exceeding +50°C.

Note

The specifications and recommendations given in this technical data sheet must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation.

We do guarantee the continuously high quality of our products. However, own adequate laboratory and practical tests to find out if the

product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster
P.O. Box 84 60 · DE-48045 Münster
Germany

Tel. +49 (0) 251 / 93 22-0
Fax +49 (0) 251 / 93 22-244
Fax +49 (0) 251 / 93 22-233 Export
www.weicon.de · info@weicon.de

WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216
Dubai · U.A.E

Phone +971 4 880 25 05
Fax +971 4 880 25 09
Mobile +971 50 545 99 83
www.weicon.ae · info@weicon.ae

WEICON Inc.

20 Steckle Place · Unit 20
Kitchener · Ontario · N2E 2C3
Canada

Phone +1 519 896 5252
Fax +1 519 896 5254
Cell +1 519 590 5168
www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi
Arifağa Sokak No: 29 Kat: 3
34530 Yenibosna – İstanbul Turkey
www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL

Str. Podului Nr.1
547176 Budiu Mic (Targu Mures)
www.weicon.com · office@weicon.com