



Leak Detection Spray

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Name of product Leak Detection Spray
Code-Nr. 116530

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended intended purpose(s)

Technical Aerosols

1.3. Details of the supplier of the safety data sheet

Distributor

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster
Postbox 48045, DE-8460 Münster
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322 - 244
E-Mail : msds@weicon.de
Internet : www.weicon.de

Advice

Produktsicherheit / Product-Safety-Department
Phone ++49(0)251 / 9322 - 0
E-mail (competent person):
msds@weicon.de

1.4. Emergency telephone number

GIZ Bonn (German, English) Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

Manufacturer

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster

1.4. Emergency telephone number

Emergency advice

-
Phone -
GIZ Bonn (Medizinische Auskunft in Deutsch und Englisch)
Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

! SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

! Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
--------------------------------------	-------------------	--------------------------

Aerosol 3	H229	
-----------	------	--

Hazard Statements

H229 Pressurised container: May burst if heated.

2.2. Label elements



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 11.01.2016

revision 23.09.2015 (GB) Version 8.3

Leak Detection Spray

Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]

! Signal word

Warning

Hazard Statements

H229 Pressurised container: May burst if heated.

Precautionary Statements

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P251 Do not pierce or burn, even after use.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

P501 Dispose of contents/container to hazardous or special waste collection point.

2.3. Other hazards

Information pertaining to special dangers for human and environment

Not classified as dangerous preparation according to Directive 1999/45/EC.

Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

SECTION 3: Composition/ information on ingredients

3.1. Substances

not applicable

3.2. Mixtures

Description

Leak Detection Spray basing on aqueous tenside solution; without solvents.

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
10024-97-2	233-032-0	nitrous oxide	< 2	Ox. Gas 1, H270 / Press. Gas, H280
137-16-6	205-281-5	Natrium-N-Lauroylsarkosinat	< 0,3	Acute Tox. 1, H330 / Eye Dam. 1, H318 / Skin Irrit. 2, H315

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Take affected person into fresh air.

Do not leave casualty unattended.

In case of inhalation

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

In case of skin contact

In case of contact with skin wash off with water.

Consult a doctor if skin irritation persists.



Leak Detection Spray

In case of eye contact

In case of contact with eyes rinse thoroughly with plenty of water and seek medical advice.

In case of ingestion

Do not induce vomiting.

If swallowed seek medical advice immediately and show the doctor packing or label.

Rinse out mouth thoroughly with water.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Product does not burn, fire-extinguishing activities according to surrounding.

5.2. Special hazards arising from the substance or mixture

Danger of bursting

Risk of formation of toxic pyrolyse products.

5.3. Advice for firefighters

Special protective equipment for fire-fighters

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

Additional information

Cool endangered containers with water spray jet.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Ensure adequate ventilation.

High risk of slipping due to leakage/spillage of product.

6.2. Environmental precautions

No information available.

6.3. Methods and material for containment and cleaning up

Flush away residues with hot water.

6.4. Reference to other sections

Safe handling: see section 7

Disposal: see section 13

Personal protection equipment: see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

No special measures necessary if used correctly.

General protective measures

Avoid contact with eyes and skin

Do not inhale gases/vapours/aerosols.

**Leak Detection Spray****Hygiene measures**

At work do not eat, drink and smoke.

Advice on protection against fire and explosion

Pressurized container.

Do not pierce or burn even after use.

The product is not combustible.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep in closed original container.

Adhere to administrative regulations relating to storage of compressed gas cylinders / containers.

Advice on storage compatibility

Do not store together with food.

Further information on storage conditions

Protect from frost.

Protect from direct solar radiation.

Protect from heat and direct solar radiation.

Storage temperature may not exceed 50°C (=122°F).

Keep in a cool place, heat causes increase in pressure and risk of bursting.

7.3. Specific end use(s)**Recommendation(s) for intended use**

See section 1.2

! SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Ingredients with occupational exposure limits to be monitored**

CAS No	Name	Code	[mg/m ³]	[ppm]	Remark
10024-97-2	Nitrous oxide	8 hours	183	100	EH40/2005

Additional advice

The statutory local and national regulations have to be observed.

8.2. Exposure controls**Respiratory protection**

Not required

! Hand protection

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Glove material specification [make/type, thickness, permeation time/life, wetting resistance]:: Nitrile rubber; 0,4mm; 480min;60min.

Chemical protective gloves must be chosen carefully in view of their design and depending on the dependence on the concentration and amounts of dangerous goods used in the specific working tasks.

Eye protection

tightly fitting goggles

Other protection measures

protective clothing

Appropriate engineering controls

Sufficient ventilation and exhaustion.

**Leak Detection Spray****SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties****Appearance**

aerosol

Colour

colourless

Odour

characteristic

Odour threshold

not determined

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
pH value	ca. 7	20 °C			
boiling point	100 °C				
melting point	0 °C				
Flash point	not applicable				Aerosol
Vapourisation rate	not determined				
Flammable (solid)	not determined				
Flammability (gas)	not determined				
Ignition temperature	not applicable				
Self ignition temperature	not determined				
Lower explosion limit	not determined				
Upper explosion limit	not determined				
Vapour pressure	ca. 6 bar	20 °C			
Relative density	ca. 1 g/cm ³	20 °C			
Vapour density	not determined				
Solubility in water					miscible
Solubility/other	not determined				
Partition coefficient n-octanol/water (log P O/W)	not determined				
Decomposition temperature	not determined				
Viscosity	not determined				
Solvent content	0 %				
Water content	> 98 %				

Oxidising properties

No information available.

**Leak Detection Spray****Explosive properties**

No information available.

9.2. Other information

No information available.

SECTION 10: Stability and reactivity**10.1. Reactivity**

No information available.

10.2. Chemical stability

No information available.

10.3. Possibility of hazardous reactions

Hazardous decomposition products

Hydrofluoric acid

10.4. Conditions to avoid

Keep away from heat.

Heating above 50°C

10.5. Incompatible materials**Substances to avoid**

Risk of bursting at temperatures above 50°C due to a pressure increase inside the container. Heating causes the pressure to increase. Risk of bursting through overheating.

10.6. Hazardous decomposition products

fluoric containing products

Thermal decomposition

Remark No decomposition if used as directed.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Acute toxicity/Irritation/Sensitization**

	Value/Validation	Species	Method	Remark
Skin irritation	No stimulation effect.			
Eye irritation	low irritant - no labeling duty			
Skin sensitization	non-sensitizing			

Experiences made from practice

According to our experience and current information, the product has no detrimental effects on health if handled and used correctly

Additional information

The product is to be handled with the caution usual with chemicals.

Other hazardous properties may not be excluded.

No toxicological data available.

**Leak Detection Spray****SECTION 12: Ecological information****12.1. Toxicity**

No information available.

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Other adverse effects**Behaviour in sewage plant**

When low concentrations are discharged correctly into adapted biological sewage treatment plants, interference with the degradation activity of activated sludge is not likely.

Additional ecological information

	Value	Method	Remark
AOX	Product can contain organically bound halogen and contribute to the adsorbable organic halogen value.		

General regulation

Ecological dates are not available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Waste code No.**

16 05 04*

Name of waste

gases in pressure containers (including halons) containing hazardous substances

Wastes marked with an asterisk are considered to be hazardous waste pursuant to Directive 2008/98/EC on hazardous waste.

Recommendations for the product

Remove in accordance with local official regulations.

Recommendations for packaging

Dispose of according to the local waste regulations.

General information

For proper waste disposal a complete emptying of the tin is necessary.

Assignment to a waste code number / waste identification according to the EWC is to be carried out on a sector or process-specific basis.

SECTION 14: Transport information

	ADR/RID	IMDG	IATA-DGR
14.1. UN number	1950	1950	1950
14.2. UN proper shipping name	AEROSOLS	AEROSOLS	Aerosols, non-flammable



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 11.01.2016

revision 23.09.2015 (GB) Version 8.3

Leak Detection Spray

	ADR/RID	IMDG	IATA-DGR
14.3. Transport hazard class(es)	2.2	2.2	2.2

14.4. Packing group	-	-	-
----------------------------	---	---	---

14.5. Environmental hazards	No	No	No
------------------------------------	----	----	----

14.6. Special precautions for user

Caution: Gases

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code
not applicable

Land and inland navigation transport ADR/RID

Hazard label(s) 2.2

tunnel restriction code E

Classification code 5A

transport in "limited quantities" according to 3.4 ADR is possible

Transport/further information

24h EMERGENCY CONTACT (TRANSPORT) +49(0)178 433 7434 (Consultank Lutz Harder GmbH)

! SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC standard

VOC content 0 %

15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

! SECTION 16: Other information

! Recommended uses and restrictions

National and local regulations concerning chemicals shall be observed.

For industrial use only.

Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU-directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 8.2

H270	May cause or intensify fire; oxidiser.
H280	Contains gas under pressure; may explode if heated.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H330	Fatal if inhaled.
