



# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Date of issue: 12/08/2015

Revision date:

Version: 1.1

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Product name : Green Line - CLEARVUE RAIN REPELLENT

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Intended for general public  
Main use category : Consumer use  
Use of the substance/mixture : Automotive Care Products.

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

Turtle Wax Europe Limited  
4th Floor Alaska House, Atlantic Park, Dunnings Bridge Road  
Liverpool, L30 4AB - United Kingdom  
T +44 151 530 4740  
[MSDS@turtlewaxeurope.com](mailto:MSDS@turtlewaxeurope.com)

#### 1.4. Emergency telephone number

Emergency number : +44 151 530 4740  
Office hours only 08:30 - 17:00

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flam. Liq. 2 H225  
Eye Irrit. 2 H319  
STOT SE 3 H336

Full text of H-statements: see section 16

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :    
GHS02 GHS07

Signal word (CLP) : Danger  
Hazardous ingredients : propan-2-ol  
Hazard statements (CLP) : H225 - Highly flammable liquid and vapour  
H319 - Causes serious eye irritation  
H336 - May cause drowsiness or dizziness  
Precautionary statements (CLP) : P102 - Keep out of reach of children  
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P261 - Avoid breathing vapours, spray, mist, fume  
P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P403+P233 - Store in a well-ventilated place. Keep container tightly closed  
P501 - Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation

#### 2.3. Other hazards

Adverse physicochemical, human health and : Highly flammable liquid and vapour. May cause drowsiness or dizziness. Causes serious eye

# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

environmental effects : irritation.  
Other hazards not contributing to the classification : None under normal conditions.

### SECTION 3: Composition/information on ingredients

#### 3.1. Substance

Not applicable

#### 3.2. Mixture

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
propan-2-ol	(CAS No) 67-63-0 (EC no) 200-661-7 (EC index no) 603-117-00-0 (REACH-no) 01-2119457558-25	>= 80	Flam. Liq. 2, H225 STOT SE 3, H336 Eye Irrit. 2, H319
sulphuric acid substance with a Community workplace exposure limit	(CAS No) 7664-93-9 (EC no) 231-639-5 (EC index no) 016-020-00-8 (REACH-no) 01-2119458838-20	0.1 - 1	Skin Corr. 1A, H314

#### Specific concentration limits:

Name	Product identifier	Specific concentration limits
sulphuric acid	(CAS No) 7664-93-9 (EC no) 231-639-5 (EC index no) 016-020-00-8 (REACH-no) 01-2119458838-20	(5 =< C < 15) Skin Irrit. 2, H315 (5 =< C < 15) Eye Irrit. 2, H319 (C >= 15) Skin Corr. 1A, H314

Full text of H-phrases: see section 16

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

First-aid measures general : If you feel unwell, seek medical advice (show the label where possible).  
First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing. Get medical advice/attention.  
First-aid measures after skin contact : Rinse skin with water/shower. Remove/Take off immediately all contaminated clothing.  
First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.  
First-aid measures after ingestion : Not expected to present a significant hazard under anticipated conditions of normal use. Rinse mouth. Get medical advice/attention if you feel unwell.

#### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries : May cause drowsiness or dizziness.  
Symptoms/injuries after inhalation : May cause drowsiness or dizziness.  
Symptoms/injuries after skin contact : May cause slight irritation.  
Symptoms/injuries after eye contact : Eye irritation.  
Symptoms/injuries after ingestion : May cause slight irritation.

#### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

#### 5.2. Special hazards arising from the substance or mixture

Fire hazard : Highly flammable liquid and vapour.  
Explosion hazard : Product is not explosive.  
Reactivity in case of fire : Not known.  
Hazardous decomposition products in case of fire : Toxic fumes may be released.

#### 5.3. Advice for firefighters

Precautionary measures fire : Evacuate area. Stop leak if safe to do so.  
Firefighting instructions : Eliminate all ignition sources if safe to do so. Evacuate area. Fight fire with normal precautions from a reasonable distance. In case of fire: stop leak if safe to do so. Use extinguishing media appropriate for surrounding fire.

# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

General measures : Avoid release to the environment. Evacuate area. No flames, no sparks. Eliminate all sources of ignition. No smoking.

##### 6.1.1. For non-emergency personnel

Protective equipment : Wear suitable protective clothing, gloves and eye or face protection.

Emergency procedures : Evacuate unnecessary personnel. Ventilate spillage area. Do not breathe vapours. Eliminate all ignition sources if safe to do so. No smoking. Avoid contact with skin and eyes. Mark out the contaminated area with signs and prevent access to unauthorized personnel. Only qualified personnel equipped with suitable protective equipment may intervene.

##### 6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. Respiratory protection. Protective gloves. For further information refer to section 8: "Exposure controls/personal protection". Avoid contact with skin and eyes. Avoid breathing vapours.

Emergency procedures : Ventilate area. Stop leak if safe to do so. Eliminate all ignition sources if safe to do so. No smoking. Mark out the contaminated area with signs and prevent access to unauthorized personnel. Use only non-sparking tools.

#### 6.2. Environmental precautions

Avoid release to the environment.

#### 6.3. Methods and material for containment and cleaning up

For containment : Collect spillage.

Methods for cleaning up : Take up liquid spill into absorbent material. Shovel into suitable and closed container for disposal. Use only non-sparking tools. This material and its container must be disposed of in a safe way, and as per local legislation.

Other information : This material and its container must be disposed of as hazardous waste.

#### 6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of solid materials or residues refer to section 13: "Disposal considerations".

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Precautions for safe handling : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Wear personal protective equipment. Use only outdoors or in a well-ventilated area. Avoid breathing vapours, spray, mist, fume. Take precautionary measures against static discharge. Ground/bond container and receiving equipment. Use explosion-proof equipment. Use only non-sparking tools. Flammable vapours may accumulate in the container. Avoid contact with skin and eyes.

Hygiene measures : Always wash hands after handling the product. Do not eat, drink or smoke when using this product.

#### 7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Take precautionary measures against static discharge. Ground/bond container and receiving equipment. Use only non-sparking tools.

Storage conditions : Keep away from ignition sources. Store in a well-ventilated place. Keep cool. Keep container tightly closed. Store locked up. Store in original container.

Incompatible materials : Heat sources. Sources of ignition.

Packaging materials : Keep only in original container.

#### 7.3. Specific end use(s)

Automotive Care Products.

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

propan-2-ol (67-63-0)		
United Kingdom	Local name	Propan-2-ol
United Kingdom	WEL TWA (mg/m <sup>3</sup> )	999 mg/m <sup>3</sup>
United Kingdom	WEL TWA (ppm)	400 ppm
United Kingdom	WEL STEL (mg/m <sup>3</sup> )	1250 mg/m <sup>3</sup>
United Kingdom	WEL STEL (ppm)	500 ppm

# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

sulphuric acid (7664-93-9)		
United Kingdom	Local name	Sulphuric acid (mist)
United Kingdom	WEL TWA (mg/m <sup>3</sup> )	0.05 mg/m <sup>3</sup>
United Kingdom	Remark (WEL)	The mist is defined as the thoracic fraction

### 8.2. Exposure controls

Appropriate engineering controls	: Eliminate ignition sources. Ensure good ventilation of the work station.
Personal protective equipment	: In case of splash hazard: safety glasses.
Hand protection	: Protective gloves
Eye protection	: Safety glasses
Skin and body protection	: Wear suitable protective clothing
Respiratory protection	: In case of insufficient ventilation, wear suitable respiratory equipment



Environmental exposure controls : Avoid release to the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: various.
Odour	: characteristic.
Odour threshold	: No data available
pH	: 1.5 - 2.5
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 12 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 0.804 - 0.824
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Product is not explosive.
Oxidising properties	: Oxidising liquids Not applicable.
Explosive limits	: No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Highly flammable liquid and vapour.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### 10.5. Incompatible materials

Acids. Oxidizing agent.

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity : Not classified

<b>propan-2-ol (67-63-0)</b>	
LD50 oral	4396 mg/kg bodyweight
LD50 dermal	12800 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	46600 mg/m <sup>3</sup>

<b>sulphuric acid (7664-93-9)</b>	
LD50 oral	2140 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	375 mg/m <sup>3</sup>

Skin corrosion/irritation : Not classified

pH: 1.5 - 2.5

Serious eye damage/irritation : Causes serious eye irritation.

pH: 1.5 - 2.5

Respiratory or skin sensitisation : Not classified

Germ cell mutagenicity : Not classified

Carcinogenicity : Not classified

Reproductive toxicity : Not classified

Specific target organ toxicity (single exposure) : May cause drowsiness or dizziness.

Specific target organ toxicity (repeated exposure) : Not classified

Aspiration hazard : Not classified

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.

Ecology - water : The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.

<b>propan-2-ol (67-63-0)</b>	
LC50 fish 1	9640 mg/l
EC50 other aquatic organisms 1	13299 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 1000 mg/l IC50 alga (72 h) mg/l

<b>sulphuric acid (7664-93-9)</b>	
LC50 fish 1	> 16 mg/l
EC50 other aquatic organisms 1	> 100 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 100 mg/l IC50 alga (72 h) mg/l

### 12.2. Persistence and degradability

<b>Green Line - CLEARVUE RAIN REPELLENT</b>	
Persistence and degradability	Not established.

### 12.3. Bioaccumulative potential

<b>Green Line - CLEARVUE RAIN REPELLENT</b>	
Bioaccumulative potential	Not established.

<b>propan-2-ol (67-63-0)</b>	
Log Pow	0.14

<b>sulphuric acid (7664-93-9)</b>	
Log Pow	-2.2

### 12.4. Mobility in soil

<b>Green Line - CLEARVUE RAIN REPELLENT</b>	
Ecology - soil	Not established.

# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

Other adverse effects : None known.  
Additional information : Avoid release to the environment

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.  
Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.  
Waste disposal recommendations : Dispose of contents/container to a hazardous or special waste collection point.  
Additional information : Flammable vapours may accumulate in the container.

## SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

### 14.1. UN number

UN-No. (ADR) : 1993  
UN-No. (IMDG) : 1993  
UN-No. (IATA) : 1993  
UN-No. (ADN) : 1993  
UN-No. (RID) : 1993

### 14.2. UN proper shipping name

Proper Shipping Name (ADR) : FLAMMABLE LIQUID, N.O.S.  
Proper Shipping Name (IMDG) : FLAMMABLE LIQUID, N.O.S.  
Proper Shipping Name (IATA) : Flammable liquid, n.o.s.  
Proper Shipping Name (ADN) : FLAMMABLE LIQUID, N.O.S.  
Proper Shipping Name (RID) : FLAMMABLE LIQUID, N.O.S.  
Transport document description (ADR) : UN 1993 FLAMMABLE LIQUID, N.O.S. (propan-2-ol(67-63-0)), 3, II, (D/E)  
Transport document description (IMDG) : UN 1993 FLAMMABLE LIQUID, N.O.S., 3, II

### 14.3. Transport hazard class(es)

#### ADR

Transport hazard class(es) (ADR) : 3  
Danger labels (ADR) : 3



#### IMDG

Transport hazard class(es) (IMDG) : 3  
Danger labels (IMDG) : 3



#### IATA

Transport hazard class(es) (IATA) : 3  
Hazard labels (IATA) : 3



# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### ADN

Transport hazard class(es) (ADN) : 3  
Danger labels (ADN) : 3

:

### RID

Transport hazard class(es) (RID) : 3  
Danger labels (RID) : 3

:



### 14.4. Packing group

Packing group (ADR) : II  
Packing group (IMDG) : II  
Packing group (IATA) : II  
Packing group (ADN) : II  
Packing group (RID) : II

### 14.5. Environmental hazards

Dangerous for the environment : No  
Marine pollutant : No  
Other information : No supplementary information available

### 14.6. Special precautions for user

#### - Overland transport

Classification code (ADR) : F1  
Special provisions (ADR) : 274, 601, 640C  
Limited quantities (ADR) : 11  
Excepted quantities (ADR) : E2  
Packing instructions (ADR) : P001  
Mixed packing provisions (ADR) : MP19  
Portable tank and bulk container instructions (ADR) : T7  
Portable tank and bulk container special provisions (ADR) : TP1, TP8, TP28  
Tank code (ADR) : L1.5BN  
Vehicle for tank carriage : FL  
Transport category (ADR) : 2  
Special provisions for carriage - Operation (ADR) : S2, S20  
Hazard identification number (Kemler No.) : 33  
Orange plates :



Tunnel restriction code (ADR) : D/E  
EAC code : •3YE

#### - Transport by sea

Special provisions (IMDG) : 274  
Limited quantities (IMDG) : 1 L  
Excepted quantities (IMDG) : E2  
Packing instructions (IMDG) : P001  
IBC packing instructions (IMDG) : IBC02

# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Tank instructions (IMDG)	: T7
Tank special provisions (IMDG)	: TP1, TP8, TP28
EmS-No. (Fire)	: F-E
EmS-No. (Spillage)	: S-E
Stowage category (IMDG)	: B

### - Air transport

PCA Excepted quantities (IATA)	: E2
PCA Limited quantities (IATA)	: Y341
PCA limited quantity max net quantity (IATA)	: 1L
PCA packing instructions (IATA)	: 353
PCA max net quantity (IATA)	: 5L
CAO packing instructions (IATA)	: 364
CAO max net quantity (IATA)	: 60L
Special provisions (IATA)	: A3
ERG code (IATA)	: 3H

### - Inland waterway transport

Classification code (ADN)	: F1
Special provisions (ADN)	: 274, 61, 64C
Limited quantities (ADN)	: 1 L
Excepted quantities (ADN)	: E2
Carriage permitted (ADN)	: T
Equipment required (ADN)	: PP, EX, A
Ventilation (ADN)	: VE01
Number of blue cones/lights (ADN)	: 1
Carriage prohibited (ADN)	: No
Not subject to ADN	: No

### - Rail transport

Classification code (RID)	: F1
Special provisions (RID)	: 274, 601, 640C
Limited quantities (RID)	: 1L
Excepted quantities (RID)	: E2
Packing instructions (RID)	: P001
Mixed packing provisions (RID)	: MP19
Portable tank and bulk container instructions (RID)	: T7
Portable tank and bulk container special provisions (RID)	: TP1, TP8, TP28
Tank codes for RID tanks (RID)	: L1.5BN
Transport category (RID)	: 2
Colis express (express parcels) (RID)	: CE7
Hazard identification number (RID)	: 33
Carriage prohibited (RID)	: No

### 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Seveso Information : This product is Seveso Directive 96/82/EC

#### 15.1.2. National regulations

No additional information available



# Green Line - CLEARVUE RAIN REPELLENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Full text of H- and EUH-statements:

Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 2	Flammable liquids, Category 2
Skin Corr. 1A	Skin corrosion/irritation, Category 1A
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H225	Highly flammable liquid and vapour
H314	Causes severe skin burns and eye damage
H319	Causes serious eye irritation
H336	May cause drowsiness or dizziness

SDS EU TURTLEWAX

*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product*