

**Productname :** SERVISOL FOAM CLEANSER 30      **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN)      **Replaces:** UDS000369\_20150515

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**SERVISOL FOAM CLEANSER 30**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

### 1.3. Details of the supplier of the safety data sheet

**CRC Industries UK Ltd.**  
**Ambersil House - Wylds Road**  
**Castlefield Industrial Estate**  
**TA6 4DD Bridgwater Somerset**  
**United Kingdom**  
**Tel.: +44 1278 727200**  
**Fax.: +44 1278 425644**  
**E-mail : hse.uk@crcind.com**

Subsidiaries		Tel	Fax
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Aerosols, category 1  
Extremely flammable aerosol.  
Pressurised container: May burst if heated.

Classification is based on test data.

**Health:** Eye irritation, category 2  
Causes serious eye irritation.

Classification based on calculation method.

**Environment:** Not classified

Classification based on calculation method.



**Productname :** SERVISOL FOAM CLEANSER 30 **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN) **Replaces:** UDS000369\_20150515

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

#### Hazard pictogram(s):



<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P280 : Wear protective gloves/protective clothing/eye protection/face protection. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.

**Regulation (EC) No 648/2004 on detergents:** aliphatic hydrocarbons 5 - 15 %  
 anionic surfactants < 5 %  
 perfumes benzyl alcohol, limonene

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926-20	68512-91-4	270-990-9	5-10	Press. Gas, Flam. Gas 1	H280,H220	K,G
1-methoxy-2-propanol; monopropylene glycol methyl ether	01-2119457435-35	107-98-2	203-539-1	1-5	Flam. Liq. 3, STOT SE 3	H226,H336	A
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	1-5	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119456620-43	-	(926-141-6)	1-5	Asp. Tox. 1	H304	B,Q
Glycine N-methyl-N-(1-oxododecyl)- sodium	01-2119527780-	137-16-6	205-	<3	Env Dam. 1. Skin Irrit	H318 H315 H330	

**Productname :** SERVISOL FOAM CLEANSER 30    **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN)    **Replaces:** UDS000369\_20150515

salt	39	281-5	2, Acute Tox. 2
<b>Explanation notes</b>			
A : substance with Community workplace exposure limit			
B : substance with national established workplace exposure limit			
G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006			
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)			
Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.			

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C



**Productname :** SERVISOL FOAM CLEANSER 30    **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN)    **Replaces:** UDS000369\_20150515

Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.  
Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.



**Productname :** SERVISOL FOAM CLEANSER 30 **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN) **Replaces:** UDS000369\_20150515

Keep out of reach of children.

### 7.3. Specific end use(s)

Cleaners - Heavy duty

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm

### 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation Wear suitable protective gloves
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Liquid under pressure.
<b>colour :</b>	Colourless to yellow.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	10



**Productname :** SERVISOL FOAM CLEANSER 30      **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN)      **Replaces:** UDS000369\_20150515

**Boiling point/range :** 82 °C  
**Flash point :** 12 °C  
**Evaporation rate :** Not available.  
**Explosion limits : upper limit :** 15 %  
**lower limit :** 0.6 %  
**Vapour pressure :** Not available.  
**Relative density :** 0.962 g/cm<sup>3</sup> (@ 20°C).  
**Solubility in water :** Soluble in water  
**Auto-ignition :** 225 °C  
**Viscosity :** Not available.

## 9.2. Other information

**VOC = volatile organic compounds** 221 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO<sub>2</sub>

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

**acute toxicity:** based on available data the classification criteria are not met  
**skin corrosion/irritation:** based on available data the classification criteria are not met



**Productname :** SERVISOL FOAM CLEANSER 30      **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN)      **Replaces:** UDS000369\_20150515

**serious eye damage/irritation:** Causes serious eye irritation.  
**respiratory or skin sensitisation:** based on available data the classification criteria are not met  
**germ cell mutagenicity:** based on available data the classification criteria are not met  
**carcinogenicity:** based on available data the classification criteria are not met  
**toxicity for reproduction:** based on available data the classification criteria are not met  
**STOT-single exposure:** based on available data the classification criteria are not met  
**STOT repeated exposure:** based on available data the classification criteria are not met  
**aspiration hazard:** based on available data the classification criteria are not met

#### Information on likely routes of exposure:

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
**Ingestion :** May cause gastrointestinal disturbances  
**Skin contact :** May cause irritation.  
**Eye contact :** Irritating to eyes

#### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LD50 oral rat	4016 mg/kg
		LC50 inhal.rat	27596 mg/l
		LD50 derm.rabit	2000 mg/kg
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	5840 mg/kg
		LC50 inhal.rat	> 25000 mg/l
		LD50 derm.rabit	13900 mg/kg
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	>5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

Not classified

#### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LC50 fish	6812 mg/l
		EC50 daphnia	23300 mg/l
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	1000 mg/l
		LC50 fish	9640 mg/l
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	EC50 daphnia	9714 mg/l
		IC50 algae	1000 mg/l



**Productname :** SERVISOL FOAM CLEANSER 30    **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN)    **Replaces:** UDS000369\_20150515

		LC50 fish	1000 mg/l
		EC50 daphnia	1000 mg/l

#### 12.2. Persistence and degradability

No information available

#### 12.3. Bioaccumulative potential

No information available

#### 12.4. Mobility in soil

Soluble in water

#### 12.5. Results of PBT and vPvB assessment

No information available

#### 12.6. Other adverse effects

No information available

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**National regulations :** Disposal should be in accordance with local, state or national legislation

### SECTION 14: Transport information

#### 14.1. UN number

UN-number : 1950

#### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F





**Productname :** SERVISOL FOAM CLEANSER 30      **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000369\_3\_20170629 (EN)      **Replaces:** UDS000369\_20150515

#### 14.4. Packing group

Packing group: ..... Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally  
hazardous: ..... No  
IMDG - Marine pollutant: ..... No  
IATA/ICAO - Environmentally  
hazardous: ..... No

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: ..... (D)  
IMDG - Ems: ..... F-D, S-U  
IATA/ICAO - PAX: ..... 203  
IATA/ICAO - CAO: ..... 203

#### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H225 : Highly flammable liquid and vapour.  
H226 : Flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H304 : May be fatal if swallowed and enters airways.  
H315 : Causes skin irritation.  
H318 : Causes serious eye damage.  
H319 : Causes serious eye irritation.  
H330 : Fatal if inhaled.  
H336 : May cause drowsiness or dizziness.

REVISIONS IN CHAPTRE : ..... 8.2. Exposure controls



---

<b>Productname :</b>	SERVISOL FOAM CLEANSER 30	<b>Creationdate :</b>	29.06.17 Version : 2.0
<b>Ref.Nr.:</b>	UDS000369_3_20170629 (EN)	<b>Replaces:</b>	UDS000369_20150515

---

acronyms and synonyms:

- TWA = time weight average
- STEL = short time exposure limit
- VOC = volatile organic compounds
- PBT = persistant bioaccumulative toxic
- vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

