

Safety Data Sheet according to Regulation (EC) No. 453/2010 Date of issue: 12/08/2015 Revision date:

Version: 1.1

:

riecauti	ionary statements (CLP)	<ul> <li>P210 - Keep away from heat, hot surfaces, sparks, open frames and other ignition sources. I smoking</li> <li>P211 - Do not spray on an open flame or other ignition source</li> <li>P251 - Do not pierce or burn, even after use</li> <li>P271 - Use only outdoors or in a well-ventilated area</li> <li>P302+P352 - IF ON SKIN: Wash with plenty of water</li> <li>P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing</li> <li>P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F</li> <li>P501 - Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation</li> <li>P102 - Keep out of reach of children</li> </ul>	
Precauti	ionary statements (CLP)	<ul> <li>H315 - Causes skin irritation</li> <li>H336 - May cause drowsiness or dizziness</li> <li>H412 - Harmful to aquatic life with long lasting effects</li> <li>P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.</li> </ul>	
nazaru	statements (CLP)	: H222 - Extremely flammable aerosol H229 - Pressurised container: May burst if heated	
-	vord (CLP) ous ingredients	: Danger : (L) COUMARIN	
2:		GHS02 GHS07	
Hazard	pictograms (CLP)		
	ng according to Regulation (EC)	No. 1272/2008 [CLP]	
2.2.	Label elements		
Full text	of H-statements: see section 16		
Aquatic	Chronic 3	H412	
STOT S	E 3	H336	
Skin Irrit		H315	
Aerosol	cation according to Regulation	H222:H229	
SECT 2.1.	ION 2: Hazards identificat Classification of the substanc		
		Office hours only 08:30 - 17:00	
Emerge	ncy number	: +44 151 530 4740	
1.4.	Emergency telephone number		
Liverpoo T +44 1	or Alaska House, Atlantic Park, Du ol, L30 4AB - United Kingdom 51 530 4740 Oturtlewaxeurope.com	nnings Bridge Road	
	/ax Europe Limited		
1.3.	Details of the supplier of the s	afety data sheet	
	tional information available		
1.2.2.	Uses advised against		
1.2.1. Intender	Relevant identified uses d for general public		
1.2.		e substance or mixture and uses advised against	
Vaporizer		: Aerosol	
Product name		: Green Line - FRESH SHINE VANILLA	
Product form		: Mixture	
Product			

### Safety Data Sheet

according to Regulation (EC) No. 453/2010

#### 2.3. Other hazards

Adverse physicochemical, human health and environmental effects

: Pressurised container: May burst if heated. Extremely flammable aerosol. May cause drowsiness or dizziness. Causes skin irritation. Harmful to aquatic life with long lasting effects.

### **SECTION 3: Composition/information on ingredients**

### 3.1. Substance

Not applicable

#### 3.2. Mixture

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Hydrocarbons, C3-4 rich, petroleum distillate,petroleum gas	(CAS No) 68512-91-4	50 - 80	Flam. Gas 1, H220 Muta. 1B, H340 Carc. 1A, H350
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics	(CAS No) 64742-49-0 (EC no) 920-750-0 (REACH-no) 01-2119475515-33	10 - 50	Skin Irrit. 2, H315 Muta. 1B, H340 Carc. 1B, H350 STOT SE 3, H336 Asp. Tox. 1, H304 Aquatic Chronic 2, H411
propan-2-ol	(CAS No) 67-63-0 (EC no) 200-661-7 (EC index no) 603-117-00-0 (REACH-no) 01-2119457558-25	1 - 30	Flam. Liq. 2, H225 STOT SE 3, H336 Eye Irrit. 2, H319
(L) COUMARIN	(CAS No) 91-64-5 (EC no) 202-086-7 (REACH-no) 01-2119949300-45	< 10	Acute Tox. 4 (Oral), H302 Skin Sens. 1, H317

#### Full text of H-phrases: see section 16

SECTION 4: First aid measures	
4.1. Description of first aid measures	· · · · · · · · · · · · · · · · · · ·
First-aid measures general	: If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
First-aid measures after skin contact	: Rinse skin with water/shower. Take off contaminated clothing. If skin irritation occurs: Get medical advice/attention.
First-aid measures after eye contact	<ul> <li>Rinse cautiously with water for several minutes. If eye irritation persists: Get medical advice/attention.</li> </ul>
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Call a POISON CENTER or doctor/physician.
4.2. Most important symptoms and effe	cts, both acute and delayed
Symptoms/injuries	: May cause drowsiness or dizziness.
Symptoms/injuries after skin contact	: Irritation.
4.3. Indication of any immediate medica	I attention and special treatment needed
Treat symptomatically.	
SECTION 5: Firefighting measures	
5.1. Extinguishing media	
Suitable extinguishing media	: Carbon dioxide. Dry powder. Foam.
5.2. Special hazards arising from the su	bstance or mixture
Fire hazard	: Extremely flammable aerosol.
Explosion hazard	: Pressurised container: May burst if heated.
Hazardous decomposition products in case of fire	: Toxic fumes may be released.
5.3. Advice for firefighters	
Precautionary measures fire	: Leaking gas fire: Do not extinguish, unless leak can be stopped safely.
Firefighting instructions	: Eliminate all ignition sources if safe to do so.
Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

### Safety Data Sheet

according to Regulation (EC) No. 453/2010

SECTION 6: Accidental release measures			
6.1. Personal precautions, protective equipment and emergency procedures			
General measures	: Avoid release to the environment. Eliminate all ignition sources if safe to do so.		
6.1.1. For non-emergency personnel			
Emergency procedures	: Ventilate spillage area. Do not breathe vapours. Avoid contact with skin and eyes.		
Emergency procedures	. Ventilate spillage area. Do not breathe vapours. Avoid contact with skill and eyes.		
6.1.2. For emergency responders			
Protective equipment	: Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".		
6.2. Environmental precautions			
Avoid release to the environment.			
6.3. Methods and material for containn	nent and cleaning up		
For containment	: Collect spillage.		
Methods for cleaning up	: Absorb spillage to prevent material damage. Use only non-sparking tools.		
Other information	: This material and its container must be disposed of as hazardous waste.		
6.4. Reference to other sections			
For further information refer to section 13. For the	further information refer to section 8: "Exposure controls/personal protection".		
<b>SECTION 7: Handling and storage</b>			
7.1. Precautions for safe handling			
Additional hazards when processed	: Flammable gas. Pressurized container: Do not pierce or burn, even after use. In use, may form flammable vapour-air mixture.		
Precautions for safe handling	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Use only outdoors or in a well-ventilated area. Avoid breathing gas. Avoid contact with skin and eyes. Wear personal protective equipment.		
Hygiene measures	: Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.		
7.2. Conditions for safe storage, including any incompatibilities			
Technical measures	: Take precautionary measures against static discharge.		
Storage conditions	<ul> <li>Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Keep cool.</li> </ul>		
Incompatible products	: Oxidizing agent. Strong acids.		
Storage temperature	: 10 - 30 °C		
Storage area	: Store in a well-ventilated place.		
Special rules on packaging	: Keep only in original container.		
7.3. Specific end use(s)			

No additional information available

# SECTION 8: Exposure controls/personal protection 8.1. Control parameters

propan-2-ol (67-63-0)		
United Kingdom	Local name	Propan-2-ol
United Kingdom	WEL TWA (mg/m <sup>3</sup> )	999 mg/m³
United Kingdom	WEL TWA (ppm)	400 ppm
United Kingdom	WEL STEL (mg/m <sup>3</sup> )	1250 mg/m <sup>3</sup>
United Kingdom	WEL STEL (ppm)	500 ppm

### 8.2. Exposure controls

Appropriate engineering controls	: Ensure good ventilation of the work station. Eliminate ignition sources.
Hand protection	: In case of repeated or prolonged contact wear gloves. Butyl rubber
Eye protection	: Safety glasses
Skin and body protection	: Wear suitable protective clothing
Respiratory protection	: In case of inadequate ventilation wear respiratory protection
Environmental exposure controls	: Avoid release to the environment.
Other information	: Do not eat, drink or smoke when using this product.

Safety Data Sheet

according to Regulation (EC) No. 453/2010

according to Regulation (EC) No. 453/2010			
SECTION 9: Physical and chemical properties			
9.1. Information on basic physical and chemical properties			
Physical state	: Gas		
Colour	: Colourless.		
Odour	: characteristic.		
Odour threshold	: No data available		
рН	: No data available		
Relative evaporation rate (butylacetate=1)	: No data available		
Melting point	: No data available		
Freezing point	: No data available		
Boiling point	: No data available		
Flash point	: No data available		
Auto-ignition temperature	: No data available		
Decomposition temperature	: No data available		
Flammability (solid, gas)	: Extremely flammable aerosol		
Vapour pressure	: 3.2 - 5.2 bar		
Relative vapour density at 20 °C	: No data available		
Relative density	: No data available		
Density	: 0.6 - 0.7		
Solubility	: immiscible.		
Log Pow	: No data available		
Viscosity, kinematic	: No data available		
Viscosity, dynamic	: No data available		
Explosive properties	: Pressurised container: May burst if heated.		
Oxidising properties	: No data available.		
Explosive limits	: No data available		
9.2. Other information			
VOC content	: 93.6 %		
SECTION 10: Stability and reactivity	tv.		
10.1. Reactivity			
Extremely flammable aerosol. Pressurised cor	ntainer: May hurst if heated		
-			
10.2. Chemical stability			
Stable under normal conditions of use.			
10.3. Possibility of hazardous reactions			
No dangerous reactions known under normal conditions of use.			
10.4. Conditions to avoid			
Keep away from heat, hot surfaces, sparks, op	pen flames and other ignition sources. No smoking.		
10.5. Incompatible materials			
Oxidizing agent.			
10.6. Hazardous decomposition products			
Under normal conditions of storage and use, hazardous decomposition products should not be produced.			
SECTION 11: Toxicological inform	ation		
11.1. Information on toxicological effects			
	: Not classified		
Acute toxicity	. NUL GASSIIICU		

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics (64742-49-0)		
LD50 oral	> 5840 mg/kg bodyweight	
LD50 dermal	> 2920 mg/kg bodyweight	
LC50 inhalation rat (Dust/Mist - mg/l/4h)	> 23300 mg/m <sup>3</sup>	
propan-2-ol (67-63-0)		
LD50 oral	4396 mg/kg bodyweight	
LD50 dermal	12800 mg/kg bodyweight	
LC50 inhalation rat (Dust/Mist - mg/l/4h)	46600 mg/m <sup>3</sup>	

### Safety Data Sheet

according to Regulation (EC) No. 453/2010

(L) COUMARIN (91-64-5)	
LD50 oral	500 mg/kg bodyweight
Skin corrosion/irritation	: Causes skin irritation.
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: May cause drowsiness or dizziness.
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified
Green Line - FRESH SHINE VANILLA	
Vaporizer	Aerosol

12.1. Toxicity		
Ecology - general	: Harmful to aquatic life with long lasting effects.	
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics (64742-49-0)		
LC50 fish 1	> 3 mg/l	
EC50 other aquatic organisms 1	4.6 mg/l EC50 waterflea (48 h)	
EC50 other aquatic organisms 2	10 mg/l IC50 algea (72 h) mg/l	
propan-2-ol (67-63-0)		
LC50 fish 1	9640 mg/l	
EC50 other aquatic organisms 1	13299 mg/l EC50 waterflea (48 h)	
EC50 other aquatic organisms 2	> 1000 mg/l IC50 algea (72 h) mg/l	
(L) COUMARIN (91-64-5)		
LC50 fish 1	56 mg/l	
EC50 other aquatic organisms 1	13.5 mg/l	
EC50 other aquatic organisms 2	IC50 algea (72 h) mg/l	

12.2. Persistence and degradability	2. Persistence and degradability	
Green Line - FRESH SHINE VANILLA		
Persistence and degradability	Not established.	
12.3. Bioaccumulative potential		
Green Line - FRESH SHINE VANILLA		
Bioaccumulative potential	Not established.	
propan-2-ol (67-63-0)		
Log Pow	0.14	
(L) COUMARIN (91-64-5)		
Log Pow	1.39	
12.4. Mobility in soil		
No additional information available		
12.5. Results of PBT and vPvB assessment		
No additional information available		

12.6. Other adverse effects	
Other adverse effects	: None known.
Additional information	: Avoid release to the environment
SECTION 13: Disposal considerati	ons
13.1. Waste treatment methods	
Regional legislation (waste)	: Disposal must be done according to official regulations.
Waste disposal recommendations	: Dispose of contents/container to a licensed hazardous-waste disposal contractor or collection site except for empty clean containers which can be disposed of as non-hazardous waste.

Safety Data Sheet

according to Regulation (EC) No. 453/2010	
<b>SECTION 14: Transport informati</b>	on
In accordance with ADR / RID / IMDG / IATA	
14.1. UN number	
UN-No. (ADR)	: 1950
UN-No. (IMDG)	: 1950
UN-No. (IATA)	: 1950
UN-No. (ADN)	: 1950
UN-No. (RID)	: 1950
14.2. UN proper shipping name	
Proper Shipping Name (ADR)	: AEROSOLS
Proper Shipping Name (IMDG)	: AEROSOLS
Proper Shipping Name (IATA)	: Aerosols, flammable
Proper Shipping Name (ADN)	: AEROSOLS
Proper Shipping Name (RID)	: AEROSOLS
Transport document description (ADR)	: UN 1950 AEROSOLS, 2.1, (D)
Transport document description (IMDG)	: UN 1950 AEROSOLS, 2.1
14.3. Transport hazard class(es)	
ADR	
Transport hazard class(es) (ADR)	: 2.1
Danger labels (ADR)	: 2.1
	2
IMDG	
Transport hazard class(es) (IMDG)	: 2.1
Danger labels (IMDG)	: 2.1
ΙΑΤΑ	
Transport hazard class(es) (IATA)	: 2.1
Hazard labels (IATA)	: 2.1
ADN	
Transport hazard class(es) (ADN)	: 2.1
Danger labels (ADN)	: 2.1
	<b>W</b>
RID	
Transport hazard class(es) (RID)	: 2.1

Safety Data Sheet

Danger labels (RID)	: 2.1			
	2			
4.4. Packing group				
Packing group (ADR)	: Not applicable			
Packing group (IMDG)	: Not applicable			
Packing group (IATA)	: Not applicable : Not applicable			
Packing group (ADN)				
Packing group (RID)	: Not applicable			
4.5. Environmental hazards				
Dangerous for the environment	: No			
Marine pollutant	: No			
Other information	: No supplementary information available			
4.6. Special precautions for user				
Overland transport				
Classification code (ADR)	: 5F			
Special provisions (ADR)	: 190, 327, 344, 625			
Limited quantities (ADR)	: 11			
Excepted quantities (ADR)	: E0			
Packing instructions (ADR)	: P207, LP02			
Special packing provisions (ADR)	: PP87, RR6, L2			
Aixed packing provisions (ADR)	: MP9			
Fransport category (ADR)	: 2			
Special provisions for carriage - Packages	: V14			
ADR)				
Special provisions for carriage - Loading, Inloading and handling (ADR)	: CV9, CV12			
Special provisions for carriage - Operation ADR)	: S2			
Funnel restriction code (ADR)	: D			
Transport by sea				
Special provisions (IMDG)	: 63, 190, 277, 327, 344, 959			
imited quantities (IMDG)	: SP277			
Excepted quantities (IMDG)	: E0			
Packing instructions (IMDG)	: P207, LP02			
Special packing provisions (IMDG)	: PP87, L2			
EmS-No. (Fire)	: F-D			
EmS-No. (Spillage)	: S-U			
Stowage category (IMDG)	: None			
Stowage and segregation (IMDG)	Protected from sources of heat For AEROSOLS with a maximum capacity of 1 litre: Category A. Segregation as for class 9 but 'Separated from' class 1 except division 1.4. For AEROSOL' with a capacity above 1 litre: Category B. Segregation as for the appropriate sub-division of class 2. For WASTE AEROSOLS: Category C. Clear of living quarters. Segregation as for the appropriate sub-division of class 2.			
Air transport				
PCA Excepted quantities (IATA)	: E0			
PCA Limited quantities (IATA)	: Y203			
PCA limited quantity max net quantity (IATA)	: 30kgG			
	: 203			
PCA packing instructions (IATA)				
	: 75kg			
PCA max net quantity (IATA)	: 75kg			

EN (English)

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Inland waterway transport Classification code (ADN) Special provisions (ADN)	: 5F
Special provisions (ADN)	
1 1 ( )	. 5F
	: 19, 327, 344, 625
imited quantities (ADN)	: 1L
Excepted quantities (ADN)	: E0
Equipment required (ADN)	: PP, EX, A
/entilation (ADN)	: VE01, VE04
Number of blue cones/lights (ADN)	: 1
Carriage prohibited (ADN)	: No
Not subject to ADN	: No
Rail transport	
Classification code (RID)	: 5F
Special provisions (RID)	: 190, 327, 344, 625
imited quantities (RID)	: 1L
Excepted quantities (RID)	: E0
Packing instructions (RID)	: P207, LP02
Special packing provisions (RID)	: PP87, RR6, L2
lixed packing provisions (RID)	: MP9
ransport category (RID)	: 2
Special provisions for carriage – Packages RID)	: W14
Special provisions for carriage - Loading, Inloading and handling (RID)	: CW9, CW12
Colis express (express parcels) (RID)	: CE2
lazard identification number (RID)	: 23
Carriage prohibited (RID)	: No

#### Not applicable

### **SECTION 15: Regulatory information**

Safety, health and environmental regulations/legislation specific for the substance or mixture 15.1.

#### 15.1.1. **EU-Regulations**

Contains no REACH substances with Annex XVII restrictions Contains no substance on the REACH candidate list Contains no REACH Annex XIV substances

VOC content

: 93.6 %

#### 15.1.2. National regulations

No additional information available

#### 15.2. **Chemical safety assessment**

No chemical safety assessment has been carried out

### **SECTION 16: Other information**

### Full text of H- and FUH-statements.

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4	
Aerosol 1	Aerosol, Category 1	
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2	
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3	
Asp. Tox. 1	Aspiration hazard, Category 1	
Carc. 1A	Carcinogenicity, Category 1A	
Carc. 1B	Carcinogenicity, Category 1B	
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2	
Flam. Gas 1	Flammable gases, Category 1	
Flam. Liq. 2	Flammable liquids, Category 2	
12/08/2015	EN (English)	8/9

### Safety Data Sheet

according to Regulation (EC) No. 453/2010

Muta. 1B	Germ cell mutagenicity, Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Sensitisation — Skin, category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H220	Extremely flammable gas
H222	Extremely flammable aerosol
H225	Highly flammable liquid and vapour
H229	Pressurised container: May burst if heated
H302	Harmful if swallowed
H304	May be fatal if swallowed and enters airways
H315	Causes skin irritation
H317	May cause an allergic skin reaction
H319	Causes serious eye irritation
H336	May cause drowsiness or dizziness
H340	May cause genetic defects
H350	May cause cancer
H411	Toxic to aquatic life with long lasting effects
H412	Harmful to aquatic life with long lasting effects

SDS EU TURTLEWAX

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product