



# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Date of issue: 30/09/2016

Revision date:

Version: 1.1

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixtures  
Product name : Power Out – Carpet and Mats Cleaner  
Vaporizer : Aerosol

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Intended for general public  
Main use category : Consumer use  
Use of the substance/mixture : Automotive Care Products.

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

Turtle Wax Europe Limited  
4th Floor Alaska House, Atlantic Park,  
Liverpool, L30 4AB - United Kingdom  
T +44 151 530 4740  
[MSDS@turtlewaxeurope.com](mailto:MSDS@turtlewaxeurope.com)

#### 1.4. Emergency telephone number

Emergency number : +44 151 530 4740  
Office hours only 08:30 - 17:00

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture


##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol 1 H222;H229  
Aerosol 3 H229  
Eye Irrit. 2 H319

Full text of hazard classes and H-statements : see section 16

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :    
GHS02 GHS07

Signal word (CLP) : Danger

Hazard statements (CLP) : H222 - Extremely flammable aerosol  
H229 - Pressurised container: May burst if heated  
H319 - Causes serious eye irritation

Precautionary statements (CLP) : P102 - Keep out of reach of children  
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P211 - Do not spray on an open flame or other ignition source  
P251 - Do not pierce or burn, even after use  
P280 - Wear protective gloves, protective clothing, eye protection, face protection  
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F

#### 2.3. Other hazards

Adverse physicochemical, human health and : Extremely flammable aerosol. Pressurised container: May burst if heated. Causes serious eye

# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

environmental effects

irritation.

### SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable

#### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Hydrocarbons, C3-4-rich, petroleum distillate, Petroleum gas, [A complex combination of hydrocarbons produced by distillation and condensation of crude oil. It consists of hydrocarbons having carbon numbers in the range of C3 through C5, predominantly C3 through C4.]	(CAS No) 68512-91-4 (EC No) 270-990-9 (EC Index No) 649-083-00-0	1 - 20	Press. Gas Flam. Gas 1, H220
Sulphuric acid, mono-C12-14-alkyl esters, sodium salts	(CAS No) 85586-07-8 (EC No) 287-809-4	< 10	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318 Aquatic Chronic 3, H412
Sodium N- lauroylsarcosinate	(CAS No) 137-16-6 (EC No) 205-281-5	< 10	Eye Dam. 1, H318
Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides	(CAS No) 308062-28-4 (EC No) 608-528-9	< 1	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318 Aquatic Acute 1, H400 Aquatic Chronic 2, H411
Methyl 9-dodecenoate (9-dodecenoic acid methyl ester)	(CAS No) 39202-17-0	< 1	Aquatic Acute 1, H400

Full text of H-statements: see section 16

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

First-aid measures general	: If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing. If experiencing respiratory symptoms: Get medical advice/attention.
First-aid measures after skin contact	: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	: Immediately rinse with plenty of water. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: If swallowed, do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person. Get immediate medical advice/attention.

#### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries after inhalation	: Not expected to present a significant inhalation hazard under anticipated conditions of normal use.
Symptoms/injuries after skin contact	: Not expected to present a significant skin hazard under anticipated conditions of normal use. May cause slight irritation.
Symptoms/injuries after eye contact	: Eye irritation.
Symptoms/injuries after ingestion	: Not expected to present a significant ingestion hazard under anticipated conditions of normal use. Ingestion may cause nausea, vomiting and diarrhea.

#### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

### SECTION 5: Fire-fighting measures

#### 5.1. Extinguishing media

Suitable extinguishing media	: Dry powder. Foam. Carbon dioxide.
Unsuitable extinguishing media	: Do not use water jet.

#### 5.2. Special hazards arising from the substance or mixture

Fire hazard	: Extremely flammable aerosol.
Explosion hazard	: Pressurised container: May burst if heated.
Reactivity in case of fire	: Not known.
Hazardous decomposition products in case of fire	: Toxic fumes may be released. Carbon dioxide. Carbon monoxide.

#### 5.3. Advice for firefighters

Precautionary measures fire	: Evacuate area.
-----------------------------	------------------

# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Firefighting instructions	: Evacuate area. Eliminate all ignition sources if safe to do so. Use extinguishing media appropriate for surrounding fire.
Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

##### 6.1.1. For non-emergency personnel

Protective equipment	: Use appropriate personal protection equipment (PPE).
Emergency procedures	: Eliminate all ignition sources if safe to do so. Ventilate spillage area. Do not breathe gas, fume, vapours, spray. Avoid contact with skin and eyes.

##### 6.1.2. For emergency responders

Protective equipment	: Use personal protective equipment as required. For further information refer to section 8: "Exposure controls/personal protection". Avoid contact with skin and eyes. Do not breathe gas/vapour/aerosol.
Emergency procedures	: Eliminate all ignition sources if safe to do so. Ventilate area.

#### 6.2. Environmental precautions

Avoid release to the environment.

#### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up	: Ventilate spillage area. Collect spillage. Take up liquid spill into absorbent material. Place in a suitable container for disposal in accordance with the waste regulations (see Section 13). Use only non-sparking tools.
Other information	: Dispose of materials or solid residues at an authorized site.

#### 6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of solid materials or residues refer to section 13: "Disposal considerations".

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Precautions for safe handling	: Wear personal protective equipment. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Pressurized container: Do not pierce or burn, even after use. Do not spray on an open flame or other ignition source. Use only in well ventilated areas.
Hygiene measures	: Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

#### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions	: Store in a well-ventilated place. Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F. Keep cool.
Incompatible materials	: Direct sunlight. Sources of ignition.
Storage area	: Store away from heat. Store in a well-ventilated place.
Packaging materials	: Keep only in original container.

#### 7.3. Specific end use(s)

Automotive Care Products.

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

No additional information available

#### 8.2. Exposure controls

Appropriate engineering controls	: Ensure adequate ventilation.
Personal protective equipment	: Not required for normal conditions of use.
Materials for protective clothing	: Not required for normal conditions of use
Hand protection	: Not required for normal conditions of use
Eye protection	: Eye protection should only be necessary where liquid could be splashed or sprayed
Skin and body protection	: Not required for normal conditions of use
Respiratory protection	: Not necessary with sufficient ventilation
Environmental exposure controls	: Avoid release to the environment.

# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Consumer exposure controls : Read label before use.

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Aerosol.
Colour	: characteristic.
Odour	: characteristic.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Pressurised container: May burst if heated.
Oxidising properties	: Not applicable.
Explosive limits	: No data available

#### 9.2. Other information

No additional information available

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

Extremely flammable aerosol.

#### 10.2. Chemical stability

Stable under normal conditions.

#### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

#### 10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

#### 10.5. Incompatible materials

Oxidizing agent.

#### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

Acute toxicity : Not classified (Based on available data, the classification criteria are not met)

#### Sodium N-lauroylsarcosinate (137-16-6)

LD50 oral	2888 mg/kg bodyweight
Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitisation	: Not classified (Based on available data, the classification criteria are not met)
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified (Based on available data, the classification criteria are not met)

# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified (Based on available data, the classification criteria are not met)
STOT-repeated exposure	: Not classified (Based on available data, the classification criteria are not met)
Aspiration hazard	: Not classified (Based on available data, the classification criteria are not met)

Power Out – Carpet and Mats Cleaner	
Vaporizer	Aerosol

### SECTION 12: Ecological information

#### 12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Ecology - water	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

Sodium N- lauroylsarcosinate (137-16-6)	
LC50 fish 1	> 100 mg/l

#### 12.2. Persistence and degradability

Power Out – Carpet and Mats Cleaner	
Persistence and degradability	No data available.

#### 12.3. Bioaccumulative potential

Power Out – Carpet and Mats Cleaner	
Bioaccumulative potential	Not established.

Sodium N- lauroylsarcosinate (137-16-6)	
Log Pow	4.1

#### 12.4. Mobility in soil

Power Out – Carpet and Mats Cleaner	
Ecology - soil	No data available.

#### 12.5. Results of PBT and vPvB assessment

No additional information available

#### 12.6. Other adverse effects

Other adverse effects	: None known.
Additional information	: No other effects known

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Regional legislation (waste)	: Disposal must be done according to official regulations.
Waste treatment methods	: Dispose of contents/container in accordance with licensed collector's sorting instructions.
Product/Packaging disposal recommendations	: Container under pressure. Do not drill or burn even after use. Dispose in a safe manner in accordance with local/national regulations. Do not pierce or burn, even after use.

### SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

#### 14.1. UN number

UN-No. (ADR)	: 1950
UN-No. (IMDG)	: 1950
UN-No. (IATA)	: 1950
UN-No. (ADN)	: 1950
UN-No. (RID)	: 1950

#### 14.2. UN proper shipping name

Proper Shipping Name (ADR)	: AEROSOLS
Proper Shipping Name (IMDG)	: AEROSOLS
Proper Shipping Name (IATA)	: Aerosols, flammable
Proper Shipping Name (ADN)	: AEROSOLS
Proper Shipping Name (RID)	: AEROSOLS
Transport document description (ADR)	: UN 1950 AEROSOLS, 2.1, (D)
Transport document description (IMDG)	: UN 1950 AEROSOLS, 2.1

# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 14.3. Transport hazard class(es)

#### ADR

Transport hazard class(es) (ADR) : 2.1

Danger labels (ADR) : 2.1

:



#### IMDG

Transport hazard class(es) (IMDG) : 2.1

Danger labels (IMDG) : 2.1

:



#### IATA

Transport hazard class(es) (IATA) : 2.1

Hazard labels (IATA) : 2.1

:



#### ADN

Transport hazard class(es) (ADN) : 2.2

Danger labels (ADN) : 2.2

:



#### RID

Transport hazard class(es) (RID) : 2.2

Danger labels (RID) : 2.2

:



### 14.4. Packing group

Packing group (ADR) : Not applicable

Packing group (IMDG) : Not applicable

Packing group (IATA) : Not applicable

Packing group (ADN) : Not applicable

Packing group (RID) : Not applicable

### 14.5. Environmental hazards

Dangerous for the environment : No

Marine pollutant : No

# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Other information : No supplementary information available

### 14.6. Special precautions for user

#### - Overland transport

Classification code (ADR) : 5F  
Special provisions (ADR) : 190, 327, 344, 625  
Limited quantities (ADR) : 1I  
Excepted quantities (ADR) : E0  
Packing instructions (ADR) : P207, LP02  
Special packing provisions (ADR) : PP87, RR6, L2  
Mixed packing provisions (ADR) : MP9  
Transport category (ADR) : 2  
Special provisions for carriage - Packages (ADR) : V14  
Special provisions for carriage - Loading, unloading and handling (ADR) : CV9, CV12  
Special provisions for carriage - Operation (ADR) : S2  
Tunnel restriction code (ADR) : D

#### - Transport by sea

Special provisions (IMDG) : 63, 190, 277, 327, 344, 959  
Limited quantities (IMDG) : SP277  
Excepted quantities (IMDG) : E0  
Packing instructions (IMDG) : P207, LP02  
Special packing provisions (IMDG) : PP87, L2  
EmS-No. (Fire) : F-D  
EmS-No. (Spillage) : S-U  
Stowage category (IMDG) : None  
Stowage and segregation (IMDG) : Protected from sources of heat For AEROSOLS with a maximum capacity of 1 litre: Category A. Segregation as for class 9 but 'Separated from' class 1 except division 1.4. For AEROSOLS with a capacity above 1 litre: Category B. Segregation as for the appropriate sub-division of class 2. For WASTE AEROSOLS: Category C. Clear of living quarters. Segregation as for the appropriate sub-division of class 2.  
MFAG-No : 126

#### - Air transport

PCA Excepted quantities (IATA) : E0  
PCA Limited quantities (IATA) : Y203  
PCA limited quantity max net quantity (IATA) : 30kgG  
PCA packing instructions (IATA) : 203  
PCA max net quantity (IATA) : 75kg  
CAO packing instructions (IATA) : 203  
CAO max net quantity (IATA) : 150kg  
Special provisions (IATA) : A145, A167, A802  
ERG code (IATA) : 10L

#### - Inland waterway transport

Classification code (ADN) : 5A  
Special provisions (ADN) : 19, 327, 344, 625  
Limited quantities (ADN) : 1 L  
Excepted quantities (ADN) : E0  
Equipment required (ADN) : PP  
Ventilation (ADN) : VE04  
Number of blue cones/lights (ADN) : 0  
Carriage prohibited (ADN) : No  
Not subject to ADN : No

#### - Rail transport

Classification code (RID) : 5A

# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Special provisions (RID)	: 190, 327, 344, 625
Limited quantities (RID)	: 1L
Excepted quantities (RID)	: E0
Packing instructions (RID)	: P207, LP02
Special packing provisions (RID)	: PP87, RR6, L2
Mixed packing provisions (RID)	: MP9
Transport category (RID)	: 3
Special provisions for carriage – Packages (RID)	: W14
Special provisions for carriage - Loading, unloading and handling (RID)	: CW9, CW12
Colis express (express parcels) (RID)	: CE2
Hazard identification number (RID)	: 20
Carriage prohibited (RID)	: No

### 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Detergent Regulation : Ingredient data sheet:

Component	CAS No	%
Hydrocarbons, C3-4-rich, petroleum distillate, Petroleum gas, [A complex combination of hydrocarbons produced by distillation and condensation of crude oil. It consists of hydrocarbons having carbon numbers in the range of C3 through C5, predominantly C3 through C4.]	68512-91-4	1 - 10%
Sulphuric acid, mono-C12-14-alkyl esters, sodium salts	85586-07-8	1 - 10%
SODIUM LAUROYL SARCOSINATE	137-16-6	1 - 10%
Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides	308062-28-4	0.1 - 1%
Methyl 9-dodecenoate (9-dodecenoic acid methyl ester)	39202-17-0	0.1 - 1%

#### 15.1.2. National regulations

Seveso directive 96/82/EC

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : This information of the Safety Data Sheet is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product. We are not responsible for the correctness of the information provided and any consequences in using it. Please read the SDS carefully before using the product.

Full text of H- and EUH-statements:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aerosol 1	Aerosol, Category 1
Aerosol 3	Aerosol, Category 3
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Gas 1	Flammable gases, Category 1



# Power Out – Carpet and Mats Cleaner

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Press. Gas	Gases under pressure
Skin Irrit. 2	Skin corrosion/irritation, Category 2
H220	Extremely flammable gas
H222	Extremely flammable aerosol
H229	Pressurised container: May burst if heated
H302	Harmful if swallowed
H315	Causes skin irritation
H318	Causes serious eye damage
H319	Causes serious eye irritation
H400	Very toxic to aquatic life
H411	Toxic to aquatic life with long lasting effects
H412	Harmful to aquatic life with long lasting effects

SDS EU TURTLEWAX

*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product*