

# **EVO-STIK Multi-Purpose Silicone Sealant**

**ACETOXY SILICONE SEALANT** 

Date: 20 May 2016 Fact Sheet No.: TDS00073

#### YOUR SMART ADVANTAGES

- Contains a fungicide to prevent mould
- Cures to form tough, long lasting seal
- Suitable for a host of different applications

#### **USES**

EVO-STIK Trade Only Multi-Purpose Silicone Sealant is suitable for interior and exterior use, sealing to many building materials, including ceramics, vitreous enamel and gloss painted surfaces. This high modulus sealant contains a fungicide to inhibit mould and mildew growth, and is resistant to cracking, shrinking and discolouration. It is ideal for joining between tiles and baths, basins, shower trays, kitchen worktops and stainless steel sink tops. It provides excellent adhesion to non-porous surfaces such as glass, stainless steel and ceramics and plastic baths and fittings.

PRODUCT CHARACTERISTICS				
Colours	White, Clear, Brown & Black			
Form	Soft gunnable paste			
Specific Gravity	0.94 approx.			
Composition	Moisture curing acetoxy silicone			
Product Codes	30812742	White	C20 x 12	
	30812741	Clear	C20 x 12	
	30812740	Brown	C20 x 12	
	30811661	Black	C20 x 12	
	30814522	White	C20 x 6	
	30814523	Clear	C20 x 6	

	30814525	Brown	C20 x 6
	30814524	Black	C20 x 6
Storage/Shelf Life	date of man original, uno cool, dry temperature	ufacture w pened pac conditions range +5°C	ths from the hen stored in kaging under within the to +25°C and Protect from

TYPICAL PERFORMANCE DATA (Approx.)				
Application Temperature	+5°C to +40°C			
Service Temperature	-30°C to +80°C			
Coverage	Approx. 11 linear metres of 6mm diameter bead per C20 cartridge			
Drying Times	Skin Formation: 30 to 40 minutes, depending on bead width, temperature and humidity.			
	Through Dry: Approx. 2 - 3mm per 24 hours at 23°C and 50% relative humidity. Fully dry in approx. 1 to 2 days depending on bead width, temperature and humidity.			
	Always tool sealant within 10 minutes of application.			

#### **DIRECTIONS FOR USE**

IMPORTANT: Before using EVO-STIK Trade Only Multi-Purpose Silicone Sealant refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.



#### **PREPARATION**

- 1. Work in warm but well ventilated conditions.
- Joint surfaces must be clean, dry, sound and free from dust, loose material and other contaminants that may impair adhesion.
- 3. If desired place masking tape along the joint edges before application. This can make it easier to make a neat, tooled finish. Use a spatula with a round end to tool the sealant and check that this tool just fits into the gap between the masking tape so that it catches the excess sealant.
- 4. Do a test run without applying any sealant to 'get a feel' for the difficult areas to seal in corners, behind taps and raised joints.

#### **APPLICATION**

- Unscrew the nozzle, and using a sharp knife, carefully cut off the dome of the cartridge, taking care not to damage the thread. Screw the nozzle onto the cartridge.
- 6. Cut off the tapered end of the nozzle at a 45° angle, to a width matching the gap to be sealed.
- 7. Fit the cartridge into the cartridge gun by pressing the release plate and pulling out the plunger. Insert cartridge and repeatedly squeeze the trigger until the sealant appears.
- 8. Place the nozzle at the start of the gap, and gently squeeze the trigger. Push forward slowly, ensuring that contact is made by the sealant with both sides of the gap. At the end of the run, release the trigger and press the plunger release plate of the gun.
- Smooth the sealant with a wet, round ended tool (do not use a wetted finger), remove any excess with a cloth moistened with white spirit and then remove the masking tape (if used) from either side of the bead.
- 10. After use, ensure to wipe away any excess adhesive from the nozzle. Replace the cap.
- 11. The sealant skins over rapidly (approx. 30 to 40 minutes) and is fully cured in approx. 24 hours depending on bead width, temperature and humidity.

#### CLEANING

#### **Uncured Sealant:**

12. Excess uncured adhesive should be removed carefully using a soft scraper. The remainder can be removed using a cloth just moistened with white spirit. Repeat using another clean cloth moistened with white spirit.

#### **Cured Sealant:**

13. There is no adequate solvent; carefully cut away excess with a very sharp knife. Do not use solvent to remove product from skin – use soap and water.

#### **PRECAUTIONS IN USE**

EVO-STIK Trade Only Multi-Purpose Silicone Sealant cannot be applied to surfaces which have frost or ice on them. Do not use on zinc, lead or cement based surfaces. Will not resist abrasion in floor joints. Do not use in swimming pools. Do not use for aquarium applications. Prevent entry of uncured sealant into drains or watercourses. Do not use on or against bitumen. Not suitable for bedding double glazed/insulating glass units into frames. Will not accept paint. Not suitable for pedestrian walkways.

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instructions, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for EVO-STIK Trade Only Multi-Purpose Silicone Sealant, available at www.bostik.co.uk.

#### **BOSTIK HOTLINE**

Smart help +44 (0) 1785 272625



## CONSTRUCTION PRODUCT REGULATION DECLARATION OF PERFORMANCE

No.:TDS00073

Product Description: **EVO-STIK Trade Only Multi-Purpose Silicone Sealant** 

Product Code: 5010591999848, 5010591999824, 5010591999817, 5000403104713

Intended Use: All-Purpose Sealant

Manufacturer: Bostik Ltd

Contact Address: Common Road

Stafford ST16 3EH

System of Assessment: System 3

Harmonised Standard: BS EN 15651-1,2,3:2012

Notified Body: 0074

Declared Performance:

Essential Characteristics	Performance	Harmonised technical specification		
Reaction to Fire	F			
Release of Chemicals	None	See Safety Data Sheet		
Water Tightness & Air Tightness as determined by:				
Resistance to Flow	≤3mm	BS EN 15651-1,2,3:2012		
Loss of Volume	NPD	BS EN 15651-1,2,3:2012		
Elastic Recovery	NPD	BS EN 15651-1,2:2012		
Tensile properties after immersion in water at 23°C*	≥25%	BS EN 15651-1,3:2012		
Tensile properties at maintained extension after immersion in water at 23°C*	NF	BS EN 15651-1,2,3:2012		
Microbiological Growth	NPD	BS EN 15651-3:2012		
Durability	NPD	BS EN 15651-1,2,3:2012		

### \*Conditioning method A, tested on Aluminium Substrate, no primer

The performance of the EVO-STIK Trade Only Multi-Purpose Silicone Sealant, 5010591999848, 5010591999824, 5010591999817, 5000403104713 is in conformity with the declared performance shown in the table above.

This declaration of performance is issued under the sole responsibility of Bostik Ltd.

#### Signed for and on behalf of Bostik Ltd by:

Name: Alison Jamieson Function: S.H.E.Q. Manager

Signature: Date: June 2014



This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Sales Tel: 0844 371 1192 Fax: 01785 241818 <u>customer.service@bostik.com</u>
Technical Advice Tel: 0844 371 1197 Fax: 01785 272867 <u>technical.service@bostik.com</u>
Technical Data & COSHH (MSDS) Data Sheets Tel: 01785 272625 Fax: 01785 212962 <u>stafford.gatehouse@bostik.com</u>

