widespread**solutions**



Booths for Glues, Aerosols and Airbrushes and more.....

Contain and filter for a cleaner, healthier working environment within art, graphics, hobbies, modelling and crafts.

Applications include filtration of:

Aerosol adhesives (glue booths for Spray Mount), aerosol lacquers and fixatives and airbrush sprays applied to artwork up to A2 in size


Craft, hobby, model aerosol and airbrush paints, solders, light grinding particles and dusts, cleaning solvents etc

A300S and A200S

Air Filtration Units



GraphicAir





www.widespreadsolutions.co.uk

GraphicAir Filtration Units Model No's A300S and A200S

NOTE: These units are recirculatory; i.e. filtered air is exhausted back into the workplace.

Description

Steel construction finished in dove grey – plastic replaceable spray/fume shield – back stand / carry handle - particulate filter – carbon impregnated fibre filter – axial fan(s), external rotor motor type brushless, UL, VDE and CSA approved (A200S has two fans) - sealed electrical wiring and switch, downstream of filters


Operation

All WS filtration and extraction systems carry a lifetime warranty, are quiet in operation and can be assembled in seconds. Place onto a desk, bench or trolley and then simply plug in and switch on.

These units can be used in two positions.

Reclining position (on back-stand) – For Spray Mount, aerosol lacquers and fixatives etc. applied to artwork placed onto the filter. A300S accommodates artwork up to A3 and A200S up to A2.

Upright position – For model sprays and airbrush use – light grinding particles – solder fume displacement – general solvent dilution etc.



Filtration

The particulate (intake) filter is a three stage graduated fibre filter with a high 'dust' holding capacity for long life. Filtration to 5 micron particles. NB: Spray particulate sizes vary from 10 to 20 microns.

The carbon impregnated fibre filter (behind intake) assists in the reduction of solvent odours.

Through the process of filtration, adsorption and dilution, operator exposure to concentrations of potentially hazardous substances is vastly reduced.

Specification

| Model Number | Fan Motor* Spec | Air Volume At Free Air | Ave. Air Velocity At Filter Face | Ave. Air Velocity At Shield Face | Noise Level LAeq dB(A) |
|-----------------|--------------------|---------------------------|-------------------------------------|-------------------------------------|---------------------------|
| A300S | 230V 50Hz 40W | 325 m3/hr | 0.5 m/sec | 0.32 m/sec | 59 |
| A2005 | 230V 50Hz 80W | 650 m3/hr | 0.5 m/sec | 0.35 m/sec | 61 |

* 110 Volts 50 or 60Hz available if required

These units are designed as predominantly 'spray traps' for studio/workshop cleanliness and for immediate operator protection from concentrations of airborne contaminants. They are not recommended for continual usage, i.e. production applications, particularly in confined and/or badly ventilated areas.

See GraphicAir extraction cabinets A300S-D, A200H-D and A100H-D for total solvent odour and gas extraction, or TechFlo filtration cabinets for higher specification filtration

Please contact WS for advice on the choice of machine for any given situation.

WS Ltd, Unit 1 Levens Hall Park, Lund Lane, Harrogate, HG3 2BG, UK T: +44 (0) 1423 522836 F: +44 (0) 1423 525656

E: enquiries@widespreadsolutions.co.uk Web: www.widespreadsolutions.co.uk

We go to great lengths to ensure accuracy in our literature, however we cannot be held responsible for errors or omissions. Information is given for guidance only and we reserve the right to alter specification.