Safety Data Sheet



Section 1. Product and Company Identification.

1.1 Model Number; 1.2 Description; 2200HL v3 Trolley Jack 2tonne High Lift Low Entry Hydraulic Oil

1.3 Manufacturer;

Sealey Group. Kempson Way, Bury St. Edmunds, Suffolk. IP32 7AR

1.4 Emergency telephone number; 44 (0) 1284 757 500 (Office Hours)

Date of source compilation; May 2014

Section 2. Hazards Identification.

Not relevant to the Model Number identified in 1.1 with Description stated in 1.2.

Section 3. Substances.

			Classification	
3.1 Chemical Name (substance)	3.1 CAS No.	3.2 Concentration Volume	Hazard Class & Category Code	Hazard Statements
Distillates, Paraffinic Petroleum Oil	64741-51-4	100%	Not classified	-

For full text of Phrases and Statements, see Section 16.

Section 4. First Aid Measures.

4.1 Description of first aid measures

Inhalation

Remove victim to fresh air and keep at rest in a position comfortable for breathing.

Skin Contact

Remove and wash contaminated clothing and shoes. Wash exposed portions of the skin with soap and water.

Eye Contact

Flush eyes with large amounts of water for 15 minutes while holding eyelids open. Seek medical attention.

Ingestion

Seek medical attention. Do not induce vomiting.

Safety Data Sheet

Section 5. Fire Fighting Measures.



5.1. Extinguishing media Foam, dry powder, carbon dioxide. Do not use water jet.

5.2. Special hazards arising from the substance or mixture The product can form flammable mixtures or can burn only on heating above the flash point.

5.3. Advice for fire-fightersDo not enter confined fire space without protective equipment.Only use water only to cool fire exposed containers. Do not use water to fight fire.

Section 6. Accidental Release Measures.

6.1. Personal precautions, protective equipment and emergency procedures If handling hydraulic oil: Ensure there is adequate ventilation. Use Personal Protective Equipment, see Section 8.

6.2. Environmental precautions

Do not empty into drains. Take up with absorbent material, e.g. sawdust, sand or vermiculite. Place materials taken up into disposable container.

6.3. Methods and material for containment and cleaning up Soak up residue with absorbent such as sawdust, sand or vermiculite. Dispose of absorbent and contaminated soil in the same manner as the product.

6.4. Reference to other sectionsSee Section 7 for information on Safe HandlingSee Section 8 for information of Personal Protective Equipment.

See Section 13 for information on disposal.

Section 7. Handling and Storage.

7.1. Precautions for safe handling Prevent small spillage and leakage to avoid slip hazard.

7.2. Conditions for safe storage, including any incompatibilities Store in dry place at room temperature. Adequate ventilation in working area may be necessary.

7.3. Specific end use(s)

Intended for use as hydraulic oil for the Model Number identified in 1.1 with Description stated in 1.2.



Section 8. Exposure Controls/Personal Protection.

Eye/Face Protection

Wear chemical goggles to prevent eye contact.

Skin Protection

Use chemical-resistant gloves, if needed.

Respiratory Protection

Not requires under normal usage. If product is handled in such a way as to create a vapour or mist, an approved respirator should be used to prevent overexposure.

Section 9. Physical and Chemical Properties.

9.1. Information on basic physical and chemical properties

The following information is not a technical specification or sales specification.

	on or sales speetheation
(a) Appearance:	Bright & clear liquid.
(b) Odour:	No information available.
(c) Odour threshold;	No information available.
(d) pH:	No information available.
(e) Melting point/freezing point;	No information available.
(f) Initial boiling point and boiling range;	No information available.
(g) Flash point;	More than 150°C
(h) Evaporation rate;	No information available.
(i) Flammability (solid, gas);	No information available.
(j) Upper/lower flammability or explosive limits;	No information available.
(k) Vapour pressure;	No information available.
(I) Vapour density;	No information available.
(m) Relative density;	No information available.
(n) Solubility (ies);	No information available.
(o) Partition coefficient: n-octanol/water;	No information available.
(p) Auto-ignition temperature;	No information available.
(q) Decomposition temperature;	No information available.
(r) Viscosity;	15.21 CsT (at 40°C)
	2.28 CsT (at 100°C)
(s) Explosive properties;	No information available.
(t) Oxidising properties.	No information available.

9.2 Other information

No information available.

Section 10	Stability and	Reactivity.
------------	---------------	-------------

10.1. Reactivity	No information available.
10.2. Chemical stability	Stable under normal ambient.
10.3. Possibility of hazardous reactions	Hazardous polymerisation will not occur.
10.4. Conditions to avoid	No information available.
10.5. Incompatible materials	Avoid contact with strong oxidants such as liquid chlorine and concentrated oxygen.
10.6. Hazardous decomposition products	Product does decompose at ambient temperature.

available. available. available. available. available. available.



Section 11. Toxicological Information.

11.1. Information on toxicological effects No information available.

Section 12. Ecological Information.

12.1. Toxicity	No information
12.2. Persistence and degradability	No information
12.3. Bioaccumulative potential	No information
12.4. Mobility in soil	No information
12.5. Results of PBT and vPvB assessment	No information
12.6. Other adverse effects	No information

Section 13. Disposal Considerations.

13.1. Waste treatment methods

Disposal must be in accordance with local authority regulations.

Section 14. Transport Information.

Product identified in 1.1 with description stated in 1.2 is not classified as hazardous for transport.

Section 15. Regulatory Information.

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture No information available.

15.2. Chemical safety assessment No information available.

Section 16. Additional Information.

Full text of Phrases and Statements used in Section 3;

The above information is believed to be accurate and represents the best information currently available. No warranty is expressed or implied by the above information.

We assume no liability resulting from use of the above information.

The end user should conduct their own investigations to determine the suitability of the above information for their particular purpose.

Issue level	Date	Revisions
1	07/11/17	First issue.

End of Safety Data Sheet.