

TECHNICAL SPECIFICATIONS

D-Sub Hood:

Material:	Zinc, Nickel Plated
Operating Temperature:	-40°C to +120°C
Cable Entry:	Side Entry Rubber Grommet RGS
Strain relief:	Clamp + Insert
Thumbscrews:	Long Jackscrews UNC 4-40 (Standard)
Cable O.D:	Up to 11.5mm

High Density D-Sub Solder Cup:


Insulator:	Glass filled TP, UL94 V-0
Shell:	Steel, Tin Plated
Contact pins:	Copper Alloy
Stamped & Formed Pins	Class 3, 100 inserts min.
Contact Plating:	Gold flash over Nickel
Operating Temperature:	-55°C to +85°C
Withstanding voltage:	>1000V Rms to 50 Hz for 1 minute
Current Rating:	3A
Insulator resistance:	>5000MΩ min.

Features:

- Available in Sizes HD15-26-44-62
- Long Jackscrews
- 360° EMI Shielding
- Quick assembly
- Pre-mounted locking screws



...with Connectors from:
Amphenol



Size DTSL	Dim A	Dim B	Dim C
9-way	32,2	42,0	15,0
15-way	40,8	42,3	15,0
25-way	54,0	42,3	15,0
37-way	70,5	48,0	15,0

Ordering information:**High Density D-Sub Connector Kits**

Size:	P/N - Kitted:	Product Code - MALE Conn. Kit
9-way	6355-5038-01	DTSL09-RG-LJS-S+L717HDE15P
15-way	6355-5038-02	DTSL15-RG-LJS-S+L717HDA26P
25-way	6355-5038-03	DTSL25-RG-LJS-S+L717HDB44P
37-way	6355-5038-04	DTSL37-RG-LJS-S+L717HDC62P

Size:	P/N - Kitted:	Product Code - FEMALE Conn. Kit
9-way	6355-5038-11	DTSL09-RG-LJS-S+L77HDE15S
15-way	6355-5038-12	DTSL15-RG-LJS-S+L77HDA26S
25-way	6355-5038-13	DTSL25-RG-LJS-S+L77HDB44S
37-way	6355-5038-14	DTSL37-RG-LJS-S+L77HDC62S



Encitech AB
Rörkullsvägen 4
SE-302 41 HALMSTAD, Sweden

Tel.: +46-(0)35-15 13 90
Fax: +46-(0)35-15 13 99

www.encitech.com