

## **PD Series - Internal Enclosed SMPSU Range**

## 15~500Watt Single Output High Quality Industrial Power Supplies with a 3 Year Warranty





- Universal Input 85–264VAC
- All using 105C long life electrolytic capacitors
- 100% full load born-in test
- Protections: Short circuit/OLP/OVP

- Compact Metal Case with Screw Terminal Block
- Compliance to EN 61000-3-2(PFC)
- Applications: industrial, automation and test
- 3 years warranty

Model No	PD-15	PD-25-S	PD-35	PD-50	PD-60	PD-100	PD-150
Ac input voltage	85~264	VACuniversal in	put (PD-150 115	230VAC by swite	ch)		
AC inrush current(max)	Cold sta	rt. 40A at 230V	AC				
DC adjustment range	± 10% b	y potential mete	r for single outp	out			
Overload protection	110%~1	50% hiccup mo	de, auto-recov	ery			
Over voltage protection	115%~1	40% hiccup mo	de, auto-recov	ery (PD-60: sh	ut off)		
Withstand voltage	I/P- O/I	P:3KVAC, I/P-F	G:1.5KVAC, O	P-FG:0.5KVA	C,1 minute		
Working temperature	-20~+7	′0°C(refer to the	derating curve	for different mo	dels)		
Safety standards	UL6095	0-1, TUV EN60	950-1				
EMC standards	En5502	2 class B,EN61	00-3-2,3, EN6	1000-4-2,3,4,5	5,6,8,11, ENV50	0204, EN61000-	-6-2(EN50082-2)
Connection	Screw T	erminal Block f	or input and out	put			
Dimension(L*W*H)( mm)	79×51×28	$79 \times 51 \times 28$	$102 \times 64 \times 33$	99×82×35	129×98×38	$160 \times 98 \times 38$	199×98×38
Case No	P18-1	P18-1	NEW	NEW	P18-2	P18-3	P18-4
Packing	48pcs/9.5kgs	48pcs/10.5kgs	THE W	MEW )	30pcs/14.2kgs	20pcs/13.6kgs	20pcs/15kgs

Model No	PDF-100 (PFC)	PDF -150 (PFC)	PDF-200 (PFC)	PDF-320 (PFC)	GPF-U500S (PFC)
Ac input voltage	85~264VAC;	120~370VDC.			
DC adjustment range	-5~+10% Ra	ted output voltage			
Overload protection	110%~150%	hiccup mode, auto-	recovery		
Over voltage protection	115%~140%	shut off, AC recycle	to re–start		
Withstand voltage	I/P- O/P:3KV	AC, I/P-FG:1.5KVA	C, 1 minute		
Working temperature	-10~+60°C(re	efer to output deratin	g curve)		
Safety standards	UL60950-1,	TUV EN60950-1			
EMC standards	En55022 clas	ss B,EN6100-3-2,3,	EN61000-4-2,3,4,5	,6,8,11, ENV50204	
Connection	Screw Termi	nal Block for input an	d output		
Dimension(L*W*H)( mm)	179*99*50	179*99*50	199*98*50	226*115*50	170*117*94
Case No	P18-5	P18-5	P18-6	P19-1	P19-2
Packing	20pcs/15.2kgs	20pcs/15.2kgs	16pcs/14.2kgs	10pcs/14.5kgs	6pcs/13.2kgs

15W-Single Output					
Model No.	Output	Tol.	R&N	Effi	
PD-15-3.3	3.3V, 0~3A	± 2%	≤80mV	70 %	
PD-15-5	5V, 0~3A	±2%	≤80mV	75 %	
PD-15-12	12V, 0~1.3A	± 1%	≤120mV	80 %	
PD-15-15	15V, 0~1A	± 1%	≤120mV	81 %	
PD-15-24	24V,0~0.63A	± 1%	≤120mV	83 %	

25W-Single Output						
Model No.	Output	Tol.	R&N	Effi		
PD-25-S3.3	3.3V, 0~6A	± 2%	≤80mV	70 %		
PD-25-S5	5V, 0~5A	± 2%	≤80mV	75 %		
PD-25-S12	12V, 0~2.1A	± 1%	≤120mV	80 %		
PD-25-S15	15V, 0~1.7A	± 1%	≤120mV	81 %		
PD-25-S24	24V, 0~1.1A	± 1%	≤120mV	83 %		

## 15~500Watt Single Output High Quality Industrial Power Supplies with a 3 Year Warranty

35W <sup>-</sup> Single Output						
Model No.	Output	Tol.	R&N	Effi		
PD-35-5	5V, 0∼6A	± 2%	≤80mV	77%		
PD-35-12	12V, 0~3A	± 1%	≤120mV	81%		
PD-35-15	15V, 0~2.4A	± 1%	≤120mV	83%		
PD-35-24	24V, 0~1.5A	± 1%	≤120mV	84%		
PD-35-48	48V, 0~0.8A	± 1%	≤240mV	84%		

50W-Single Output					
Model No.	Output	Tol.	R&N	Effi	
PD-50 <b>-</b> 5	5V,0~8A	± 2%	≤80mV	78%	
PD-50-12	12V, 0~4.2A	± 1%	≤120mV	81%	
PD-50-15	15V, 0~3.4A	± 1%	≤120mV	83 %	
PD-50-24	24V, 0~2.2A	± 1%	≤120mV	84%	
PD-50-48	48V, 0~1.1A	± 1%	≤240mV	86 %	

60W-Sing	60W-Single Output					
Model No.	Output	Tol.	R&N	Effi		
PD-60-5	5V, 0~12A	± 2%	≤50mV	83%		
PD-60-12	12V, 0~5A	± 1%	≤120mV	80%		
PD-60-15	15V, 0~4A	± 1%	≤120mV	80%		
PD-60-24	24V, 0~2.5A	± 1%	≤120mV	80%		
PD-60-48	48V, 0~1.25A	±1%	≤240mV	83%		

100W-Single Output					
Model No.	Output	Tol.	R&N	Effi	
PD-100-5	5V, 0~16A	±2%	≤80mV	79%	
PD-100-12	12V, 0~8.5A	± 1%	≤100mV	81%	
PD-100-15	15V, 0~7A	± 1%	≤100mV	83%	
PD-100-24	24V, 0~4.5A	± 1%	≤120mV	85%	
PD-100-48	48V, 0~2.3A	± 1%	≤200mV	84%	

150W-Single Output					
Model No.	Output	Tol.	R&N	Effi	
PD-150-5	5V,0~26A	±2%	≤80mV	79%	
PD-150-12	12V, 0~12.5A	± 1%	≤120mV	83%	
PD-150-15	15V, 0~10 A	± 1%	≤120mV	84%	
PD-150-24	24V, 0~6.5A	± 1%	≤120mV	85%	
PD-150-48	48V, 0~3.3A	±1%	≤200mV	86%	

100W-Single Output (PFC)					
Model No.	Output	Tol.	R&N	Effi	
PDF-100-5	5V, 0~20A	±2%	≤100mV	78 %	
PDF-100-12	12V, 0~8.5A	± 2%	≤100mV	83%	
PDF-100-15	15V, 0~6.7A	±2%	≤100mV	83%	
PDF-100-24	24V, 0~4.2A	± 1%	≤150mV	83%	
PDF-100-48	48V, 0~2.15A	± 1%	≤250mV	84%	

150W-Single Output (PFC)						
Model No.	Output	Tol.	R&N	Effi		
PDF-150-5	5V, 0~30A	± 2%	≤100mV	80%		
PDF-150-12	12V, 0~12.5A	±1%	≤100mV	83%		
PDF-150-15	15V, 0~10A	± 1%	≤100mV	83%		
PDF-150-24	24V, 0~6.3A	± 1%	≤150mV	83%		
PDF-150-48	48V, 0~3.2A	± 1%	≤240mV	83%		

200W-Single Output (PFC)					
Model No.	Output	Tol.	R&N	Effi	
PDF-200-5	5V, 0~40A	±2%	≤100mV	83%	
PDF-200-12	12V, 0~16.7	4 ±2%	≤100mV	79%	
PDF-200-15	15V, 0~13.4A	± 2%	≤100mV	82%	
PDF-200-24	24V, 0~8.4A	± 1%	≤150mV	82%	
PDF-200-48	48V, 0~4.2A	± 1%	≤250mV	83%	

320W-Single Output (PFC)						
Model No.	Output	Tol.	R&N	Effi		
PDF-320-4	4V, 0~60A	±2%	≤100mV	79%		
PDF-320-5	5V, 0~60A	± 2%	≤150mV	79%		
PDF-320-12	12V, 0~25A	± 1%	≤150mV	86%		
PDF-320-15	15V, 0~21A	± 1%	≤150mV	87%		
PDF-320-24	24V, 0~13A	± 1%	≤150mV	87%		
PDF-320-48	48V, 0~6.7A	± 1%	≤240mV	88%		

500W-Single Output (PFC)							
Model No.	Output	Tol.	R&N	Effi			
GPF-U500S12	12V, 0~40A	± 3%	≤120mV	78%			
GPF-U500S15	15V, 0~33A	± 3%	≤150mV	80%			
GPF-U500S24	24V, 0~20A	± 3%	≤240mV	81%			
GPF-U500S27.5	27.5V, 0~18	A ±3%	≤270mV	86%			
GPF-U500S36	36V, 0~13.8A	4 ±3%	≤360mV	82%			
GPF-U500S48	48V, 0~10A	±3%	≤480mV	82%			