



Features:

- Universal AC input
- Built in active PFC, PF>0.95
- Operating altitude up to 5000m
- 100% full load burn in test
- PCB both sides with conformal coating

- Highly efficient and high reliability
- Protections:
SCP/OLP/OPP
- Built in cooling fan speed control
- 3 Year Warranty

Specifications					
Part Number	GKF-320-5II	GKF-320-12II	GKF-320-24II	GKF-320-36II	GKF-320-48II
DC Output	5V	12V	24V	36V	48V
Rated Current	55A	25A	13A	8.8A	6.7A
Current Range	0~55A	0~25A	0~13A	0~8.8A	0~6.7A
Ripple & Noise	<150mV	<150mV	<200mV	<200mV	<200mV
Voltage ADJ. Range	-5%~+10% rated output voltage				
Voltage Accuracy	+1.0%				
Line Regulation	+0.5%				
Load Regulation	+1.0%				
Set-up Time	<2S (230Vac input, Full load)				
Hold up Time	>10mS (230Vac input, Full load)				
Temperature Coefficient	+0.03%				
Overshoot and Undershoot	<5.0%				
Voltage Range	85Vac~264Vac, 120Vdc~370Vdc				
Frequency Range	47Hz~63Hz				
Power Factor (Typical)	PF>0.98/115VAC PF>0.95/230VAC				
Efficiency (Typical)	79%	84.5%	87%	87%	87.5%
AC Current (max.)	<4.5A				
Inrush Current (Typical)	<50A@230Vac <30A@115Vac Cold Start				
Leakage Current	Input-Output:<0.25mA Input-PG:<1.0mA				
Over Load	105%~150% of rated output current, hiccup mode, auto recovery				
Over Power	105%~150% of rated output current, hiccup mode, auto recovery				
Short Circuit	Long-term mode, auto recovery				
Operating amb. Temp. & Hum.	-25°C ~ 70°C; 20%~90%RH No condensing				
Vibration	10 ~ 500Hz, 2G 10min/1 cycle period for 60 minutes.				
Storage Temp. & Hum.	-40°C ~ 85°C; 10% ~ 95% RG No condensing				
Safety Standards	UL60950-1 2nd ED; IEC 60950-1:2005(2nd ED) ;EN60950-1:2006				
Withstand Voltage	Primary-Secondary: 3.0KVac; <10mA. Primary-PG: 1.5K Vac <10mA Secondary-PG: 0.5KVDC;<10mA				
Isolation Resistance	>100M ohms				
EMI Conduction & Radiation	Compliance to EN55022, EN55024 Class B				
Harmonic Current	Compliance to EN61000-32,-3				
EMS Immunity	Compliance to EN61000-4-2,3,4,5,6,8,11; EN55024, EN61000-6-2 heavy industry level				
MTBF (Mean time before failure)	More than 200,000Hrs (25°C Full load)				
Dimensions	199x99x50mm				
Packing	12PCS/CTN, 9.8KGS, 0.04CBM				
Cooling method	Cooling by forced air (built in DC fan)				



Stontronics Ltd

Chancerygate Business Centre, Cradock Road, Reading, Berkshire, RG2 0AH.


Tel: +44 (0) 118 931 1199 • Fax: +44 (0) 118 931 1145 • Email: info@stontronics.co.uk • Web: www.stontronics.co.uk

Please Note: Image shown is representative of entire range. Individual PSU image &/or drawings or data sheets available on request.


Stontronics Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice.

Mechanical Specification

unit:mm



Block Diagram



Derating Curve

