

ENERGIZER 341





Industry Standard Dimensions

mm (inches)

7.90 (0.311)
7.62 (0.300)

R0.40 (0.016)
Typical

(+)

0.15 (0.006) Maximum Ref.
Permissible deflection from a flat

0.02 (0.001) Minimum Ref. (applies to top edge of gasket or edge of crimp, whichever is higher)

DESIGNED FOR USE ON CONTINUOUS LOW Dr and

Specifications

Chemical System: Silver Oxide (Zn/Ag₂O)

Nominal Voltage: 1.55 Volts

Typical Capacity: 13 mAh* (to 1.2 volts)


Capacity Test: 68K ohm continuous drain at 21°C

Typical Weight: 0.29 grams (0.009 oz.)

Typical Volume: 0.07 cubic centimeters (0.004 cubic inch)

Impedance (40 Hz): 35 to 45 ohms


^{*} Varies according to the applied load, temperature, and cutoff voltage.



Typical Discharge Charz at ristics

Typical Performance at 21° (70°F)


Schedule: Jus




<u>Schedule</u>	Typical Drains at 1.55V	<u>Load</u>	Cutoff 1.2V
	(milliamperes)	(ohm)	(hours)
Continuous	0.023	68K	565

Temperature Characteristics

Typical Performance at Low Discharge Rates





Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

© Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 4315F Page 1 of 1