


Order code: **01-8026****Scope:**

This specification defines the characteristics of a three core coil cord for use in general power supply applications.

**Construction Details**

		Diameter
Conductor	80/0.15mm Plain Annealed Copper per BS6360, Class 5	1.24mm
Insulation	PVC per BS6746	2.5mm
	Colours: Blue, Brown, Yellow/Green	
Cable	Three insulated conductors cabled together	
Jacket	PVC per BS6746	7.3mm
	Colour: Black	
Jacket Print	“<HAR> 2011 H05VVH8-F COIL”	

**Properties**

Temperature Rating	70°C
Current Rating	10.0 Amp

**Compliance**

BS6500  
Cenelec Harmonized Type H05VVH8-F

**Coil Cord Dimensions**

Coil Dimension	24mm
Dimension A	150mm
Dimension B (Compressed)	380mm
Dimension B (Relaxed)	700-800mm
Dimension B (Stretched)	2200mm

Note: The relaxed dimension has been taken after the cable has been stretched

