



Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Date of issue: 12/08/2015

Revision date:

Version: 1.1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : Green Line - CLEARVUE GLASS CLEAN

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public
Main use category : Consumer use
Use of the substance/mixture : Automotive Care Products.

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Turtle Wax Europe Limited
4th Floor Alaska House, Atlantic Park, Dunnings Bridge Road
Liverpool, L30 4AB - United Kingdom
T +44 151 530 4740
MSDS@turtlewaxeurope.com

1.4. Emergency telephone number

Emergency number : +44 151 530 4740
Office hours only 08:30 - 17:00

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Precautionary statements (CLP) : P102 - Keep out of reach of children

2.3. Other hazards

Adverse physicochemical, human health and environmental effects : To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

Other hazards not contributing to the classification : None under normal conditions.

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
2-BUTOXYETHANOL	(CAS No) 111-76-2 (EC no) 203-905-0 (EC index no) 603-014-00-0 (REACH-no) 01-2119475108-36	1 - 10	Acute Tox. 4 (Inhalation), H332 Eye Irrit. 2, H319 Skin Irrit. 2, H315
3-BUTOXYPROPAN-2-OL	(CAS No) 5131-66-8 (EC no) 225-878-4 (EC index no) 603-052-00-8 (REACH-no) 01-2119475527-28	1 - 10	Eye Irrit. 2, H319 Skin Irrit. 2, H315

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

propan-2-ol	(CAS No) 67-63-0 (EC no) 200-661-7 (EC index no) 603-117-00-0 (REACH-no) 01-2119457558-25	1 - 10	Flam. Liq. 2, H225 STOT SE 3, H336 Eye Irrit. 2, H319
METHOXY-2-PROPANOL	(CAS No) 107-98-2 (EC no) 203-539-1 (EC index no) 603-064-00-3 (REACH-no) 01-2119457435-35	1 - 10	Flam. Liq. 3, H226 STOT SE 3, H336
DIOCTYL SODIUM SULPHOSUCCINATE	(CAS No) 577-11-7 (EC no) 209-406-4 (REACH-no) 01-2119491296-29	0.1 - 1	Skin Irrit. 2, H315 Eye Dam. 1, H318
Ethanol	(CAS No) 64-17-5 (EC no) 200-578-6 (EC index no) 603-002-00-5 (REACH-no) 01-2119457610-43	< 0.1	Flam. Liq. 2, H225 Eye Irrit. 2, H319
METHOXYPROPANOL	(CAS No) 1589-47-5 (EC no) 216-455-5 (EC index no) 603-106-00-0	< 0.1	Flam. Liq. 3, H226 Repr. 1B, H360D STOT SE 3, H335 Skin Irrit. 2, H315 Eye Dam. 1, H318
Pyrithione Zinc	(CAS No) 13463-41-7	< 0.1	Acute Tox. 4 (Oral), H302 Acute Tox. 4 (Inhalation:dust,mist), H332 Eye Dam. 1, H318 Aquatic Acute 1, H400
2-methylisothiazol-3(2H)-one	(CAS No) 2682-20-4	< 0.1	Acute Tox. 4 (Oral), H302 Acute Tox. 3 (Inhalation:dust,mist), H331 Skin Corr. 1B, H314 Skin Sens. 1, H317 Aquatic Acute 1, H400
Partially Fluorinated Alkyl Polyether	(CAS No) 000-00-1	< 0.1	Acute Tox. 4 (Oral), H302 Aquatic Chronic 3, H412
1,2-Benzisothiazolin-3-one	(CAS No) 2634-33-5 (EC no) 220-120-9 (EC index no) 613-088-00-6	< 0.1	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318 Skin Sens. 1, H317 Aquatic Acute 1, H400

Specific concentration limits:

Name	Product identifier	Specific concentration limits
1,2-Benzisothiazolin-3-one	(CAS No) 2634-33-5 (EC no) 220-120-9 (EC index no) 613-088-00-6	(C >= 0.05) Skin Sens. 1, H317

Full text of H-phrases: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Not expected to present a significant hazard under anticipated conditions of normal use.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Not expected to present a significant hazard under anticipated conditions of normal use. Rinse mouth.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries	: To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.
Symptoms/injuries after inhalation	: None under normal use.
Symptoms/injuries after skin contact	: May cause slight irritation.
Symptoms/injuries after eye contact	: May cause slight irritation.
Symptoms/injuries after ingestion	: May cause slight irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam. Carbon dioxide.
------------------------------	--

5.2. Special hazards arising from the substance or mixture

Fire hazard	: The product is not flammable.
Explosion hazard	: Product is not explosive.

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Reactivity in case of fire : Not known.
Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Precautionary measures fire : Not applicable.
Firefighting instructions : Use extinguishing media appropriate for surrounding fire.
Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Avoid release to the environment.

6.1.1. For non-emergency personnel

Protective equipment : Not required for normal conditions of use.
Emergency procedures : Ventilate spillage area.

6.1.2. For emergency responders

Protective equipment : Not required for normal conditions of use. For further information refer to section 8: "Exposure controls/personal protection".
Emergency procedures : Ventilate area. Stop leak if safe to do so.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment : Collect spillage.
Methods for cleaning up : Take up liquid spill into absorbent material. Shovel into suitable and closed container for disposal. This material and its container must be disposed of in a safe way, and as per local legislation.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of solid materials or residues refer to section 13: "Disposal considerations".

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.
Hygiene measures : Always wash hands after handling the product. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool. Store in original container.
Packaging materials : Keep only in original container.

7.3. Specific end use(s)

Automotive Care Products.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Ethanol (64-17-5)		
United Kingdom	Local name	Ethanol
United Kingdom	WEL TWA (mg/m ³)	1920 mg/m ³
United Kingdom	WEL TWA (ppm)	1000 ppm
METHOXY-2-PROPANOL (107-98-2)		
United Kingdom	Local name	1-Methoxypropan-2-ol
United Kingdom	WEL TWA (mg/m ³)	375 mg/m ³
United Kingdom	WEL TWA (ppm)	100 ppm
United Kingdom	WEL STEL (mg/m ³)	560 mg/m ³
United Kingdom	WEL STEL (ppm)	150 ppm
United Kingdom	Remark (WEL)	Sk
propan-2-ol (67-63-0)		
United Kingdom	Local name	Propan-2-ol
United Kingdom	WEL TWA (mg/m ³)	999 mg/m ³

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

propan-2-ol (67-63-0)		
United Kingdom	WEL TWA (ppm)	400 ppm
United Kingdom	WEL STEL (mg/m ³)	1250 mg/m ³
United Kingdom	WEL STEL (ppm)	500 ppm
2-BUTOXYETHANOL (111-76-2)		
United Kingdom	Local name	2-Butoxyethanol
United Kingdom	WEL TWA (mg/m ³)	123 mg/m ³
United Kingdom	WEL TWA (ppm)	25 ppm
United Kingdom	WEL STEL (mg/m ³)	246 mg/m ³
United Kingdom	WEL STEL (ppm)	50 ppm
United Kingdom	Remark (WEL)	Sk, BMGV

8.2. Exposure controls

Appropriate engineering controls	: Ensure good ventilation of the work station.
Personal protective equipment	: Not required for normal conditions of use.
Hand protection	: Protective gloves
Eye protection	: Safety glasses
Skin and body protection	: Wear suitable protective clothing
Respiratory protection	: Not required for normal conditions of use
Environmental exposure controls	: Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: clear.
Odour	: characteristic.
Odour threshold	: No data available
pH	: 3.4 - 3.9
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 58 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 0.993 - 1.003
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Product is not explosive.
Oxidising properties	: Oxidising liquids Not applicable.
Explosive limits	: No data available

9.2. Other information

Refractive index	: 1.341 - 1.343
------------------	-----------------

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

Acids. Oxidizing agent.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

1,2-Benzisothiazolin-3-one (2634-33-5)	
LD50 oral	1020 mg/kg bodyweight
LD50 dermal	> 2000 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	100 mg/m ³
DIOCTYL SODIUM SULPHOSUCCINATE (577-11-7)	
LD50 oral	4620 mg/kg bodyweight
LD50 dermal	> 10000 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	20000 mg/m ³
Ethanol (64-17-5)	
LD50 oral	10470 mg/kg bodyweight
LD50 dermal	15800 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	> 99999 mg/m ³
METHOXY-2-PROPANOL (107-98-2)	
LD50 oral	3739 mg/kg bodyweight
LD50 dermal	> 2000 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	> 26315 mg/m ³
propan-2-ol (67-63-0)	
LD50 oral	4396 mg/kg bodyweight
LD50 dermal	12800 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	46600 mg/m ³
2-BUTOXYETHANOL (111-76-2)	
LD50 oral	1746 mg/kg bodyweight
LD50 dermal	435 mg/kg bodyweight
LC50 inhalation rat (mg/l)	11 ppm/4h
LC50 inhalation rat (Dust/Mist - mg/l/4h)	2200 mg/m ³

Skin corrosion/irritation	: Not classified pH: 3.4 - 3.9
Serious eye damage/irritation	: Not classified pH: 3.4 - 3.9
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: Not classified
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.
Ecology - water	: The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

1,2-Benzisothiazolin-3-one (2634-33-5)	
LC50 fish 1	> 1.6 mg/l
EC50 other aquatic organisms 1	> 1.35 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 0.07 mg/l IC50 alga (72 h) mg/l
DIOCTYL SODIUM SULPHOSUCCINATE (577-11-7)	
LC50 fish 1	28 mg/l
EC50 other aquatic organisms 1	36 mg/l
EC50 other aquatic organisms 2	IC50 alga (72 h) mg/l
Ethanol (64-17-5)	
LC50 fish 1	14200 mg/l
EC50 other aquatic organisms 1	5012 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	275 mg/l IC50 alga (72 h) mg/l
METHOXY-2-PROPANOL (107-98-2)	
LC50 fish 1	> 4600 mg/l
EC50 other aquatic organisms 1	23300 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 500 mg/l IC50 alga (72 h) mg/l
propan-2-ol (67-63-0)	
LC50 fish 1	9640 mg/l
EC50 other aquatic organisms 1	13299 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 1000 mg/l IC50 alga (72 h) mg/l
2-BUTOXYETHANOL (111-76-2)	
LC50 fish 1	1474 mg/l
EC50 other aquatic organisms 1	1550 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	911 mg/l IC50 alga (72 h) mg/l

12.2. Persistence and degradability

Green Line - CLEARVUE GLASS CLEAN	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

Green Line - CLEARVUE GLASS CLEAN	
Bioaccumulative potential	Not established.

1,2-Benzisothiazolin-3-one (2634-33-5)	
Log Pow	0.64
DIOCTYL SODIUM SULPHOSUCCINATE (577-11-7)	
Log Pow	6.1
Ethanol (64-17-5)	
Log Pow	-0.3
METHOXY-2-PROPANOL (107-98-2)	
Log Pow	-0.49
propan-2-ol (67-63-0)	
Log Pow	0.14
2-BUTOXYETHANOL (111-76-2)	
Log Pow	0.83

12.4. Mobility in soil

Green Line - CLEARVUE GLASS CLEAN	
Ecology - soil	Not established.

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Other adverse effects : None known.
Additional information : Avoid release to the environment

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.
Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.
Waste disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

Not regulated for transport

14.2. UN proper shipping name

Proper Shipping Name (ADR)	: Not applicable
Proper Shipping Name (IMDG)	: Not applicable
Proper Shipping Name (IATA)	: Not applicable
Proper Shipping Name (ADN)	: Not applicable
Proper Shipping Name (RID)	: Not applicable

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : Not applicable

IMDG

Transport hazard class(es) (IMDG) : Not applicable

IATA

Transport hazard class(es) (IATA) : Not applicable

ADN

Transport hazard class(es) (ADN) : Not applicable

RID

Transport hazard class(es) (RID) : Not applicable

14.4. Packing group

Packing group (ADR)	: Not applicable
Packing group (IMDG)	: Not applicable
Packing group (IATA)	: Not applicable
Packing group (ADN)	: Not applicable
Packing group (RID)	: Not applicable

14.5. Environmental hazards

Dangerous for the environment	: No
Marine pollutant	: No
Other information	: No supplementary information available

14.6. Special precautions for user

- Overland transport

No data available

- Transport by sea

No data available

- Air transport

No data available

- Inland waterway transport

Carriage prohibited (ADN)	: No
Not subject to ADN	: No

- Rail transport

Carriage prohibited (RID) : No

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Detergent Regulation : Ingredient data sheet:

Component	CAS No	%
AQUA	7732-18-5	>=10%
BUTOXYETHANOL	111-76-2	1 - 10%
3-BUTOXYPROPAN-2-OL	5131-66-8	1 - 10%
ISOPROPYL ALCOHOL	67-63-0	1 - 10%
METHOXYISOPROPANOL	107-98-2	1 - 10%
ACETIC ACID	64-19-7	0.1 - 1%
DIETHYLHEXYL SODIUM SULFOSUCCINATE	577-11-7	0.1 - 1%
ALCOHOL	64-17-5	<0.1%
METHOXYPROPANOL	1589-47-5	<0.1%
Pyrithione Zinc	13463-41-7	<0.1%
2-methylisothiazol-3(2H)-one	2682-20-4	<0.1%
Partially Fluorinated Alkyl Polyether	000-00-1	<0.1%
BENZISOTHIAZOLINONE	2634-33-5	<0.1%

Detergent Regulation : Labelling of contents:

Component	%
BENZISOTHIAZOLINONE	

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Full text of H- and EUH-statements:

Acute Tox. 3 (Inhalation:dust,mist)	Acute toxicity (inhalation:dust,mist) Category 3
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Acute Tox. 4 (Inhalation:dust,mist)	Acute toxicity (inhalation:dust,mist) Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 2	Flammable liquids, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Repr. 1B	Reproductive toxicity, Category 1B
Skin Corr. 1B	Skin corrosion/irritation, Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Sensitisation — Skin, category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Respiratory tract irritation
H225	Highly flammable liquid and vapour
H226	Flammable liquid and vapour
H302	Harmful if swallowed
H314	Causes severe skin burns and eye damage
H315	Causes skin irritation
H317	May cause an allergic skin reaction
H318	Causes serious eye damage
H319	Causes serious eye irritation

Green Line - CLEARVUE GLASS CLEAN

Safety Data Sheet

according to Regulation (EC) No. 453/2010

H331	Toxic if inhaled
H332	Harmful if inhaled
H335	May cause respiratory irritation
H336	May cause drowsiness or dizziness
H360D	May damage the unborn child
H400	Very toxic to aquatic life
H412	Harmful to aquatic life with long lasting effects

SDS EU TURTLEWAX

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product