

2.5mm Silicone Rubber Test Lead Wire

5m Pack

Product Description

Multi-construction Single

Cable Construction

Conductor	Tinned Copper
Cross section	2.5mm ²
Construction(±0.003mm)	T0.08× 462
Standard Dia.	1.98
Jacket	silicone rubber
Thickness	0.95
Jacket Dia.(mm)	3.90±0.15
Color	Red: Black; Blue; Yellow Green

Marking


No Printing

PACKAGING

5M/ plastic Bag

Suitable pieces/Box

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	8.02
Min.Insulation DC Resistance at 20°C (MΩ*Km)	>500
Rated Temperature (°C)	-55~+200
Rated Voltage (V)	300/500

RoHS GUIDELINE

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls(PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	