

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Date of issue: 24/04/2015 Revision date: : Version: 1.1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture

Product name : Green Line - WET N BLACK

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public

Main use category : Consumer use

Use of the substance/mixture : Automotive Care Products.

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Turtle Wax Europe Limited
4th Floor Alaska House, Atlantic Park, Dunnings Bridge Road
Liverpool, L30 4AB - United Kingdom
T +44 151 530 4740
MSDS@turtlewaxeurope.com

1.4. Emergency telephone number

Emergency number : +44 151 530 4740

Office hours only 08:30 - 17:00

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flam. Liq. 3 H226 STOT SE 3 H336

Full text of H-statements: see section 16

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)





GHS02

GHS07

Signal word (CLP) : Warning

Hazardous ingredients : Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics

Hazard statements (CLP) : H226 - Flammable liquid and vapour

H336 - May cause drowsiness or dizziness

Precautionary statements (CLP) : P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No

smoking

P261 - Avoid breathing vapours, fume, mist, spray P271 - Use only outdoors or in a well-ventilated area

P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing P501 - Dispose of contents/container to hazardous or special waste collection point, in

accordance with local, regional, national and/or international regulation

2.3. Other hazards

Adverse physicochemical, human health and

environmental effects

: Flammable liquid and vapour. May cause drowsiness or dizziness.

Other hazards not contributing to the

classification

: None under normal conditions.

12/08/2015 EN (English) 1/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

| Name | Product identifier | % | Classification according to Regulation (EC) No. 1272/2008 [CLP] |
|--|---|---------|---|
| Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics | (CAS No) 64742-48-9 (EC no) 919-857-5 (REACH-no) 01-2119463258-33 | 70 - 80 | STOT SE 3, H336 Asp. Tox. 1, H304 |
| water | (CAS No) 7732-18-5 (EC no) 231-791-2 | 10 - 30 | Not classified |
| Polydimethylsiloxane | (CAS No) 63148-62-9 | 1 - 10 | Not classified |
| WACKER AK 1000 SILICONE FLUID | | 1 - 10 | Not classified |
| ISOTRIDECANOL ETHOXYLATE (EO 3-5) | (CAS No) 24938-91-8 | 0.1 - 1 | Eye Dam. 1, H318 |
| Cyclopentasiloxane, decamethyl- | (CAS No) 541-02-6 | 0.1 - 1 | Not classified |
| Xanthan gum | (CAS No) 11138-66-2 (EC no) 234-394-2 | < 0.1 | Not classified |
| Trimethylphenyl-silsesquioxane | (CAS No) 70131-69-0 | < 0.1 | Not classified |
| Pyrithione Zinc | (CAS No) 13463-41-7 | < 0.1 | Acute Tox. 4 (Oral), H302 Acute Tox. 4 (Inhalation:dust,mist), H332 Eye Dam. 1, H318 Aquatic Acute 1, H400 |
| 2-methylisothiazol-3(2H)-one | (CAS No) 2682-20-4 | < 0.1 | Acute Tox. 4 (Oral), H302 Acute Tox. 3 (Inhalation:dust,mist), H331 Skin Corr. 1B, H314 Skin Sens. 1, H317 Aquatic Acute 1, H400 |
| 1,2-Benzisothiazolin-3-one | (CAS No) 2634-33-5 (EC no) 220-120-9 (EC index no) 613-088-00-6 | < 0.1 | Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318 Skin Sens. 1, H317 Aquatic Acute 1, H400 |

Specific concentration limits:

| Name | Product identifier | Specific concentration limits |
|----------------------------|---|--------------------------------|
| 1,2-Benzisothiazolin-3-one | (CAS No) 2634-33-5 (EC no) 220-120-9 (EC index no) 613-088-00-6 | (C >= 0.05) Skin Sens. 1, H317 |

Full text of H-phrases: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : If medical advice is needed, have product container or label at hand.

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing. Get medical advice/attention.

First-aid measures after skin contact : Wash with plenty of soap and water.

First-aid measures after eye contact : Rinse eyes with water as a precaution. Get medical advice/attention if you feel unwell.

First-aid measures after ingestion : Not expected to present a significant hazard under anticipated conditions of normal use. Rinse

mouth. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries : May cause drowsiness or dizziness. Symptoms/injuries after inhalation : May cause drowsiness or dizziness.

Symptoms/injuries after skin contact : May cause slight irritation.

Symptoms/injuries after eye contact : May cause slight irritation.

Symptoms/injuries after ingestion : May cause slight irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

12/08/2015 EN (English) 2/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

5.2. Special hazards arising from the substance or mixture

Fire hazard : Flammable liquid and vapour. Explosion hazard : Product is not explosive.

Reactivity in case of fire : Not known.

Hazardous decomposition products in case of

fire

: Toxic fumes may be released.

5.3. Advice for firefighters

Protection during firefighting

Precautionary measures fire

: Evacuate area. Stop leak if safe to do so.

Firefighting instructions : Eliminate all ignition sources if safe to do so. Evacuate area. Fight fire with normal precautions

from a reasonable distance. In case of fire: stop leak if safe to do so. Use extinguishing media

appropriate for surrounding fire.

: Do not attempt to take action without suitable protective equipment. Self-contained breathing

apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures

Avoid release to the environment. Evacuate area. No flames, no sparks. Eliminate all sources of ignition. No smoking.

6.1.1. For non-emergency personnel

Protective equipment

: Wear suitable protective clothing, gloves and eye or face protection.

Emergency procedures

: Evacuate unnecessary personnel. Do not breathe vapours. Avoid contact with skin. Eliminate all ignition sources if safe to do so. No smoking. Mark out the contaminated area with signs and prevent access to unauthorized personnel. Only qualified personnel equipped with suitable protective equipment may intervene.

6.1.2. For emergency responders

Protective equipment

: Do not attempt to take action without suitable protective equipment. Respiratory protection. Protective gloves. Avoid breathing vapours. Avoid contact with skin and eyes. For further information refer to section 8: "Exposure controls/personal protection".

Emergency procedures

: Ventilate area. Stop leak if safe to do so. Eliminate all ignition sources if safe to do so. No smoking. Mark out the contaminated area with signs and prevent access to unauthorized personnel. Use only non-sparking tools.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment

: Collect spillage.

Methods for cleaning up

: Take up liquid spill into absorbent material. Shovel into suitable and closed container for disposal. Use only non-sparking tools. This material and its container must be disposed of in a safe way, and as per local legislation.

Other information

: This material and its container must be disposed of as hazardous waste.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of solid materials or residues refer to section 13: "Disposal considerations".

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling

: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Wear personal protective equipment. Avoid breathing vapours, fume, mist, spray. Take precautionary measures against static discharge. Ground/bond container and receiving equipment. Use explosion-proof equipment. Use only non-sparking tools. Flammable vapours may accumulate in the container. Use only outdoors or in a well-ventilated area.

Hygiene measures

: Always wash hands after handling the product. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures

: Take precautionary measures against static discharge. Use only non-sparking tools. Ground/bond container and receiving equipment.

Storage conditions

: Keep away from ignition sources. Store in a well-ventilated place. Keep cool. Keep container tightly closed. Store in original container. Store locked up.

Incompatible materials : Heat sources. Sources of ignition. Packaging materials : Keep only in original container.

7.3. Specific end use(s)

Automotive Care Products.

12/08/2015 EN (English) 3/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Appropriate engineering controls : Eliminate ignition sources. Ensure good ventilation of the work station.

Personal protective equipment : Gloves.

Hand protection : Protective gloves
Eye protection : Safety glasses

Skin and body protection : Wear suitable protective clothing

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment



Environmental exposure controls : Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid Colour : clear. Odour : characteristic. Odour threshold : No data available : No data available рΗ Relative evaporation rate (butylacetate=1) : No data available : Not applicable Melting point Freezing point No data available

Boiling point : $35 \, ^{\circ}\text{C}$ Flash point : $42 \, ^{\circ}\text{C}$

: No data available Auto-ignition temperature Decomposition temperature : No data available : Not applicable Flammability (solid, gas) Vapour pressure : No data available : No data available Relative vapour density at 20 °C Relative density : 0.79 - 0.83 Solubility : No data available Log Pow : No data available · 15 - 30 mm²/s Viscosity, kinematic Viscosity, dynamic : No data available Explosive properties : Product is not explosive. Oxidising properties : Oxidising liquids Not applicable.

Explosive limits : No data available

9.2. Other information

Refractive index : 1.4185 - 1.4225

SECTION 10: Stability and reactivity

10.1. Reactivity

Flammable liquid and vapour.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

12/08/2015 EN (English) 4/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

10.5. Incompatible materials

Acids. Oxidizing agent.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

| 1,2-Benzisothiazolin-3-one (2634-33-5) | |
|--|--------------------------------------|
| LD50 oral | 1020 mg/kg bodyweight |
| LD50 dermal | > 2000 mg/kg bodyweight |
| LC50 inhalation rat (Dust/Mist - mg/l/4h) | 100 mg/m³ |
| Skin corrosion/irritation | : Not classified |
| Serious eye damage/irritation | : Not classified |
| Respiratory or skin sensitisation | : Not classified |
| Germ cell mutagenicity | : Not classified |
| Carcinogenicity | : Not classified |
| Reproductive toxicity | : Not classified |
| Specific target organ toxicity (single exposure) | : May cause drowsiness or dizziness. |
| Specific target organ toxicity (repeated exposure) | : Not classified |
| Aspiration hazard | : Not classified |
| Green Line - WET N BLACK | |
| Viscosity, kinematic | 15 - 30 mm²/s |

| SECTION 12: Ecolog | gical information |
|---------------------------|-------------------|

12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms or to cause long-term adverse

effects in the environment.

Ecology - water : The product is not considered harmful to aquatic organisms or to cause long-term adverse

effects in the environment.

| Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics (64742-48-9) | |
|---|------------------------------------|
| LC50 fish 1 | > 1000 mg/l |
| EC50 other aquatic organisms 1 | > 1000 mg/l EC50 waterflea (48 h) |
| EC50 other aquatic organisms 2 | > 1000 mg/l IC50 algea (72 h) mg/l |
| 1,2-Benzisothiazolin-3-one (2634-33-5) | |
| LC50 fish 1 | > 1.6 mg/l |
| EC50 other aquatic organisms 1 | > 1.35 mg/l EC50 waterflea (48 h) |
| EC50 other aquatic organisms 2 | > 0.07 mg/l IC50 algea (72 h) mg/l |

12.2. Persistence and degradability

| Green Line - WET N BLACK | |
|-------------------------------|------------------|
| Persistence and degradability | Not established. |

12.3. Bioaccumulative potential

| Green Line - WET N BLACK | |
|--|------------------|
| Bioaccumulative potential | Not established. |
| water (7732-18-5) | |
| Log Pow | -1.38 |
| 1,2-Benzisothiazolin-3-one (2634-33-5) | |
| Log Pow | 0.64 |

12.4. Mobility in soil

| Green Line - WET N BLACK | |
|--------------------------|------------------|
| Ecology - soil | Not established. |

12.5. Results of PBT and vPvB assessment

No additional information available

12/08/2015 EN (English) 5/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

12.6. Other adverse effects

Other adverse effects : None known.

Additional information : Avoid release to the environment

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions. Do

not flush liquid into public sewer or water systems.

Waste disposal recommendations : Avoid release to the environment. Discharging into rivers and drains is forbidden. Dispose of

contents/container to a hazardous or special waste collection point.

Additional information : Flammable vapours may accumulate in the container.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

 UN-No. (ADR)
 : 1993

 UN-No. (IMDG)
 : 1993

 UN-No. (IATA)
 : 1993

 UN-No. (ADN)
 : 1993

 UN-No. (RID)
 : 1993

14.2. UN proper shipping name

Proper Shipping Name (ADR) : FLAMMABLE LIQUID, N.O.S.
Proper Shipping Name (IMDG) : FLAMMABLE LIQUID, N.O.S.
Proper Shipping Name (IATA) : Flammable liquid, n.o.s.
Proper Shipping Name (ADN) : FLAMMABLE LIQUID, N.O.S.
Proper Shipping Name (RID) : FLAMMABLE LIQUID, N.O.S.

Transport document description (ADR) : UN 1993 FLAMMABLE LIQUID, N.O.S. (Methanol(67-56-1)), 3, III, (D/E)

Transport document description (IMDG) : UN 1993 FLAMMABLE LIQUID, N.O.S., 3, III

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : 3
Danger labels (ADR) : 3



IMDG

Transport hazard class(es) (IMDG) : 3
Danger labels (IMDG) : 3



IATA

Transport hazard class(es) (IATA) : 3
Hazard labels (IATA) : 3

3

12/08/2015 EN (English) 6/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

ADN

Transport hazard class(es) (ADN) : 3 Danger labels (ADN) : 3



RID

Transport hazard class(es) (RID) : 3 Danger labels (RID) : 3





Packing group

: 111 Packing group (ADR) Packing group (IMDG) : 111 Packing group (IATA) : 111 : III Packing group (ADN) Packing group (RID) : 111

Environmental hazards

Dangerous for the environment : No Marine pollutant : No

Other information : No supplementary information available

14.6. Special precautions for user

- Overland transport

Classification code (ADR) : F1

Special provisions (ADR) : 274, 601, 640E

Limited quantities (ADR) : 51 Excepted quantities (ADR) : E1

Packing instructions (ADR) : P001, IBC03, LP01, R001

Mixed packing provisions (ADR) : MP19 Portable tank and bulk container instructions : T4

(ADR)

Portable tank and bulk container special

provisions (ADR)

Tank code (ADR) : LGBF Vehicle for tank carriage : FL Transport category (ADR) : 3 Special provisions for carriage - Packages : V12

(ADR)

Special provisions for carriage - Operation : S2

(ADR)

Hazard identification number (Kemler No.) : 30

Orange plates

30 1993

: TP1, TP29

Tunnel restriction code (ADR) : D/E EAC code : •3YE

12/08/2015 EN (English) 7/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

- Transport by sea

Special provisions (IMDG) : 223, 274, 955

Limited quantities (IMDG) : 5 L
Excepted quantities (IMDG) : E1

Packing instructions (IMDG) : P001, LP01
IBC packing instructions (IMDG) : IBC03
Tank instructions (IMDG) : T4
Tank special provisions (IMDG) : TP1, TP29
EmS-No. (Fire) : F-E
EmS-No. (Spillage) : S-E
Stowage category (IMDG) : A

- Air transport

PCA Excepted quantities (IATA) : E1 PCA Limited quantities (IATA) : Y344 PCA limited quantity max net quantity (IATA) : 10L PCA packing instructions (IATA) : 355 PCA max net quantity (IATA) : 60L CAO packing instructions (IATA) : 366 CAO max net quantity (IATA) : 220L Special provisions (IATA) · A3 ERG code (IATA) : 3L

- Inland waterway transport

Classification code (ADN) : F1

Special provisions (ADN) : 274, 61, 64E

Limited quantities (ADN) : 5 L Excepted quantities (ADN) : E1 Carriage permitted (ADN) : T Equipment required (ADN) : PP. EX. A Ventilation (ADN) : VE01 Number of blue cones/lights (ADN) : 0 Carriage prohibited (ADN) : No Not subject to ADN : No

- Rail transport

Classification code (RID) : F1

Special provisions (RID) : 274, 601, 640E

Limited quantities (RID) : 5L Excepted quantities (RID) : E1

Packing instructions (RID) : P001, IBC03, LP01, R001

Mixed packing provisions (RID) : MP19
Portable tank and bulk container instructions : T4

(RID)

Portable tank and bulk container special

: TP1, TP29

provisions (RID)

Tank codes for RID tanks (RID) : LGBF
Transport category (RID) : 3
Special provisions for carriage – Packages : W12

RID)

Colis express (express parcels) (RID) : CE4
Hazard identification number (RID) : 30
Carriage prohibited (RID) : No

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

12/08/2015 EN (English) 8/9

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Seveso Information : This product is a Seveso Directive 96/82/EC

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Full text of H- and EUH-statements:

| Acute toxicity (inhalation:dust,mist) Category 3 |
|--|
| Acute toxicity (inhalation:dust,mist) Category 4 |
| Acute toxicity (oral), Category 4 |
| Hazardous to the aquatic environment — Acute Hazard, Category 1 |
| Aspiration hazard, Category 1 |
| Serious eye damage/eye irritation, Category 1 |
| Flammable liquids, Category 3 |
| Skin corrosion/irritation, Category 1B |
| Skin corrosion/irritation, Category 2 |
| Sensitisation — Skin, category 1 |
| Specific target organ toxicity — Single exposure, Category 3, Narcosis |
| Flammable liquid and vapour |
| Harmful if swallowed |
| May be fatal if swallowed and enters airways |
| Causes severe skin burns and eye damage |
| Causes skin irritation |
| May cause an allergic skin reaction |
| Causes serious eye damage |
| Toxic if inhaled |
| Harmful if inhaled |
| May cause drowsiness or dizziness |
| Very toxic to aquatic life |
| |

SDS EU TURTLEWAX

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product

12/08/2015 EN (English) 9/9