

Product Description

Multi-construction
Single

Cable Construction

Conductor	Tinned Copper
Cross section	0.25mm ²
Construction(±0.003mm)	T0.08× 50
Standard Dia.	0.65
Jacket	silicone rubber
Thickness	0.65
Jacket Dia.(mm)	2.0±0.1
Color	Red: Black;

Marking


No Printing

PACKAGING

25M/ Reel

Suitable Reels/Box

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	74
Min.Insulation DC Resistance at 20°C (MΩ*Km)	>500
Rated Temperature (°C)	-55~+200
Rated Voltage (V)	300/500

RoHS GUIDELINE

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	