

Order code	Manufacturer code	Description
02-0885	n/a	COAXIAL CABLE RG174AU 50 OHM 30.5M RC

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 9174
Page 1 of 1 Pages

Issue: 4
Issue Date: 3/29/2006
Effective Date: 5/1/2006

A. Construction

Diameters

- | | | | |
|----|---------------|-------------------------------------|-------|
| 1) | Component 1 | 1 X 1 COAX | |
| | a) Conductor | 26 (7/34) AWG BCW | |
| | b) Insulation | 0.0205" Wall, Nom. Polyethylene(PE) | 0.060 |
| | (1) Color(s) | | |
-
- | Cond | Color | Cond | Color | Cond | Color |
|------|-------|------|-------|------|-------|
| 1 | CLEAR | | | | |
-
- | | | | |
|----|-------------|--|----------------|
| 2) | Shield | TC BRAID Shield,85% Coverage, Min. | |
| 3) | Jacket | 0.012" Wall, Nom., Type I PVC | 0.102+/- 0.002 |
| | a) Color(s) | BLACK | |
| | b) Print | ALPHA WIRE-* P/N 9174
RG 174/U RU AWM STYLE 1354 ROHS
* = Factory Code | |

B. Industry Approvals

- | | | | |
|----|----------|-------------------------|--------------|
| 1) | UL | AWM/STYLE1354 | 60°C / 30V |
| 2) | Military | MIL-C-17D/119F RG 174/U | 85°C / 1100V |
- 3) EU Directive 2002/95/EC(RoHS):
All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
- 4) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

C. Physical & Mechanical Properties

- | | | |
|----|-------------------|--------------------|
| 1) | Temperature Range | -40 to 80°C |
| 2) | Bend Radius | 10X Cable Diameter |
| 3) | Pull Tension | 3.9 Lbs, Maximum |

D. Electrical Properties

(For Engineering purposes only)

- | | | |
|-----|---------------------------|------------------------------|
| 1) | Voltage Rating | 1100 V _{RMS} |
| 2) | Characteristic Impedance | 50 Ω +/- 2 |
| 3) | Ground Capacitance | 30.8 pf/ft @1 kHz, Nominal |
| 4) | Velocity of Propagation | 66 % |
| 5) | Conductor DCR | 96.7 Ω/1000ft @20°C, Nominal |
| 6) | OA Shield DCR | 11.8 Ω/1000ft @20°C, Nominal |
| 7) | Voltage Withstanding | 4.5 kV, Minimum |
| 8) | Corona Extinction | 1.5 kV, Minimum |
| 9) | SRL | 20 db, Minimum |
| 10) | Attenuation, Max dB/100ft | 6 @ 50 MHz
48 @ 1 GHz |

E. Other

- | | |
|----|------------|
| 1) | Packaging |
| | a) 1000 FT |
| | b) 500 FT |
| | c) 100 FT |

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.
Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.