


DRAWING & CABLE CONSTRUCTION

SPECIFICATION	16/0.2TC 0.50mm² 20AWG Equipment Wire	P/N	01-0900 、 01-0905 、 01-0910 、 01-0915 、 01-0920 、 01-0925 、 01-0930 、 01-0935 、 01-0940 、 01-0945 、 01-0950
Rapid Catalogy Number	GW010900 、 010905 、 010910 、 010915 、 010920 、 010925 、 010930 、 010935 、 010940 、 010945 、 010950	DATE	17th. Mar., 2016
IN WALL	NO.	SHEET	1/1
TYPE	N/A	VERSION	A.3
LENGTH	100Meters	MADE BY	
100M SPOOL SIZE	03mm-90*60*100	APPROVED BY	
Q'ty/Carton	25 PCS	REVISIONS	
Net Weight	18.5Kgs		
Gross Weight	19.5Kgs		
Measure	0.99'		

MANUFACTURE STANDARD

Proceeding	Description/Color	Materal	Thickness	Outer Diameter	Shape	Resistance ohm/km	Electronic Conductivity	Tension KG	Current Max. A	Rated Voltage
Conductor	16/0.2mm	Tinned Copper				36.8	98%	13	15	
Jacket	11 colors	PVC 105°C	0.33mm	1.6mm±0.1	Round					300V
Printing	N/A									
Printing Contents	N/A									

Drawing



Remark:
Current means maximum amps
for chassis wiring
PVC=polyvinyl chloride