

Trade name: Harz EG Product no.: A2

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name

### **Harz EG**

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

### Relevant identified uses of the substance or mixture

filling compound for electrotecnical use

#### Uses advised against

No data available.

### 1.3 Details of the supplier of the safety data sheet

#### **Address**

BBC Cellpack GmbH Carl-Zeiss-Strasse 20

79761 Waldshut-Tiengen

Telephone no. +49 (0)7741 6007-0 Fax no. +49 (0)7741 64989

e-mail electrical.products@cellpack.com

#### Information provided by / telephone

+49 (0)7741 6007-0

### **Advice on Safety Data Sheet**

msds@cellpack.com

### 1.4 Emergency telephone number

For medical advice (in German and English): +49 (0)551 192 40 (Giftinformationszentrum Nord)

### **SECTION 2: Hazards identification**

### 2.1 Classification of the substance or mixture

#### **Classification information**

This product does not meet the classification and labelling criteria given in the Regulation (EC) No 1272/2008 (CLP).

### 2.2 Label elements

Not relevant

### 2.3 Other hazards

No data available.

### **SECTION 3: Composition/information on ingredients**

### 3.1 Substances

Not applicable. The product is not a substance.

### 3.2 Mixtures

### **Chemical characterization**

Mixture (preparation)

### **Hazardous ingredients**

This product does not contain substances to be mentioned according to EU Regulation No 1907/2006 (REACH), annex II.

### 3.3 Other information

The product does not contain hazardous substances according to EC-Directive 67/548/EWG.



Trade name: Harz EG Product no.: A2

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

### **SECTION 4: First aid measures**

### 4.1 Description of first aid measures

#### **General information**

In all cases of doubt, or when sickness symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person. Remove soiled or soaked clothing immediately.

#### After inhalation

Remove to fresh air, keep patient warm and at rest. Irregular breathing/no breathing: artificial respiration. If unconscious place in recovery position and seek medical advice.

### After skin contact

Wash skin thoroughly with soap and water or use recognised skin cleanser. Do NOT use solvents or thinners.

#### After eye contact

Remove contact lenses, irrigate copiously with clean, fresh water for at least 10 minutes, holding the eyelids apart and seek medical advice.

#### After ingestion

Do not induce vomiting. Call a doctor immediately. Never give anything by mouth to an unconscious person. Keep at rest

### 4.2 Most important symptoms and effects, both acute and delayed

No data available.

### 4.3 Indication of any immediate medical attention and special treatment needed

No data available.

### **SECTION 5: Firefighting measures**

### 5.1 Extinguishing media

### Suitable extinguishing media

Alcohol resistant foam, CO2, powders, water spray

### Unsuitable extinguishing media

High power water jet

### 5.2 Special hazards arising from the substance or mixture

Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazard.

#### 5.3 Advice for firefighters

Appropriate breathing apparatus may be required. Wear protective clothing. Cool endangered containers with water in case of fire. DO NOT ALLOW RUN-OFF FROM FIRE FIGHTING TO ENTER DRAINS OR WATER COURSES

### **SECTION 6: Accidental release measures**

### 6.1 Personal precautions, protective equipment and emergency procedures

#### For non-emergency personnel

Exclude sources of ignition and ventilate the area. Do not inhale vapours. Refer to protective measures listed in sections 7 and 8.

### For emergency responders

No data available. Personal protective equipment (PPE) - see Section 8.

### 6.2 Environmental precautions

Do not allow to enter drains. If the product contaminates lakes, rivers or sewage, inform appropriate authorities in accordance with local regulations.

#### 6.3 Methods and material for containment and cleaning up

Contain and collect spillage with non-combustible absorbent materials, e.g. sand, earth, vermiculite, diatomaceous earth and place in container for disposal according to local regulations (see section 13). Clean preferably with a detergent - avoid use of solvents.



Trade name: Harz EG Product no.: A2

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

#### 6.4 Reference to other sections

No data available.

### **SECTION 7: Handling and storage**

### 7.1 Precautions for safe handling

#### Advice on safe handling

Comply with the health and safety at work laws.

### General protective and hygiene measures

Do not eat or drink during work - no smoking. Wash hands before breaks and after work. Do not inhale vapours.

### Advice on protection against fire and explosion

No special measures necessary.

### 7.2 Conditions for safe storage, including any incompatibilities

#### Technical measures and storage conditions

Always keep in containers of same material as the original one. See also instructions on the label. Avoid heating and direct sunlight. Keep container dry in a cool, well-ventilated place. Protect from heat and direct sunlight.

### Recommended storage temperature

Value 0 - 40 °C

#### Requirements for storage rooms and vessels

Keep container tightly closed. Never use pressure to empty: container is not a pressure vessel. No smoking. Prevent unauthorized access! Containers which are opened must be carefully closed and kept upright to prevent leakage.

### Incompatible products

Keep away from oxidizing agents, from strongly alkaline and strongly acid materials.

### 7.3 Specific end use(s)

No data available.

### SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

No parameters available for monitoring.

### 8.2 Exposure controls

### Appropriate engineering controls

Provide adequate ventilation. Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and solvent vapour below the OEL (=Occupational Exposure Limit), suitable respiratory protection must be worn.

#### Personal protective equipment

#### Respiratory protection

If workers are exposed to concentrations above the exposure limit they must use appropriate, certified respirators: Use half-mask model with cartridge or air-fed.

#### Eye / face protection

Use safety goggles.

### **Hand protection**

Use protective gloves (DIN EN 374). Please read the protective glove manufacturer's information relating to permeation rates and breakthrough times and the particular conditions at the workplace.

#### Other

Personal should wear antistatic clothings made of natural fiber or of high temperature resistant synthetic fiber. All parts of the body should be washed after contact.

#### **Environmental exposure controls**

No data available.

### **SECTION 9: Physical and chemical properties**



Trade name: Harz EG Product no.: A2

Kinematic viscosity

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

### 9.1 Information on basic physical and chemical properties

r cteristic lue ta available g point / boiling range ta available g point/freezing point ta available mposition temperature ta available			
r cteristic lue ta available g point / boiling range ta available g point/freezing point ta available mposition temperature			
r cteristic lue ta available g point / boiling range ta available g point/freezing point ta available mposition temperature			
r cteristic lue ta available g point / boiling range ta available g point/freezing point ta available mposition temperature			
r cteristic lue ta available g point / boiling range ta available g point/freezing point ta available mposition temperature			
teristic lue ta available g point / boiling range ta available g point/freezing point ta available mposition temperature			
teristic lue ta available g point / boiling range ta available g point/freezing point ta available mposition temperature			
ta available g point / boiling range ta available g point/freezing point ta available mposition temperature			
ta available  g point / boiling range ta available  g point/freezing point ta available  mposition temperature			
g point / boiling range ta available g point/freezing point ta available mposition temperature			
ta available  g point/freezing point ta available  nposition temperature			
g point/freezing point ta available nposition temperature			
ta available  nposition temperature			
nposition temperature			
a available			
a arandoro			
point			
d	>  ISO 2592	150	°C
	130 2392		
on temperature			
ta available			
nability			
ta available			
explosion limit			
ta available			
explosion limit			
ta available			
ır pressure			
ta available			
ve vapour density			
ta available			
ve density			
ta available			
ty			
		1.02	g/cm³
ence temperature d	ASTM D 792	23	°C
ility in water nents	partly soluble		
	partry soluble		
ility			
ta available			
on coefficient n-octanol/water (log val ta available	lue)		



Trade name: Harz EG Product no.: A2

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

Value	850 mPa*s
Reference temperature	23 °C
Type	dynamic
Method	ISO 2555

Solvent content			
Value	<	0.5	%

Particle characteristics	
No data available	

### 9.2 Other information

Other information	
No data available.	

### **SECTION 10: Stability and reactivity**

### 10.1 Reactivity

No data available.

### 10.2 Chemical stability

No data available.

### 10.3 Possibility of hazardous reactions

No data available.

### 10.4 Conditions to avoid

Reproduction toxicity
No data available

Stable under recommended storage and handling conditions(See section 7).

### 10.5 Incompatible materials

Keep away from oxidizing agents, strongly alkaline and strongly acid materials in order to avoid exothermic reactions.

### 10.6 Hazardous decomposition products

When exposed to high temperatures may produce hazardous decomposition products such as carbon monoxide and dioxide, smoke, oxides of nitrogen.

### **SECTION** 11: Toxicological information

### 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity	
No data available	
Acute dermal toxicity	
No data available	
Acute inhalational toxicity	
No data available	
Skin corrosion/irritation	
No data available	
Serious eye damage/irritation	
No data available	
Respiratory or skin sensitisation	
No data available	
Germ cell mutagenicity	
No data available	



Trade name: Harz EG Product no.: A2

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

### Carcinogenicity

No data available

### STOT - single exposure

No data available

### STOT - repeated exposure

No data available

### Aspiration hazard

No data available

### 11.2 Information on other hazards

### **Endocrine disrupting properties**

No data available.

#### Other information

The product was classified in toxicological terms on the basis of the results of the calculation procedure outlined within General Directive on Preparations (1999/45/EC).

### **SECTION 12: Ecological information**

### 12.1 Toxicity

#### Toxicity to fish (acute)

No data available

### **Toxicity to fish (chronic)**

No data available

### Toxicity to Daphnia (acute)

No data available

### Toxicity to Daphnia (chronic)

No data available

### Toxicity to algae (acute)

No data available

### Toxicity to algae (chronic)

No data available

### **Bacteria toxicity**

No data available

### 12.2 Persistence and degradability

No data available.

#### 12.3 Bioaccumulative potential

No data available.

### 12.4 Mobility in soil

No data available.

### 12.5 Results of PBT and vPvB assessment

No data available.

### 12.6 Endocrine disrupting properties

No data available.

### 12.7 Other adverse effects

No data available.

### 12.8 Other information

Other information



Trade name: Harz EG Product no.: A2

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

There are no data available on the preparation itself. For components which are dangerous for the environment see section 3

The product should not be allowed to enter drains or water courses.

### **SECTION 13: Disposal considerations**

### 13.1 Waste treatment methods

#### **Product**

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

#### **Packaging**

Contaminated packaging should be emptied as far as possible and after appropriate cleansing may be taken for reuse. Packaging that cannot be cleaned should be disposed of in agreement with the regional waste disposal company.

### **SECTION 14: Transport information**

### 14.1 Transport ADR/RID/ADN

The product is not subject to ADR/RID/ADN regulations.

### 14.2 Transport IMDG

The product is not subject to IMDG regulations.

### 14.3 Transport ICAO-TI / IATA

The product is not subject to ICAO-TI / IATA regulations.

#### 14.4 Other information

No data available.

### 14.5 Environmental hazards

Information on environmental hazards, if relevant, please see 14.1 - 14.3.

### 14.6 Special precautions for user

No data available.

### 14.7 Maritime transport in bulk according to IMO instruments

Not relevant

### **SECTION 15: Regulatory information**

# 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture EU regulations

### Regulation (EC) No 1907/2006 (REACH) Annex XIV (List of substances subject to authorisation)

According to the data available and/or specifications supplied by upstream suppliers, this product does not contain any substances considered as substances requiring authorisation as listed on Annex XIV of the REACH regulation (EC) 1907/2006.

### REACH candidate list of substances of very high concern (SVHC) for authorisation

According to available data and the information provided by preliminary suppliers, the product does not contain substances that are considered substances meeting the criteria for inclusion in annex XIV (List of Substances Subject to Authorisation) as laid down in Article 57 and article 59 of REACH (EC) 1907/2006.

# Regulation (EC) No 1907/2006 (REACH) Annex XVII: RESTRICTIONS ON THE MANUFACTURE, PLACING ON THE MARKET AND USE OF CERTAIN DANGEROUS SUBSTANCES, MIXTURES AND ARTICLES

The product contains following substance(s) that are considered being subject to REACH regulation (EC) 1907/2006 annex XVII.

ann	ZA AVII.			
No	Substance name	CAS no.	EC no.	No
1	2-methylpropan-1-ol	78-83-1	201-148-0	75
2	xvlene	1330-20-7	215-535-7	75

Directive 2012/18/EU on the control of major-accident hazards involving dangerous substances



Trade name: Harz EG Product no.: A2

Current version: 5.0.0, issued: 22.03.2023 Replaced version: 4.3.0, issued: 12.01.2022 Region: GB

This product is not subject to Part 1 or 2 of Annex I.

#### Other regulations

Employment restrictions, according to the regulations for protection of expectant and nursing mothers and the youth health and safety regulations, serving to protect against hazardous materials, should be observed.

### 15.2 Chemical safety assessment

No data available.

### **SECTION 16: Other information**

#### Sources of key data used to compile the data sheet:

Regulation (EC) No 1907/2006 (REACH), 1272/2008 (CLP) as amended in each case.

Directives 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164.

National Threshold Limit Values of the corresponding countries as amended in each case.

Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.

The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding section.

This information is based on our present knowledge and experience.

The safety data sheet describes products with a view to safety requirements.

It does not however, constitute a guarantee for any specific product properties and shall not establish a legally valid contractual relationship.

Document protected by copyright. Alterations or reproductions require the express written permission of UMCO GmbH.

Prod-ID 613866