

TECHNICAL SPECIFICATIONS

D-Sub Hood:


Material:	UL Recognised Plastic Material
Plating:	Nickel over Copper
Operating Temperature:	-55°C to +105°C
Cable Entry:	Top
Thumbscrews:	UNC 4-40 (Standard)
Cable O.D:	Up to 11,5mm

High Density D-Sub Solder Cup:


Insulator:	Glass filled TP, UL94 V-0
Shell:	Steel, Tin Plated
Contact pins:	Copper Alloy Gold Flash over Ni.
Stamped & Formed Pins	Class 3, 100 inserts min.
Contact Plating:	Gold flash over Nickel
Operating Temperature:	-55°C to +85°C
Withstanding voltage:	>1000V Rms to 50 Hz for 1 minute
Current Rating:	3A
Insulator resistance:	>5000MΩ min.

Features:

- Available in sizes 9-15-25
- Quick-Snap locking system
- Re-openable



...with Connectors from:
Amphenol



Size DPPK-M	Dim A	Dim B	Dim C
9-way	32,5	38,0	15,0
15-way	41,0	38,0	15,0
25-way	54,5	40,0	15,0
37-way	71,0	40,0	15,0

Ordering information:**High Density D-Sub Connector Kits**

Size:	P/N - Kitted:	Product Code - MALE Conn. Kit
HD 15	6355-5011-01	DPPK-M-09+L717HDE15P
HD 26	6355-5011-02	DPPK-M-15+L717HDA26P
HD 44	6355-5011-03	DPPK-M-25+L717HDB44P
HD 62	6355-5011-04	DPPK-M-37+L717HDC62P

Size:	P/N - Kitted:	Product Code - FEMALE Conn. Kit
HD 15	6355-5011-11	DPPK-M-09+L77HDE15S
HD 26	6355-5011-12	DPPK-M-15+L77HDA26S
HD 44	6355-5011-13	DPPK-M-25+L77HDB44S
HD 62	6355-5011-14	DPPK-M-37+L77HDC62S



Encitech AB
Rörkullsvägen 4
SE-302 41 HALMSTAD, Sweden

Tel.: +46-(0)35-15 13 90
Fax: +46-(0)35-15 13 99

www.encitech.com