






Electrical Specification

Contact Resistance:  $\leq 30\text{m}\Omega$   
Dielectric Strength: 500V AC  
Insulation Resistance : 1000M $\Omega$   
Operating Temperature: -25°C to +85°C  
Rated Current: 1.5A  
Rated Voltage: 30V  
Lifetime: >1500 mating cycles



| ISS. | AMEND  | DATE     |
|------|--------|----------|
| 1    | ISSUED | 02/08/24 |



| ITEM | DESCRIPTION           | MATERIAL / FINISH  |
|------|-----------------------|--------------------|
| 1    | XLR FT FRAME          | ZINC DIECAST BLACK |
| 2    | USB COVER FRONT       | PA6 / BLACK        |
| 3    | USB COVER REAR        | PA6 / BLACK        |
| 4    | USB2.0 CONNECTOR (4x) | COMPOSITE          |
| 5    | PCB (2x)              | FR4                |
| 6    | SCREW (2x)            | STEEL              |

| RoHS<br>✓COMPLIANT                                                                                                                                     |
|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| TOLERANCE<br>NO DEC. PLACE $\pm$<br>1 DEC. PLACE $\pm$<br>2 DEC. PLACE $\pm$<br>HOLE $\varnothing$ $\pm$<br>ANGLES $\pm$<br>UNLESS<br>OTHERWISE STATED |

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,  
Redhill, Surrey, RH1 2PF, England, UK  
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED  
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2024

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

DO NOT SCALE

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DRAWN: T.J.O.

APPROVED: D.P.J.

TITLE: XLR FT DUAL USB2.0 A-A FEMALE BLACK METAL

DRWG. No. CP30086

FORM: A4DRWGH