






Electrical Specification
Contact Resistance: ≤ 30mΩ
Dielectric Strength: 500V AC
Insulation Resistance : 1000MΩ
Operating Temperature: -25°C to +85°C
Rated Current: 1.5A
Rated Voltage: 30V
Lifetime: >1500 mating cycles



ISS.	AMEND	DATE
1	ISSUED	02/08/24



ITEM	DESCRIPTION	MATERIAL / FINISH
1	XLR FT FRAME	ZINC DIECAST NICKEL
2	USB COVER FRONT	PA6 / BLACK
3	USB COVER REAR	PA6 / BLACK
4	USB3.0 CONNECTOR (4x)	COMPOSITE
5	PCB (2x)	FR4
6	SCREW (2x)	STEEL

RoHS COMPLIANT
TOLERANCE NO DEC. PLACE ± 1 DEC. PLACE ± 2 DEC. PLACE ± HOLE Ø ± ANGLES ± UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.
76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2024

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

DO NOT SCALE

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DRAWN: T.J.O.

APPROVED: D.P.J.

TITLE: XLR FT DUAL USB3.0 A-A FEMALE METAL

DRWG. No. CP30087

FORM: A4DRWGH