

D1RFRD006

7

6

5

4


3

2

1




REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------




VIEW B

A




SEC A-A



NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 5.08MM,POLES: 2-24P
- 3.RATED VOLTAGE/CURRENT:UL 300V/15A
VDE 320V/20A
- 4.OPERATION TEMPERATURES: -40°C~+105°C
- 5.RATED IMPULSE VOLTAGE: 4.0KV
- 6.INSULATION RESISTANCE: 5000MΩ/DC1000V
- 7.UNDIMENSIONED TOLERANCES:

Pitch range in mm		Nominal dimension range in mm						
to	over	to	over	to	over	to	over	
6	10	10	24	30	60	100	150	⌒
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	□



P.C.B LAYOUT

2	2EDGR-Pin header Automatic assembly	1008B00340(H)	XX	COPPER	SN PLATED
2	2EDGR(A)Pin header Manual assembly	1008B00330(H)	XX	COPPER	SN PLATED
1	2EDGRC-5.08-Housing	1009A0YXXA(H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES

DETAILED LISTS	MM (INCH)		MATERIAL:		 DEGSON®			
	TOLERANCES EXCEPT AS NOTED		FINISH:					
	.X ± .XX ± .XXX ± .X" ± .XX" ± .XXX" ±		PART NO.:		NAME: 2EDGRC-5.08-XXP-1Y-00A(H)			
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING			REV T6
			CHKD:		DRAWING NO.: 2EDGRC-5.08-E06			
	THIRD ANGLE PROJECTION		DRFT: HW 08/23/05"		DO NOT SCALE DRAWING		SCALE N/A	SHEET 1/1
	4		3		2		1	