

Equipment Wire

Order code	Manufacturer code	Description
01-2264	n/a	100M REEL GREY/BLUE 7/0.2MM WIRE RC
01-2266	n/a	100M REEL WHITE/BLACK 7/0.2MM WIRE (RC)
01-2258	n/a	100M REEL GREEN/RED 7/0.2MM WIRE RC
01-2260	n/a	100M REEL VIOLET/RED 7/0.2MM WIRE RC
01-2262	n/a	100M REEL GREY/BLACK 7/0.2MM WIRE
01-2252	n/a	100M REEL YELLOW/BLACK 7/0.2MM WIRE RC
01-2254	n/a	100M REEL YELLOW/RED 7/0.2MM WIRE RC
01-2256	n/a	100M REEL YELLOW/GREEN 7/0.2MM WIRE RC
01-2246	n/a	100M REEL RED/BLUE 7/0.2MM WIRE RC
01-2248	n/a	100M REEL ORANGE/BLACK 7/0.2MM WIRE RC
01-2250	n/a	100M REEL ORANGE/RED 7/0.2MM WIRE RC
01-2270	n/a	100M REEL PINK/BLACK 7/0.2MM WIRE RC
01-2272	n/a	100M REEL GREEN/YELLOW 7/0.2MM WIRE RC
01-2244	n/a	100M REEL RED/GREEN 7/0.2MM WIRE RC
01-2240	n/a	100M REEL RED/BLACK 7/0.2MM WIRE RC
01-2242	n/a	100M REEL RED/BROWN 7/0.2MM WIRE RC
01-2268	n/a	100M REEL WHITE/RED 7/0.2MM WIRE RC

Equipment Wire	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

7/0.2mm Equipment Wire – (Bi-Colours)

Equipment Wires to Defence Standard 61-12 Part 6

Specification

7/0.2mm Type 2 [0.22mm²]

Conductor	:	7 Strands of 0.2mm diameter tinned annealed copper wire
Insulation	:	PVC to a radial thickness of 0.3mm
Diameter	:	1.2mm nominal OD
Rating	:	1KV r.m.s., 1.4 amps at 70°C 2.0 amps at 25°C ambient Maximum resistance at 20°C - 88 ohms/Km

NB:- Wires manufactured to Defence Standard 61-12 Part 6 types 1, 2 and 3 also comply with the requirements of BS 4808 classes 1, 2 and 3 for corresponding stranding and types. Because the requirements of Defence Standard 61-12 Part 6 are more rigorous than that required by BS 4808 the converse is not necessarily true.