

D1RFRD006

7

6

5

4


3

2




1

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------




VIEW A



NOTES:


- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 5.0MM,POLES: 2-24P
- 3.RATED VOLTAGE/CURRENT:UL 300V/15A
VDE 320V/20A
- 4.OPERATION TEMPERATURES:-40°C~+105°C
- 5.RATED IMPULSE VOLTAGE:4.0KV
- 6.INSULATION RESISTANCE:5000MΩ/DC1000V
- 7.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm						
	over 6	over 10		over 30	over 60	over 100	over 150		
to 6	to 10	to 24	to 30	to 60	to 100	to 150			
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10	



P.C.B. LAYOUT

2	2EDGV-Pin header Automatic assembly	1007B00340(H)	XX	COPPER	Sn Plated
2	2EDGV-Pin header Manual assembly	1007B00330(H)	XX	COPPER	Sn Plated
1	2EDGVC-5.0 Housing	1019A0YXXA(H)	1	PA66	UL94V-0

DETACHED LISTS			MATERIAL:							
	TOLERANCES EXCEPT AS NOTED		FINISH:							
	.X ± .XX ± .XXX ± .X" ± .XX" ± .XXX" ±		PART NO.:		NAME: 2EDGVC-5.0-XXP-1Y-00A(H)					
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING			REV	T5	
			CHKD:		DRAWING NO.: 2EDGVC-5.0-E01					
	THIRD ANGLE PROJECTION		DRFT:Zhuwm 07/24/04"		DO NOT SCALE DRAWING		SCALE	N/A	SHEET	1/1