






REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------



NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 5.0MM ,POLES: 2P-24P
- 3.RATED VOLTAGE/CURRENT: UL 300V/10A
IEC 250V/17.5A
- 4.OPERATION TEMPERATURES: -40℃~+105℃
- 5.WITHSTANDING VOLTAGE: AC2000V/1MIN
- 6.INSULATION RESISTANCE: 5000MΩ/DC1000V
- 7.WIRE RANGE: 14~26AWG, 0.5~1.5MM²
- 8.MAX.TORQUE VALUE: M2.5, 3.0KGF.CM
- 9.UNDIMENSIONED TOLERANCES:

PITCH RANGE IN MM			NOMINAL DIMENSION RANGE IN MM					
TO 6	OVER 6 TO 10	OVER 10 TO 24	TO 30	OVER 30 TO 60	OVER 60 TO 100	OVER 100 TO 150	OVER 150	
±0.10	±0.15	±0.25	±0.20	±0.30	±0.50	±0.70	±1.00	0.05/1

4	DG126"十"Screws—M2.5	S000001510(H)	XX	steel	Cr ³⁺ Zn
3	DG306 Spring	X000000160(H)	XX	stainless steel	
2	DG306 Pin	4006B00020(H)	XX	Brass	Tin plated
1	DG126—5.0—Housing	4019A.YYXXA(H)	1	PA66	UL94V—C
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES

DETACHED LISTS	MM (INCH)		MATERIAL:		 DEGSON®				
	TOLERANCES EXCEPT AS NOTED		FINISH:						
	.X ± .XX ± .XXX ±	.X" ± .XX" ± .XXX" ±	PART NO.:		NAME: DG126-5.0-XXP-1Y-00A(H)				
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING			REV	T4
		CHKD:		DRAWING NO.: DG126-5.0-E02					
THIRD ANGLE PROJECTION		DRFT: HAOYH 04/06/05		DO NOT SCALE DRAWING		SCALE	1:1	SHEET	1/1