





REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 5.0MM ,POLES: 2-XXP
- 3.RATED VOLTAGE/CURRENT:UL 300V/15A
VDE 250V/18A
- 4.OPERATION TEMPERATURES: -40℃~+105℃
- 5.WITHSTANDING VOLTAGE: AC2000V/1MIN
- 6.INSULATION RESISTANCE: 5000M Ω /DC1000V
- 7.WIRE RANGE: 24~12AWG,2.5MM²
- 8.MAX.TORQUE VALUE: M2.5,4.08KGF.CM
- 9.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm						
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150		
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10	



1	DG128-5.0-Housing	4027A0YXXA(H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTES

DETACHED LISTS	MM (INCH)		MATERIAL:		DEGSON®			
	TOLERANCES EXCEPT AS NOTED		FINISH:					
	.X ± .XX ± .XXX ±		.X' ± .XX' ± .XXX' ±		PART NO.:		NAME: DG128-5.0-XXP-1Y-00A(H)	
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING		REV	T5
			CHKD:		DRAWING NO.: DG128-5.0-E06			
	THIRD ANGLE PROJECTION		DRFT: DZJ 01/13/05"		DO NOT SCALE DRAWING		SCALE	N/A
							SHEET	1/1

4	DG128"-Screws	S000001460(H)	XX	Steel	Cr ³ +Zn
3	DG128-Cage	X000000020(H)	XX	Brass	Ni plated
2	DG128-Pin header	4027B00010(H)	XX	Brass	SnCe