





REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------


NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 7.5MM POLES: 2P-XXP
- 3.RATED VOLTAGE CURRENT:UL 300V 20A
VDE 450V 20A
- 4.OPERATION TEMPERATURES: -40°C~+105°C
- 5.WITHSTANDING VOLTAGE: AC2000V/1MIN
- 6.INSULATION RESISTANCE: 5000M Ω /DC1000V
- 7.WIRE RANGE: 26~12AWG,2.5MM²
- 8.MAX.TORQUE VALUE: M3, 5.1KGF.CM
- 9.UNDIMENSIONED TOLERANCES:

Pitch range in mm		Nominal dimension range in mm						
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150	—
± 0.10	± 0.15	± 0.25	± 0.2	± 0.3	± 0.5	± 0.7	± 1.0	$0.05/10$



SECTION A-A



4	DG129-Cover	4110C0YXXA(H)	1	PA66	UL94V-0
4	DG129-Pin header	4029B00010(H)	XX	Barss	SnCe
3	DG129-Screws-M3	S000001430(H)	XX	Steel	Cr ³ Zn
2	DG129-Cage	X000000200(H)	XX	Brass	Ni plated

1	DG129-7.5 Housing	4110A0YXXA(H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES

TOLERANCES EXCEPT AS NOTED		MATERIAL:	DEGSON [®]		
.X ±	.X' ±	FINISH:			
.XX ±	.XX' ±	PART NO.:	NAME:		
.XXX ±	.XXX' ±		DG129-7.5-XXP-1Y-00A(H)		
ANGLES ± 1°		APPD:	TITLE: ASSEMBLY DRAWING		REV
THIRD ANGLE PROJECTION		CHKD:	DRAWING NO.: DG129-7.5-E01		T1
		DRFT: ZYH 08/08/08"	DO NOT SCALE DRAWING	SCALE	SHEET
			N/A		1/1