



REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------



NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.THICKNESS: 12.20MM
- 3.OPERATION TEMPERATURES: -40℃~+105℃
- 4.WIRE RANGE: 12~4AWG , 0.2~16MM²
- 5.MAX.TORQUE VALUE: M4 ,12.24KGF.CM
- 6.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm					—
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150	⌒ □
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10



SECTION B-B



1	PC16-PE-Housing	6012A0401A(H)	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q"TY	NOTES

TOLERANCES EXCEPT AS NOTED		MATERIAL:	DEGSON®	
.X ±	.X' ±	FINISH:		
.XX ±	.XX' ±	PART NO.:	NAME:	
.XXX ±	.XXX' ±		PC16-PE-01P-1Y-00A(H)	
ANGLES ± 1°		APPD:	TITLE: ASSEMBLY DRAWING	
THIRD ANGLE PROJECTION		CHKD:	DRAWING NO.: PC16-PE-E01	
		DRFT: Zhuwm 11/02/05"	DO NOT SCALE DRAWING	SCALE N/A
			SHEET 1/1	

3	PC 16-PE hardware	6012B00010(H)	1		
2	PC16-PE-Housing	6012A0801A(H)	1	PA66	UL94V-0