

Product Description

Multi-construction
Single

Cable Construction

Conductor	Bare Copper
Cross section	2.5mm ²
Construction(±0.003mm)	0.08× 498
Standard Dia.	2.06
Jacket	PVC
Thickness	0.85
Jacket Dia.(mm)	3.90±0.15
Color	Red(RAL3000); Black; Blue(RAL5015); Yellow(RAL1021) Green(RAL6032)

Marking


No Printing

PACKAGING

5M/ plastic Bag

Suitable pieces/Box

Design



Electrical Characteristics

Max. Conductor DC Resistance at 20°C (Ω/Km)	7.43
Min. Insulation DC Resistance at 20°C (MΩ*Km)	>500
Rated Temperature (°C)	-20~+80
Rated Voltage (V)	300/500

RoHS GUIDELINE

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	