





REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.THICKNESS: 8.2MM
- 3.OPERATION TEMPERATURES: -40℃~+105℃
- 4.WIRE RANGE: 24~10AWG,0.2~6MM²
- 5.MAX.TORQUE VALUE: M4,12.24KGF.CM
- 6.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm					
to	over	over	to	over	over	over	over	
6	6 to 10	10 to 24	30	30 to 60	60 to 100	100 to 150	150	∩
								□
	±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0
								0.05/10



5	PC6-PE-Ground contact	6016B00010(H)	1		
4	PC6-PE Brass cage	X000001280(H)	2	Brass	Ni plated
3	PC6 Screw	S000001490(H)	2	Brass	Ni plated
2	PC6-PE-Housing	6016A0801A(H)	1	PA66	UL94V-0

1	PC6-PE-Housing	6016A0401A(H)		PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
TOLERANCES EXCEPT AS NOTED		DEGSON®			
MATERIAL:		NAME:			
FINISH:		PC6-PE-01P-1Y-00A(H)			
PART NO.:		TITLE: ASSEMBLY DRAWING			
APPD:		DRAWING NO.: PC6-PE-E01		REV	T4
CHKD:		DO NOT SCALE DRAWING		SCALE	N/A
DRFT: LIUM 11/16/05"		SHEET		1/1	

DETACHED LISTS

MM (INCH)	MATERIAL:
TOLERANCES EXCEPT AS NOTED	FINISH:
.X ±	.X' ±
.XX ±	.XX' ±
.XXX ±	.XXX' ±

ANGLES ± 1°	APPD:
THIRD ANGLE PROJECTION	CHKD:
	DRFT: LIUM 11/16/05"

TITLE: ASSEMBLY DRAWING

DRAWING NO.: PC6-PE-E01

DO NOT SCALE DRAWING

SCALE N/A

SHEET 1/1