





REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------



SECTION A-A



NOTES:

1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.

2.PITCH: 7.5MM, POLES: 2-XXP

3.RATED VOLTAGE/CURRENT: UL 300V/15A
VDE 450V/18A

4.OPERATION TEMPERATURES: -40℃~+105℃

5.WITHSTANDING VOLTAGE: AC2000V/1MIN

6.INSULATION RESISTANCE: 5000MΩ/DC1000V

7.WIRE RANGE: 24-12AWG, 2.5MM²

8.MAX.TORQUE VALUE: M2.5, 4.08KGF.CM

9.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm					
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150	
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10

4	DG128 pin Header	4027B00010(H)	XX	Brass	SnCe
3	DG128 "—"screw	S000001460(H)	XX	Steel	Cr ³⁺ Zn
2	DG128 Cage	X000000020(H)	XX	Brass	Ni plated

1	DG128-7.5-Housing	4026A0YXXA(H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTES

DETACHED LISTS	↔ MM (INCH)		MATERIAL:		DEGSON®					
	TOLERANCES EXCEPT AS NOTED		FINISH:							
	.X ± .XX ± .XXX ±		.X' ± .XX' ± .XXX' ±		PART NO.:		NAME: DG128-7.5-XXP-1Y-00A(H)			
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING			REV	T5	
			CHKD:		DRAWING NO.: DG128-7.5-E02					
	THIRD ANGLE PROJECTION		DRFT: Haoyh 06/27/05"		DO NOT SCALE DRAWING		SCALE	N/A	SHEET	1/1